

Contents

Cooperating organisations	9
Acknowledgements	10
Preface	11
Introduction	13
Chapter 1 General requirements	15
1.1 General	15
1.2 Equipment	15
1.3 The Electricity at Work Regulations 1989	16
1.4 The Construction (Design and Management) Regulations 2007	16
1.5 Building Regulations	17
1.5.1 The Building Regulations 2000 (England and Wales)	17
1.5.2 The Building (Scotland) Regulations 2004	19
1.6 Competence	19
Chapter 2 Selection and erection of equipment	21
2.1 General	21
2.2 Compliance with standards	21
2.2.1 European norms (ENs)	21
2.2.2 Harmonization documents (HDs)	21
2.3 Operational conditions and external influences	22
2.3.1 Motors	23
2.3.2 Electromagnetic compatibility (EMC)	23
2.3.3 Harmonics	23
2.4 Identification and notices	24
2.4.1 Cables and conductors	24
2.4.2 Circuits	25
2.4.3 Switchgear	25
2.4.4 Warning notices	25
2.4.5 Other notices	26
2.4.6 Safety signs	26
2.4.7 Notices and identification labels	26
2.5 Mutual detrimental influence	28
2.6 Compatibility	28
2.7 Functional earthing	29

2.8	Low voltage (LV) switchgear and controlgear assemblies	29
2.8.1	Forms of separation	29
2.8.2	General	32

Chapter 3 Protection against overcurrent, electric shock and overvoltage 33

3.1	Protection against electric shock – overview	33
3.1.1	Automatic disconnection of supply	34
3.1.2	Basic protection	34
3.1.3	Fault protection	34
3.1.4	Additional protection	34
3.2	Protective devices	34
3.3	Overcurrent protective devices	34
3.3.1	Motor circuits	36
3.4	Fuses	36
3.5	Circuit-breakers	38
3.5.1	Circuit-breakers for applications not exceeding 440 V a.c.	38
3.5.2	Circuit-breakers for applications not exceeding 1000 V a.c. (MCCBs)	38
3.5.3	Circuit-breakers – general	39
3.6	Insulation monitoring devices (IMDs)	40
3.7	Residual current devices (RCDs)	40
3.7.1	Terminology	41
3.7.2	A wide choice of device	42
3.7.3	Discrimination (selectivity)	43
3.7.4	Additional protection	46
3.7.5	Location of RCDs	46
3.7.6	Selection of types of RCD	46
3.7.7	TT systems	47
3.7.8	Two distinct categories	47
3.7.9	Limitations and precautions	48
3.7.10	Unwanted tripping	48
3.8	Automatic disconnection of supply	49
3.8.1	Types of protective conductor	50
3.8.2	Protective bonding	51
3.8.3	Sizing of earthing conductor and main protective bonding conductors	52
3.8.4	Earthing of flush metal accessory boxes	53
3.9	Protection against voltage disturbances	55
3.9.1	Disturbances due to earth faults in the high voltage system and due to faults in the low voltage system	55
3.9.2	Protection against overvoltages of atmospheric origin or due to switching	55
3.9.3	Equipment impulse withstand voltage	55
3.9.4	AQ criteria and risk assessment	57
3.9.5	Switching overvoltages	57
3.9.6	Surge protective devices (SPDs)	57

Chapter 4	External influences	63
4.1	General	63
4.2	Ambient temperature (AA)	63
4.3	Solar radiation (AN) and ultraviolet radiation	64
4.4	The IP and IK codes	65
4.5	Presence of water (AD) or high humidity (AB)	65
4.6	Presence of solid foreign bodies (AE)	66
4.7	Presence of corrosive or polluting substances (AF)	66
4.8	Impact (AG), vibration (AH) and other mechanical stresses (AJ)	67
4.9	Presence of fauna (AL), flora and/or mould growth (AK)	68
4.10	Potentially explosive atmospheres	69
4.11	Precautions where particular risks of fire exist	69
4.11.1	Locations with risks of fire due to the nature of processed or stored materials	69
4.11.2	Locations constructed of combustible materials	71
4.11.3	Fire propagating structures	71
4.11.4	Locations of national, commercial, industrial or public significance	72
Chapter 5	Installation of cables	73
5.1	Cable selection	73
5.1.1	Conduit, trunking and ducting systems standards	74
5.2	Cables concealed in structures	76
5.2.1	Walls and partitions	76
5.2.2	Floors and ceilings	77
5.3	Cable routes and livestock	78
5.4	Capacities of conduit and trunking	79
5.5	Selection of cables and wiring systems with low emission of smoke and corrosive gases when affected by fire	79
5.6	'Section 20'	80
5.7	Buried cables	81
5.8	Sealing and fire stopping	84
Chapter 6	Sizing of cables	87
6.1	Current-carrying capacity and voltage drop	87
6.2	Diversity	88
6.3	Neutral conductors	88
6.4	Voltage drop in consumers' installations	89
Chapter 7	Other influences	91
7.1	Electrical connections	91
7.2	Cables in contact with thermal insulation	92
7.3	Mutual or individual deterioration	94
7.4	Proximity of wiring systems to other services	95
7.5	Plasticiser migration from PVC insulation	96
7.6	Section 444 Measures against electromagnetic disturbances	97
7.6.1	Introduction to electromagnetic compatibility (EMC)	97

7.6.2	EMC Legislation	97
7.6.3	Scope of BS 7671 Section 444	98
7.6.4	Section 444 and general EMC advice	98
7.6.5	Recommended further reading	105

Chapter 8 Installation of equipment **107**

8.1	Earthing requirements for the installation of equipment having high protective conductor currents	107
8.1.1	Scope	107
8.1.2	The risks	108
8.1.3	Equipment	109
8.1.4	Labelling	109
8.1.5	Ring circuits	109
8.1.6	Radial circuits	112
8.1.7	Busbar systems	112
8.1.8	RCDs and high protective conductor currents	113
8.2	Water heating	113
8.3	Safety services	114
8.4	Other equipment	114
8.5	Luminaires	115
8.5.1	Scope	115
8.5.2	General	115
8.5.3	Protection against fire	115
8.5.4	Transformers, convertors and controlgear	116
8.5.5	Independent lamp controlgear	117
8.5.6	Stroboscopic effect	117
8.6	Highway power supplies, street furniture and external lighting installations	117
8.6.1	Protection against electric shock	117
8.6.2	Equipment doors	117
8.6.3	Devices for isolation and switching	118
8.6.4	Protection and identification of cables	118
8.6.5	External influences	118
8.6.6	Bus shelters, etc. and decorative lighting	119
8.6.7	References	119
8.7	Extra-low voltage lighting installations	119
8.7.1	Protection against overcurrent	119
8.7.2	Isolation and switching	119
8.7.3	Protection against fire	120
8.7.4	Nature of processed or stored materials	120
8.7.5	Fire risk of transformers and convertors	120
8.7.6	Fire risk from short-circuiting of uninsulated conductors	120
8.7.7	Bare conductors	121
8.7.8	Suspended systems	121
8.7.9	Cross-sectional area of conductors	121
8.8	Selection and erection in relation to operation and maintainability	122

Appendix A	Cable capacities of conduit and trunking	123
A1	General	123
A2	Single-core thermoplastic (PVC) insulated cables in straight runs of conduit not exceeding 3 m in length	124
A3	Single-core thermoplastic (PVC) insulated cables in straight runs of conduit exceeding 3 m in length, or in runs of any length incorporating bends or sets	125
A4	Single-core thermoplastic (PVC) insulated cables in trunking	127
A5	Other sizes and types of cable in conduit or trunking, including flexible conduit	128
A6	Background to the tables	129
Appendix B	Degrees of protection provided by enclosures	131
B1	IP code for ingress protection	131
B1.1	General	131
B1.2	Additional letter	133
B1.3	Supplementary letter	133
B1.4	Product marking	134
B1.5	Drip-proof and splashproof	134
B2	IK code for impact protection	135
B2.1	General	135
Appendix C	Standard circuit arrangements and the provision of socket-outlets	137
C1	General	137
C2	Final circuits using socket-outlets and fused connection units complying with BS 1363	137
C2.1	Layout	137
C2.2	Circuit protection	139
C2.3	Conductor size	139
C2.4	Spurs	139
C2.5	Permanently connected equipment	140
C3	Radial final circuits using 16 A socket-outlets complying with BS EN 60309-2 (BS 4343)	140
C3.1	General	140
C3.2	Circuit protection	140
C3.3	Conductor size	140
C3.4	Types of socket-outlet	140
C4	Cooker final circuits in household premises	140
C5	Water heating and electric shower final circuits in household premises	141
C6	Provision of socket-outlets	141
C6.1	Number of socket-outlets	141
C6.2	Sinks and electrical accessories	143
C7	Mounting heights of accessories	143
C7.1	BS 8300:2009+A1:2010 Design of buildings and their approaches to meet the needs of disabled people – Code of practice	144

Appendix D	Limitation of earth fault loop impedance for compliance with Regulation 543.1.1	147
D1	Selection of a circuit protective conductor	153
D2	Steel conduit and trunking	153
D3	Steel-wire armoured cables	155
D4	Mineral insulated cable with copper sheath	159
D5	Thermoplastic (PVC) insulated and sheathed cables to BS 6004	161
Appendix E	Resistance and impedance of copper and aluminium conductors under fault conditions	163
E1	Verification	166
E2	Mineral insulated cable with copper sheath	166
E3	Steel-wire armour, steel conduit and steel trunking	169
Appendix F	Selection and erection of wiring systems	171
F1	General	171
F2	British Standards	178
F3	Fire stopping	178
Appendix G	Notes on methods of support for cables, conductors and wiring systems	179
G1	Cables generally	179
G2	Particular applications	180
G3	Overhead wiring	180
G4	Conduit and cable trunking	184
G5	Conduit bends	185
G6	Spacing of supports for busbar trunking systems	185
Appendix H	Maximum demand and diversity	187
Appendix I	Permitted protective conductor currents	191
Appendix J	Standard symbols, units and graphical symbols for general electrical purposes	193
J1	General symbols	193
	J1.1 SI derived units	195
J2	Symbols for use in schematic wiring diagrams	196
	J2.1 Making and breaking current	197
	J2.2 Isolating	197
	J2.3 Making, breaking and isolating	197
	J2.4 Meters	197
J3	Location symbols for installations	197
Appendix K	Addresses of associated bodies and industry contacts	199
Index		205