

## Base strip - MSTBVA 2,5/ 8-G-5,08-RN - 1936076

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Header, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 8, Pitch: 5.08 mm, Color: green, Contact surface: Tin, Mounting: Soldering, Article with engagement nose




The figure shows a 10-position version of the product

### Why buy this product

- Plug-in direction vertical to the PCB
- Versions with engagement noses for locking plugs with self-locking flanges



### Key commercial data

|                                      |   |
|--------------------------------------|---|
| Packing unit                         | 50 pc   |
| Minimum order quantity               | 50 pc   |
| GTIN                                 | <br>4 017918 822064 |
| Weight per Piece (excluding packing) | 3.26 g  |
| Custom tariff number                 | 85366990  |
| Country of origin                    | Germany   |
| Note                                 | Made to Order (non-returnable)  |

### Technical data

#### Dimensions

|                |          |
|----------------|----------|
| Length         | 8.6 mm   |
| Pitch          | 5.08 mm  |
| Dimension a    | 35.56 mm |
| Pin dimensions | 1 x 1 mm |
| Hole diameter  | 1.4 mm   |

#### General

|                             |                    |
|-----------------------------|--------------------|
| Range of articles           | MSTBVA 2,5/..-G-RN |
| Insulating material group   | IIIa               |
| Rated surge voltage (III/3) | 4 kV               |
| Rated surge voltage (III/2) | 4 kV               |

## Base strip - MSTBVA 2,5/ 8-G-5,08-RN - 1936076

### Technical data

#### General

|   |        |
|---|--------|
| Rated surge voltage (II/2)              | 4 kV   |
| Rated voltage (III/3)                   | 250 V  |
| Rated voltage (III/2)                   | 320 V  |
| Rated voltage (II/2)                    | 400 V  |
| Connection in acc. with standard        | EN-VDE |
| Nominal current I <sub>N</sub>          | 12 A   |
| Maximum load current                    | 12 A   |
| Insulating material                     | PBT    |
| Inflammability class according to UL 94 | V0     |
| Color                                   | green  |
| Number of positions                     | 8      |

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 272607xx |
| eCl@ss 4.1 | 27260701 |
| eCl@ss 5.0 | 27260701 |
| eCl@ss 5.1 | 27260701 |
| eCl@ss 6.0 | 27260704 |
| eCl@ss 7.0 | 27440402 |
| eCl@ss 8.0 | 27440402 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC001121 |
| ETIM 4.0 | EC002637 |
| ETIM 5.0 | EC002637 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211810 |
| UNSPSC 7.0901 | 39121409 |
| UNSPSC 11     | 39121409 |
| UNSPSC 12.01  | 39121409 |
| UNSPSC 13.2   | 39121409 |

### Approvals

#### Approvals

---

#### Approvals

UL Recognized / VDE Gutachten mit Fertigungsüberwachung / cUL Recognized / IECCE CB Scheme / CCA / EAC / cULus Recognized

# Base strip - MSTBVA 2,5/ 8-G-5,08-RN - 1936076

## Approvals

Ex Approvals

Approvals submitted

### Approval details

|                    |       |       |
|--------------------|-------|-------|
| UL Recognized      |       |       |
|                    | B     | D     |
| Nominal current IN | 12 A  | 10 A  |
| Nominal voltage UN | 300 V | 300 V |

|   |       |
|---|-------|
| VDE Gutachten mit Fertigungsüberwachung |       |
| Nominal current IN                      | 12 A  |
| Nominal voltage UN                      | 250 V |

|                    |       |       |
|--------------------|-------|-------|
| cUL Recognized     |       |       |
|                    | B     | D     |
| Nominal current IN | 12 A  | 10 A  |
| Nominal voltage UN | 300 V | 300 V |

|                    |       |
|--------------------|-------|
| IECEE CB Scheme    |       |
| Nominal current IN | 12 A  |
| Nominal voltage UN | 250 V |

|                    |       |
|--------------------|-------|
| CCA                |       |
| Nominal current IN | 12 A  |
| Nominal voltage UN | 250 V |

# Base strip - MSTBVA 2,5/ 8-G-5,08-RN - 1936076

## Approvals

EAC

cULus Recognized

## Accessories

Accessories

Coding element


Coding star - CR-MSTB - 1734401

Coding section, inserted into the recess in the header or the inverted plug, red insulating material



## Drawings

Drilling diagram



Dimensioned drawing

