




This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.



Customer drawing

DIM.S SHELL	A	B	C	Pitch
9	30.70	16.40	25.00	2.74
15	39.00	24.80	33.30	2.74
25	52.90	38.50	47.00	2.77
37	69.20	54.90	63.50	2.77

REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
1			02/19/08	

D-SUB TECHNICAL DATA

SHELL : Steel 2.5um(100u") min tin over 1.25um(50u") min nickel
BODY : Glass filled thermoplastic.
Flame retardant to UL94 V-0 Color Black
CONTACTS : Brass
0.1um(4u") min gold over 1.25um(50u") min nickel
ELECTRICAL : Voltage rating :300 V RMS at 50 Hz
Current rating 7.5A.
Insulation resistance >5000 M Ohms
Contact resistance 20 mOhms max.
CLIMATIC : Temperature range -55 °C up to 85°C
Damp heat 21 days(40 °C-95% HR)
MARKING : Amphenol...(Series No.)
Commercial reference
Manufacturing date

PRODUCT CODE

L 77D X XX S F179

L: RoHS Compliance

77D: tinned shell
for receptacle

Shell Size: E,A,B,C

Termination:
Wire wrap:
F179=length 9.60mm

Contact type:
S: Socket

Configuration: 09,15,25,37

UNLESS OTHERWISE SPECIFIED TOLERANCES		APPROVAL	DATE
U.S.	METRIC	DRAWN	Christine.cui 02/19/08
.X +/-	0.50	CHECKED	lik.wang 02/19/08
.XX +/-	0.30	CHECKED	
.XXX +/-	0.20		
FRACTIONS +/-			
ANGLES +/-	5°		
FOR MATERIALS AND FINISHES SEE NOTES		DRAWING FILE :	
REMOVE SHARP EDGES		ANGLE OF PROJECTION	
DIMENSIONS			
U.S.	INCHES		
METRIC	MM		

Amphenol			
TITLE			
machined contacts connector, D series			
SIZE	DRAWING NO.	REV.	
A4	C L77DXXXXSF179	1	
SCALE	NONE	SHEET 1 OF 1	