

Control- and safety isolating- resp. isolating transformer **STEU 160/23**



Advantages

Dual input voltage 230 and 400 Vac
Very good switch-on behaviour thanks to reduced starting currents
High performance for the volume thanks to compact design
Primary side ± 15 V tapings for voltage adjustment
Very good corrosion protection and low noise thanks to BLOCKIMPEX vacuum impregnation
Quick to cable up thanks to the use of spring-loaded terminals
Contact protected screw connection terminals complying with UVV BGV A3
Simple mounting thanks to robust metal footplate with oval slots
Up to 250 VA with combination footplate for bolted and rail mounting

Applications

As a control transformer for the electrical isolation of the input and output sides. The construction of the transformer to supply control systems according to VDE 0113 is designed.

As an isolating transformer for the safe electrical isolation of the input and output sides. The transformer may be used to set up protective separation as a protective measure in accordance with VDE 0100.

As a safety transformer for the safe electrical isolation of the input and output sides. The transformer is suitable for creating SELV and PELV circuits because of the limit on the output voltage.

Standards



Control transformer
to: VDE 0570 Teil 2-2, DIN EN 61558-2-2, EN 61558-2-2, IEC 61558-2-2,
UL 5085-1/-2, CSA 22.2 No.66
Isolating transformer
to: VDE 0570 Part 2-4, DIN EN 61558-2-4, EN 61558-2-4, IEC 61558-2-4,
UL 5085-1/-2, CSA 22.2 No.66

Approvals




UL 5085-1/-2, CSA 22.2 No.66



Control- and safety isolating- resp. isolating transformer STEU 160/23

Type	STEU 160/23
Electrical data	Input
	Rated input Voltage 230/400 Vac
	Tappings Input ± 15 V
	Rated frequency 50 - 60 Hz
	Output
	Rated output voltage 2 x 115 Vac
	Rated power VDE (DB cos phi=1) 160 VA
	Rated power VDE (KB cos phi=0.5) 490 VA
	No-load voltage (app. x factor) 1.10
	Efficiency 86 %
	Standards
Classification	Control- and isolating transformer
Approvals	
Approvals	cURus
Environment	
Ambient temperature max.	40 °C
Cooling method	self cooling
Safety and protection	
Type	open type
Class of Insulation System	VDE=B, UL=class 130
Protection index	IP 00
Safety class (prepared)	I
Short circuit strength	non-short-circuit proof
PRI Fusing recommendation by circuit breaker with tripping characteristic type 20 x I rated related to set)	
Setting range 230 ± 15 Vac	0.63 - 1.00 A
Setting value 230 ± 15 Vac	0.80 A
Setting range 400 ± 15 Vac	0.40 - 0.63 A
Setting value 400 ± 15 Vac	0.46 A
Order numbers	
Order Number	STEU 160/23

Type	STEU 160/23
Terminal and mounting	Terminals Spring terminal, PE 6.3 x 0.8
	Fixing method Dual purpose base plate also for installation on mounting rails
Fixing screws	M5
Measures and weights	
Weight	2.90 kg



Subjects to change.