

BJDL6-4



Products Low Voltage Products and Systems Connection Devices Terminal Blocks Accessories Jumper Bars

General Information

Extended Product Type:	BJDL6-4
Product ID:	1SNA291194R1700
EAN:	3472592911946
Catalog Description:	BJDL6-4 Jumper Bars
Long Description:	- Jumper bar for spring blocks with the same spacing, - Facilitate & secure your jumper bar assembly process: - Screwless mounting, - Pre-cut poles for alternated jumpering between terminal blocks, - Insulated, - Positive locking.

Additional Information

ABB Industrial IT Suite:	Control IT
Color:	Orange
Country of Origin:	France (FR)
Customs Tariff Number:	39269097
Data Sheet, Technical Information:	1SNC160001C0207-CH-J Accessories
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
EAN:	3472592911946
ETIM 4:	EC000489 - Cross-connector for terminal block
ETIM 5:	EC000489 - Cross-connector for terminal block
ETIM 6:	EC000489 - Cross-connector for terminal block
Function:	Jumper Bars
IT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Instructions and Manuals:	1SNC160001C0207-CH-J Accessories
Invoice Description:	BJDL6-4 Jumper Bars
Minimum Order Quantity:	50 piece
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Number of Poles:	4
Object Classification Code:	X
Order Multiple:	50 piece
Package Level 1 EAN:	3472592911946
Package Level 1 Gross Weight:	0.025 kg
Package Level 1 Length:	250 mm
Package Level 1 Units:	50 piece
Package Level 1 Width:	168 mm
Package Level 2 Units:	2500 piece
Product Main Type:	BJDL
Product Name:	Jumper Bar
Product Net Weight:	0.5 g
Product Packing Type:	Bag
Rated Current (I_n):	Main Circuit 32 A
RoHS Date:	18 08 2005
RoHS Information:	1SND230492F0201
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Selling Unit of Measure:	piece
Short Description:	Jumper Bars BJDL6-4
Spacing:	6 mm
Suitable For:	D4/6.2L D4/6.3L D4/6.4L D4/6.LNTP.L D4/6.NT.L