




Price* : 84.15 GBP



Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LX1D8
Control circuit type	AC 50/60 Hz
[Uc] control circuit voltage	415 V AC 50/60 Hz
Average resistance	21011 Ohm at 20 °C
Inductance of closed circuit	482.42 H
Product compatibility	LC1D115 LC1D150
Mechanical durability	8 Mcycles
Operating rate	1200 cyc/h at <= 60 °C

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	0.3...0.5 Uc at 55 °C drop-out 50/60 Hz 0.8...1.15 Uc at 55 °C operational 50/60 Hz
Inrush power in VA	280...350 VA at 20 °C (cos f 0.9) 60 Hz 280...350 VA at 20 °C (cos f 0.9) 50 Hz
Hold-in power consumption in VA	2...18 VA at 20 °C (cos f 0.9) 50 Hz 2...18 VA at 20 °C (cos f 0.9) 60 Hz
Heat dissipation	3...4.5 W at 50/60 Hz

Environment

Ambient air temperature for operation	-5...60 °C
---------------------------------------	------------

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

RoHS (date code: YYWW)	Compliant - since 0932 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product environmental
Product end of life instructions	Available End of life manual

Contractual warranty

Warranty period	18 months
-----------------	-----------