



SLOPE BI-METAL BLADES

Product Code	Blade-length (inch) (mm)		Blade-thickness (inch) (mm)		Teeth per inch
Self Service Package, 5 Per Pack					
3840-150-5/8-SL-5P	6	150	0.050	1.3	5/8
3840-228-6-SL-5P	6	228	0.050	1.3	6
3840-300-6-SL-5P	9	300	0.050	1.3	6
3840-300-8/12-SL-5P	12	300	0.050	1.3	8/12


Industrial Package, 10 Per Pack

3840-150-5/8-SL-10P	6	150	0.050	1.3	5/8
3840-228-6-SL-10P	9	228	0.050	1.3	6
3840-300-6-SL-10P	12	300	0.050	1.3	6
3840-300-8/12-SL-10P	2	300	0.050	1.3	8/12

Industrial Package, 100 Per Pack

3840-150-5/8-SL-100p	6	150	0.050	1.3	5/8
----------------------	---	-----	-------	-----	-----

- For all-round cutting of metal, plastic, laminates and wood with nails.



SCROLL BI-METAL BLADES

Product Code	Blade-length (inch) (mm)		Blade-thickness (inch) (mm)		Teeth per inch
Self Service Package, 5 Per Pack					
3840-100-10-SC-5P	4	100	0.035	0.9	10
3840-100-14-SC-5P	4	100	0.035	0.9	14
3840-100-18-SC-5P	4	100	0.035	0.9	18
3840-150-4/6-SC-5P	6	150	0.050	1.3	4/6

Industrial Package, 10 Per Pack

3840-150-4/6-SC-10P	6	150	0.050	1.3	4/6
---------------------	---	-----	-------	-----	-----

- For all-round cutting of metal, plastic, laminates and wood with nails.



DEMOLITION/FIRE & RESCUE BI-METAL BLADES

Product Code	Blade-length (inch) (mm)		Blade-thickness (inch) (mm)		Teeth per inch
Self Service Package, 5 Per Pack					
3840-150-5/8-DSL-5P	6	150	0.062	1.6	5/8
3840-228-5/8-DSL-5P	9	228	0.062	1.6	5/8
3840-300-5/8-DSL-5P	12	300	0.062	1.6	5/8
3840-228-10-DSL-5P	9	228	0.062	1.6	10/14

Industrial Package, 10 Per Pack

3840-150-5/8-DSL-10P	6	150	0.062	1.6	5/8
3840-228-5/8-DSL-10P	9	228	0.062	1.6	5/8
3840-300-5/8-DSL-10P	12	300	0.062	1.6	5/8
3840-228-10-DSL-10P	9	228	0.062	1.6	10/14

- Extra heavy-duty bi-metal blade with coarse teeth for building and demolition work
- Blade thickness is increased 0.062" (1.6 mm) for greater strength – making this blade ideal for cutting any building material – even heavy wood with large-dimension nails.
- Designed for use by emergency services.

