


F
E
D
C
B
A

10	9	8	7	6	5	4	3	2	1
FINISHED LENGTH (SEE TABLE)									
									
CONNECTOR SPECIFICATION:									
VOLTAGE RATING		250 VAC/VDC							
AMPERAGE RATING		max. 4 AMPS							
PROTECTION		IP67							
OPERATING TEMPERATURE		-20°C TO 80°C							
ITEM	COMPONENT	MATERIAL	FINISH						
7	LABLE	MYLAR	BLACK/YELLOW						
6	O-RING	VITON	RED						
5	COUPLER	BRASS	NICKEL PLATED						
4	PIN CONTACT	COPPER ALLOY	GOLD OVER NICKEL						
3	INSERT	PUR	BLACK						
2	OVERMOLD	POLYURETHANE (PUR)	YELLOW						
1	CABLE- 22/3-5 (COPPER STRANDING) 3/4/5 CONDUCT. 300V	JACKET: PUR	BLACK						

DESCRIPTION EC NO: WEU2010-0284 DRWN: LSTEMMLE 2010/01/20 CHKD: NS APPR: NSTAUDIG 2010/01/26	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
			 = 0  = 0		mm	INCH	DRAWN BY	DATE	MICRO-CHANGE CORDSET 3/4/5-POL FE 90 SE 22/3-5 BLACK PUR CABLE	
		4 PLACES		±---	±---	----	----			
		3 PLACES		±---		CHECKED BY	DATE			
		2 PLACES		±---	±.01	RE	2010/01/21			
		1 PLACE		±0.3	±---	APPROVED BY	DATE			
		ANGULAR ± --- °			NSTAUDIG 2010/01/25			MOLEX INCORPORATED		
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO.			DOCUMENT NO.	SHEET NO.	
					SEE TABLE SHEET 2			SD-120065-043		1 OF 1
					SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

F
E
D
C
B
A

F

E

D

C

B

A

F

E

D

C

B

A

POL	MATERIAL NUMBER	ENGINEERING NUMBER	FINISHED LENGTH
3	1200060011	803001P03M020	6.56' +3.5" -0 [2.0M +89 -0]

POL	MATERIAL NUMBER	ENGINEERING NUMBER	FINISHED LENGTH
4	1200060024	804001P03M020	6.56' +3.5" -0 [2.0M +89 -0]
4	1200652147	804001P03M040	13.12' +6.5" -0 [4.0M +165 -0]
4	1200060025	804001P03M050	16.40' +6.5" -0 [5.0M +165 -0]
4	1200658206	804001P03M060	19.69' +6.5" -0 [6.0M +165 -0]
4	1200651787	804001P03M100	32.81' +12.5" -0 [10.0M +318 -0]

POL	MATERIAL NUMBER	ENGINEERING NUMBER	FINISHED LENGTH
5	1200060663	805001P03M020	6.56' +3.5" -0 [2.0M +89 -0]
5	1200658184	805001P03M040	13.12' +6.5" -0 [4.0M +165 -0]
5	1200651793	805001P03M050	16.40' +6.5" -0 [5.0M +165 -0]
5	1200652156	805001P03M060	19.69' +6.5" -0 [6.0M +165 -0]
5	1200060664	805001P03M100	32.81' +12.5" -0 [10.0M +318 -0]

DESCRIPTION EC NO: WEU2010-0284 DRWN: LSTEMMLE 2010/01/20 CHKD: NS APPR: NSTAUDIG 2010/01/26	DESCRIPTION REV	QUALITY SYMBOLS ▽ = 0 ▽C = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
				mm	INCH	DRAWN BY		DATE		MICRO-CHANGE CORDSET 3/4/5-POL FE 90 SE 22/3-5 BLACK PUR CABLE
			4 PLACES	±---	±---	----		----		
			3 PLACES	±---	±---	CHECKED BY		DATE		
			2 PLACES	±---	±.01	RE		2010/01/21		
			1 PLACE	±0.3	±---	APPROVED BY		DATE		
			ANGULAR ± --- °			NSTAUDIG		2010/01/25		MOLEX INCORPORATED
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO.		DOCUMENT NO.		SHEET NO.
						SEE TABLE		SD-120065-043		1 OF 1
						SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			