

Willsher and Quick Ltd

HIGH TECHNOLOGY ENCLOSURE SOLUTIONS

RS COMPONENTS TECHNICAL DATA SHEET

PART No – A2766RS

OVERVIEW

27U High x 600 Wide x 675 Deep Access Rack Complete With

- Part Ventilated Glass Front Door – Steel Rear Door
- 4 x 19" Mounts – Set of Side Panels

STRUCTURE

Designed for loads up to 750kg and tested to 900kg* when supported equally on the vertical panel mounts.

View Of 42U x 800
Wide x 875 Deep
Racks with Plinths



FRAMEWORK

The rack has a top and bottom tubular frame, which is clad with sheet steel fascias and connected by two vertical aluminium extrusions. (UK and World-wide Patents Pending)

FRAME MATERIALS

Tubular Frame	25 x 25 x 2.5 Wall Thickness Mild Steel Tube with 2.0mm Welded plates
Fascias	1.2mm CR4 Mild Steel Zinc-coated to 2.5 Microns
19" Panel Mounts	2.0mm CR4 Mild Steel
Centre Verticals	Aluminium Extrusion (2.97kg Per Metre Density)
Corner Trims	25% Glass filled Nylon 6 – Self colour

PANEL MATERIALS

Side and Top Panels	1.2mm CR4 Mild Steel
Front Door Metalwork	1.5mm CR4 Mild Steel
Front Door Glass	4.0mm Thick Toughened Grey Tinted Glass to BS6206 1981
Rear Door	1.5mm CR4 Mild Steel
Hinge Mouldings	25% Glass filled Nylon 6 – Self colour

19" PANEL MOUNTS


Conforming to IEC 297 standard with mounting facilities for universal front fixing and WQ side mounting accessories.

FIXINGS AND HARDWARE

Main fixings	M6 Socket Set Screws – 10.9 Tensile Strength
Extrusion fixings	M6 Hex Head Screws – 8.8 Tensile Strength
Hinge fixings	M5 Socket Head Screws – 8.8 Tensile Strength

* Written Details On Request

Willsher & Quick Limited – Walrow Industrial Estate – Highbridge – Somerset – TA9 4AQ
Tel +44 (0) 1278 783371 Fax +44 (0) 1278 789037 E-Mail sales@wql.co.uk Web www.wql.co.uk



Willsher and Quick Ltd

HIGH TECHNOLOGY ENCLOSURE SOLUTIONS

RS COMPONENTS TECHNICAL DATA SHEET

PART No – A2766RS

IP RATING – IEC 529

IP20

SECURITY

Each door has a central, pull out and turn locking handle with two point locking. Doors are LH Hinged as standard but can be supplied or converted to RH Hinged.

Side panels are internally released using spring loaded pin mechanisms.

SECURITY MATERIALS

Handle	Nylon 66 – Self Colour
Lock Rod Guides	Nylon 6 - Natural
Locking Rods	Mild Steel Bar – 8mm Dia.

ACCESSORIES

Specific to Rack – Top Fan Trays, QRSV Shelving

Universal – All front mounting accessories using the front 19" panel mounts

FINISH

Corner Mouldings, Door Hinge Mouldings, Door Lock Assembly

Natural Colour System NCS-4550-R90B Blue (VDI 22 Texture)

Vertical Extrusions

Mixed Metal Iron Phosphate Pre-treatment Brent Pyrene 269

Natural Colour System NCS-4550-R90B Blue Structured Epoxy Polyester Powder DFT 50 Microns

Fascias, Top Panels, Side Panels and Doors

Mixed Metal Iron Phosphate Pre-treatment Brent Pyrene 269

Natural Colour System NCS-1502-Y Light Grey Structured Epoxy Polyester Powder DFT 50 Microns

Panel Mounts, Top Panel Fixing Channels, Lock Rods and Fixing Screws

Zinc and yellow passivate to BS 1706 1990 Fe/zn5c2c

OVERALL DIMENSIONS

1344 High x 600 Wide x 675 Deep