

LC1F2654MD

TeSys F contactor - 4P (4 NO) - AC-1 - ≤ 440 V
350 A - coil 220 V DC



Main

Range	TeSys
Product name	TeSys F
Product or component type	Contacteur
Device short name	LC1F
Contacteur application	Resistive load
Utilisation category	AC-1
Poles description	4P
Pole contact composition	4 NO
[Ue] rated operational voltage	≤ 1000 V AC 50/60 Hz ≤ 460 V DC
[Ie] rated operational current	350 A (≤ 40 °C) at ≤ 440 V AC AC-1
Control circuit type	DC standard
Control circuit voltage	220 V DC
[Uimp] rated impulse withstand voltage	8 kV
Overvoltage category	III
[Ith] conventional free air thermal current	350 A at ≤ 40 °C
Irms rated making capacity	2650 A AC conforming to IEC 60947-4-1
Rated breaking capacity	2120 kA conforming to IEC 60947-4-1
[Icw] rated short-time withstand current	2200 A ≤ 40 °C 10 s 1230 A ≤ 40 °C 30 s 950 A ≤ 40 °C 1 min 620 A ≤ 40 °C 3 min 480 A ≤ 40 °C 10 min
Associated fuse rating	315 A aM at ≤ 440 V 400 A gG at ≤ 440 V
Average impedance	0.3 mOhm at 50 Hz - Ith 350 A
[Ui] rated insulation voltage	1000 V conforming to IEC 60947-4-1 1500 V conforming to VDE 0110 group C
Power dissipation per pole	37 W AC-1
Mounting support	Plate
Standards	EN 60947-1 EN 60947-4-1 IEC 60947-1 IEC 60947-4-1 JEM 1038
Product certifications	BV CCC CSA DNV GL RINA RMRoS UL LROS
Connections - terminals	Control circuit : screw clamp terminals 2 cable(s) 1...2.5 mm ² - cable stiffness: flexible - with cable end Power circuit : connector 1 cable(s) 240 mm ² Control circuit : screw clamp terminals 1 cable(s) 1...4 mm ² - cable stiffness: flexible - without cable end Control circuit : screw clamp terminals 2 cable(s) 1...4 mm ² - cable stiffness: flexible - without cable

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

end
 Control circuit : screw clamp terminals 1 cable(s)
 1...4 mm² - cable stiffness: flexible - with cable end
 Control circuit : screw clamp terminals 1 cable(s)
 1...4 mm² - cable stiffness: solid - without cable
 end
 Control circuit : screw clamp terminals 2 cable(s)
 1...4 mm² - cable stiffness: solid - without cable
 end
 Power circuit : lugs-ring terminals 1 cable(s) 240
 mm²
 Power circuit : bar 2 x (32 x 4 mm)

Tightening torque	Power circuit : 35 N.m Control circuit : 1.2 N.m
Operating time	40...50 ms closing 40...65 ms opening
Mechanical durability	10 Mcycles
Operating rate	2400 cyc/h at <= 55 °C

Complementary

Control circuit voltage limits	0.85...1.1 Uc at 55 °C operational 0.15...0.2 Uc at 55 °C drop-out
Inrush power in W	750 W at 20 °C
Hold-in power consumption in W	5 W at 20 °C
Heat dissipation	5 W

Environment

IP degree of protection	IP20 front face with shrouds (ordered separately) conforming to IEC 60529 IP20 front face with shrouds (ordered separately) conforming to VDE 0106
Protective treatment	TH
Ambient air temperature for operation	-5...55 °C
Ambient air temperature for storage	-60...80 °C
Permissible ambient air temperature around the device	-40...70 °C
Operating altitude	3000 m without derating in temperature
Mechanical robustness	Vibrations contactor open 2 Gn, 5...300 Hz Shocks contactor closed 15 Gn for 11 ms Shocks contactor open 6 Gn for 11 ms Vibrations contactor closed 5 Gn, 5...300 Hz
Height	203 mm
Width	244.5 mm
Depth	213 mm
Product weight	8.54 kg

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 0852 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available