

General Information

Extended Product Type:	416BSFV6
Product ID:	2CMA168169R1000
EAN:	7392696681698
Catalog Description:	Phase sequence changer surface inlet, 6h, 16A, IP44, 3P+N+E
Long Description:	Phase sequence changer surface inlet, 6h, 16A, IP44, 3P+N+E

Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Phase Sequence Products

Ordering

EAN:	7392696681698
Minimum Order Quantity:	1 piece
Country of Origin:	Czech Republic (CZ)

Dimensions

Product Net Width:	79 mm
Product Net Height:	81 mm
Product Net Length:	125 mm
Product Net Depth:	81 mm
Product Net Weight:	0.19 kg

Container Information

Package Level 1 Gross Weight:	0.19 kg
Package Level 1 EAN:	7392696681698
Package Level 1 Units:	1 piece

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001
Environmental Information:	2CMC700001D0002
RoHS Information:	2CMC700057D0001

Additional Information

Degree of Protection:	IP44
Enclosure Material:	Thermoplastic
Frequency (f):	50 Hz 60 Hz
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	IND. P&S#416BSFV6
Number of Poles:	5
Object Classification Code:	2CMT005069
Product Main Type:	BSFV
Product Name:	Industrial Plugs and Sockets
Rated Current (I _n):	16 A
Rated Voltage (U _r):	346 ... 415 V
RoHS Date:	L23
Standards:	IEC 60 309-2
Suitable For:	416BSFV6
Suitable for Product Class:	Industrial Plugs and Sockets

Classifications

E-nummer:	2416003
UNSPSC:	39120000

