

Terminal block 5.08mm

MB362-508M

□□ : Poles  
**508 : Pitch 5.08mm**  
**362 : Standard**  
**MB : Type**

**PCB Layout**

Pitch : 5.08mm (0.200inch)					
Poles	A(mm)	A(inch)	Poles	A(mm)	A(inch)
4	12.70	0.500	30	78.74	3.100
6	17.78	0.700	32	83.82	3.300
8	22.86	0.900	34	88.90	3.500
10	27.94	1.100	36	93.98	3.700
12	33.02	1.300	38	99.06	3.900
14	38.10	1.500	40	104.14	4.100
16	43.18	1.700	42	109.22	4.300
18	48.26	1.900	44	114.30	4.500
20	53.34	2.100	46	119.38	4.700
22	58.42	2.300	48	124.46	4.900
24	63.50	2.500	50	129.54	5.100
26	68.58	2.700			
28	73.66	2.900			

Current rating : 16Amp AC300V  
 Insulation withstands volt : AC2000V min  
 Insulation resistance : >2000MΩ DC500V  
 Operation temperature : -40°C to +105°C  
 Wire strip length : 4mm~5mm  
 Wire range : 12~26 AWG  
 Screw torque : 5.0 lb-inch

文件管制

MAY 09, 2012

文管中心

CONFIRMED & ACCEPTED BY \_\_\_\_\_

	Material	Plating/Finish	Remark
1	Insulating body Polyamide 66(UL94V-0)		Green
2	Cage clamp Brass	Tin plated	
3	Terminal Brass	Tin plated	
4	Screw Steel	Zinc plated	

PART NO.	MB362-508Mxx
SHEET OF	2/2

VERSION	F
DATE	2012/05/09

CONFIRMED BY	<i>Wenderson</i>
GENERAL MANAGER	<i>J. L. K.</i>

單據編號 : QR-0703-08 版次 : A版

