

## Product Datasheet

# 10" 7pcs Quick Release Ratchet Kit

**Specifications:**

**Patented quick change die set for easy installation.  
No tools required for interchange die set.  
Crimper is easily operated by either  
left or right hand user.**

**Dimensions:**

- 1. Insulated terminal:**  
AWG 22-18/16-14/12-10.  
ø 0.5-1.0/1.5-2.5/4.0-6.0mm<sup>2</sup>.
- 2. Non-Insulated terminal:**  
AWG 20-18/16-14/12-10/8.  
ø 1.5/2.5/6.0/10 mm<sup>2</sup>.
- 3. Open insulated terminal:**  
AWG 20-18/16-14/12-10.  
ø 0.5-1.0/1.5-2.5/4.0-6.0 mm<sup>2</sup>.
- 4. Open barrel terminal:**  
AWG 22-18/24-22/26-24.  
ø 0.1-0.25/0.25-0.5/0.5-1.0 mm<sup>2</sup>.
- 5. Open barrel terminal & D-Sub, V3.2:**  
AWG 12/22/8-6.  
ø 2.5/0.5/730-10 mm<sup>2</sup>.
- 6. Spark plug connector:**  
AWG 17  
ø 1 mm<sup>2</sup>.

**RoHS**

**Operating Instructions:**

