

## Relay connectors - ST-REL3-HG110/21 - 2821038

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Relay connector, equipped with Hengstler miniature round relay, contacts (AgCdO+Au): small to large loads, 1 PDT, input voltage 110 V DC, with light indicator, can be plugged on basic termination blocks

The illustration shows version ST-REL3-HG 24/21



### Key commercial data

Packing unit	10 pc
GTIN	 4 017918 076955
Weight per Piece (excluding packing)	61.0 g
Custom tariff number	85364900
Country of origin	Germany

### Technical data

#### Dimensions

Width	20.8 mm
Height	33 mm
Depth	66.5 mm

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

#### Coil side

Nominal input voltage $U_N$	110 V DC
Input voltage range in reference to $U_N$	0.8 ... 1.1
Nominal input current at $U_{IN}$	5.5 mA
Typical response time	15 ms
Typical release time	25 ms
Operating voltage display	Yes
Protective circuit	Damping diode, polarity protection Damping diode, polarity protection diode

## Relay connectors - ST-REL3-HG110/21 - 2821038

### Technical data

#### Contact side

Contact type	Single contact, 1-PDT
Contact material	AgCdO, hard gold-plated
Maximum switching voltage	250 V AC/DC
Maximum inrush current	6 A
Limiting continuous current	6 A
Interrupting rating (ohmic load) max.	120 W (at 24 V DC)
	180 W (at 48 V DC)
	105 W (at 60 V DC)
	60 W (at 110 V DC)
	90 W (at 220 V DC)
	1500 VA (for 250 V AC)

#### General

Test voltage relay winding/relay contact	2 kV AC (50 Hz, 1 min.)
Operating mode	100% operating factor
Mechanical service life	Approx. 10 <sup>7</sup> cycles
Standards/regulations	DIN VDE 0110b, Gr. C for 250 V DC
	DIN VDE 0160 (in relevant parts)

### Classifications

#### eCl@ss

eCl@ss 4.0	27371104
eCl@ss 4.1	27371104
eCl@ss 5.0	27371001
eCl@ss 5.1	27371001
eCl@ss 6.0	27371001
eCl@ss 7.0	27371001
eCl@ss 8.0	27371001

#### ETIM

ETIM 2.0	EC000196
ETIM 3.0	EC000196
ETIM 4.0	EC000196
ETIM 5.0	EC000196

#### UNSPSC

UNSPSC 6.01	30211916
UNSPSC 7.0901	39121515
UNSPSC 11	39121515
UNSPSC 12.01	39121515

# Relay connectors - ST-REL3-HG110/21 - 2821038

## Classifications

### UNSPSC

UNSPSC 13.2	39121515
-------------	----------

## Approvals

### Approvals

---

### Approvals

GOST / GOST

---



Ex Approvals

---

Approvals submitted

---

## Approval details



## Accessories

### Additional products

Basic terminal block - URELG 3-PMTK - 2820709



Basic termination blocks with test connection on both sides and knife disconnection for NS 32 and NS 35/7.5 DIN rail, with end cover, for ST-REL..., ST-OV... and ST-OE... plugs, 3-pos.

Basic terminal block - UDK-RELG 3 - 2777043



Basic termination blocks with test connection on both sides and double connections with the same potential for NS 32 and NS 35/7.5 DIN rail, with end cover, for ST-REL..., ST-OV... and ST-OE... plugs, 3-pos.

## Relay connectors - ST-REL3-HG110/21 - 2821038

### Accessories

---

#### Basic terminal block - URELG 3 - 2820136



Basic termination blocks with screw connection for NS 32 and NS 35/7.5 DIN rail, with end cover, for ST-REL..., ST-OV... and ST-OE... plugs, 3-pos.

---

#### Basic terminal block - ZFK-RELG 3 - 2829917



Basic termination blocks with spring-cage connection for NS 35/7.5 DIN rail, with end cover, for ST-REL..., ST-OV... and ST-OE... plugs, 3-pos.

---

### Drawings

## Relay connectors - ST-REL3-HG110/21 - 2821038

Circuit diagram

