




INSULATION SERRATIONS

1

4.34 ±0.08 DIA

[.171 ±.003]

FOR #8 STUD

8.71

[.343]

BODY

7.14 MIN

[.281]

"D" MAX

"E" MAX

1

2

3

4

STAMP AMP 16-14* APPROX AS SHOWN

TONGUE MATERIAL THK: 0.79 ±0.05 [.031 ±.002]

SUPERSEDED BY 8-34160-1

MATERIAL: BODY - CU PER ASTM B152

SLEEVE - PVC, COLOR - BLUE

22.12 [.871]	17.70 [.697]	3.00-4.90 [.118-.193]	50	LOOSE PC, BAG	3 8-34160-5
			5	LOOSE PC, BLS	8-34160-4
			100	LOOSE PC, BOX	8-34160-1
23.37 [.920]	18.95 [.746]	3.81-.635 [.150-.250]	5000	ON TAPE, REEL	2-34160-3
			-	LOOSE PIECE	2-34160-2
22.12 [.871]	17.70 [.697]	3.00-4.90 [.118-.193]	5000	ON TAPE, REEL	2-34160-1
			-	LOOSE PIECE	34160
"E"	"D"	WIRE INSULATION DIA	QTY	PACKAGE TYPE	PART NUMBER

AMP INCORPORATED

CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER

1-800-522-6752

FOR APPLICATION TOOLING INFORMATION

TOOLING ASSISTANCE CENTER

1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

MAX RECOMMENDED OPERATING TEMPERATURE:

105°C [221° F]

VOLTAGE RATING:

N/A

CIRCULAR MIL AREA:

1.04-2.62mm² [2,050-5,180]

SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

MM [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± 0.20[.008]

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH

TIN PER ASTM B545

DWN

DK SCHRUM

02/08/93

CHK

RE HERSEY

8/15/93

APVD

M BARNABA

8/15/93

PRODUCT SPEC

UL 486A

APPLICATION SPEC

NOT AVAILABLE

WEIGHT

-

CUSTOMER DRAWING

STE

TE Connectivity

NAME

TERMINAL, RING TONGUE, PLASTI-GRIP, WIRE SIZE, 16-14 AWG

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-34160

-

SCALE

4:1

SHEET

1 OF 1

REV

R1

1470-19 (3/11)