


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
CM	0		P	REVISED PER ECO-11-005027	11MAR11	RK

D

C


B

A



1. PARTS MUST COMPLY WITH AMP SOLDERABILITY SPECIFICATION 109-11-3.

△ CONTACT IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN 0.00076 [.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN ON SOLDERTAIL END.



RECOMMENDED P.C. BOARD LAYOUT
FOR 1.57 [.062] THICK P.C. BOARD
SCALE 10:1

PHOS BRZ, TIN PLATED	NYLON,UL94V-2	1586515-3
△	NYLON,UL94V-2	1586515-2
PIN CONTACT MATERIAL & FINISH	HOUSING MATERIAL & COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	7/28/05	TE Connectivity		
		CHK	7/28/05			
DIMENSIONS: mm [INCHES]		APVD	7/28/05	NAME HEADER ASSEMBLY, 4 CIRCUIT, COMMERCIAL MATE-N-LOK(TM)		
		PRODUCT SPEC				
		APPLICATION SPEC		SIZE A2		
MATERIAL SEE TABLE		WEIGHT	-	CAGE CODE 00779		DRAWING NO C=1586515
		FINISH	SEE TABLE			
CUSTOMER DRAWING				SCALE	5:1	SHEET
				1 OF 1		REV
						P