

## D6/8.ADO

ABB contact for United  
States of America



### General Information

---

<b>Extended Product Type:</b>	D6/8.ADO
<b>Product ID:</b>	1SNA199042R2500
<b>EAN:</b>	3472591990423
<b>Catalog Description:</b>	D6/8.ADO IDC Terminal Blocks - Feed-through ADO - screw clamp - Grey
<b>Long Description:</b>	D6/8.ADO IDC Terminal Blocks - Feed-through - Grey, 2.5mm <sup>2</sup> RatedCrossSection, 8mm Spacing TH 35-7.5, TH 35-15 Rail

---

### Categories

---

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » IDC Terminal Blocks

---

### Ordering

---

<b>EAN:</b>	3472591990423
<b>Minimum Order Quantity:</b>	50 piece
<b>Customs Tariff Number:</b>	85369010

---

### Dimensions

---

<b>Product Net Width:</b>	8.0 mm
<b>Product Net Height:</b>	45.0 mm
<b>Product Net Depth:</b>	41.0 mm
<b>Product Net Weight:</b>	11.00 g

---

### Container Information

---

<b>Package Level 1 Units:</b>	50 piece
<b>Package Level 1 Width:</b>	81 mm
<b>Package Level 1 Height:</b>	47 mm
<b>Package Level 1 Length:</b>	220 mm
<b>Package Level 1 Gross Weight:</b>	0.55000 kg
<b>Package Level 1 EAN:</b>	3472591990423
<b>Package Level 2 Units:</b>	750 piece
<b>Package Level 2 Width:</b>	300 mm
<b>Package Level 2 Height:</b>	150 mm
<b>Package Level 2 Length:</b>	500 mm
<b>Package Level 2 Gross Weight:</b>	8.6 kg
<b>Package Level 3 Units:</b>	36000 piece
<b>Product Packing Type:</b>	Box

---

### Environmental

---

<b>Ambient Air Temperature:</b>	Operation -55 ... +110 °C Storage -55 ... +110 °C
<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment

---

### Technical UL/CSA

---

<b>Maximum Operating Voltage UL/CSA:</b>	Main Circuit 600 V
<b>Connecting Capacity-Main Circuit UL/CSA:</b>	Screw Clamp / Flexible 1x 22 ... 8 AWG Screw Clamp / Flexible 2x 22 ... 12 AWG Screw Clamp / Rigid 1x 22 ... 8 AWG

Screw Clamp / Rigid 2x 22 ... 12 AWG

Flammability According to UL94:

V0

**Additional Information**

<b>Ambient Temperature:</b>	-5 ... +40 °C
<b>Color:</b>	Grey
<b>Connecting Capacity-Main Circuit:</b>	Screw Clamp / Flexible 1x 0.22 ... 6 mm <sup>2</sup> Screw Clamp / Rigid 1x 0.2 ... 10 mm <sup>2</sup>
<b>Connection Type:</b>	Screw clamp - ADO System
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
<b>Dielectric Test Voltage:</b>	3500 V
<b>Function:</b>	Feed-through
<b>Gauge Type:</b>	A5
<b>Gauge(s) of Form:</b>	A5
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Insulation Material:</b>	Polyamide
<b>Mounting on DIN Rail:</b>	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
<b>Number of Levels:</b>	1
<b>Pollution Degree:</b>	3
<b>Product Main Type:</b>	D6/8.ADO
<b>Product Name:</b>	Terminal block
<b>Rated Cross-Section:</b>	2.5 mm <sup>2</sup>
<b>Rated Current (I<sub>n</sub>):</b>	Main Circuit 24 A
<b>Rated Impulse Withstand Voltage (U<sub>imp</sub>):</b>	8000 V
<b>Rated Short-time Withstand Current (I<sub>cw</sub>):</b>	for 1.0s 300 A
<b>Rated Voltage (U<sub>r</sub>):</b>	1000 V
<b>Recommended Screw Driver:</b>	4.5 mm
<b>Spacing:</b>	8 mm
<b>Sub-Function:</b>	2 connections
<b>Wire Stripping Length:</b>	12.0 mm

**Certificates and Declarations (Document Number)**

<b>BV Certificate:</b>	1SND163013A0200
<b>CB Certificate:</b>	1SND163010A0200
<b>cUL Certificate:</b>	1SND163005A0200
<b>Declaration of Conformity - CE:</b>	1SND225010C1007
<b>GOST Certificate:</b>	1SND161005A1104
<b>RoHS Information:</b>	1SND230472F0201

**Classifications**

<b>E-number:</b>	2925812
<b>ETIM 4.0:</b>	EC000897 - Feed-through terminal block
<b>ETIM 5.0:</b>	EC000897 - Feed-through terminal block
<b>Object Classification Code:</b>	X



