

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

NOTES:

1 PACK IN ACCORDANCE WITH AMP SPEC 107-3275

2 100 TRAY PACK IN ACCORDANCE
WITH AMP SPEC 107-3275

3 Au PLATING

4 Ni PLATING

5. ELECTRICAL CHARECTERISTICS

FREQUENCY RANGE: DC-4GHz

NOMINAL IMPEDANCE 50 Ohm

INSULATION RESISTANCE: 5000 MOhm

WORKING VOLTAGE: 500 Volts RMS at Sea Level

DIELECTRIC WITHSTAND VOLTAGE: 1500 Volts RMS Max

CONTACT RESISTANCE

CENTRE CONTACT: 1.50 mOhm MAX

OUTER CONTACT: 0.20 mOhm MAX

VSWR @ xGHz: N/A

INSERTION LOSS xdb N/A

6. MECHANICAL CHARECTERISTICS

COUPLING RETENTION FORCE: N/A


CABLE RETENTION FORCE: N/A

MOUNT NUT RECOMMENDED TORQUE: 2N


DURABILITY: 500 CYCLES MIN

7. ENVIRONMENTAL CHARECTERISTICS

OPERATING TEMPERATURE: -65 to +85°C



RECOMMENDED MOUNTING HOLE



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
B	E		D	ECR-09-007005	29/04/09	MJG	JA

1	1	4	BRASS	HEX NUT	7
1	1	4	STEEL	WASHER	6
1	1		ABS	INSULATION	5
1	1	4	BRASS	SLEEVE	4
2	2		PTFE	DIELECTRIC	3
1	1	3	BRASS	CONTACT	2
1	1	4	BRASS	BODY	1
6--0	1--0	FINISH	MATERIAL	DESCRIPTION	ITEM
2	1				
QTY/ASSY			PARTS LIST		

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN J. SANDWELL 13/12/05	Tyco Electronics UK Ltd. Bideford, North Devon, EX39 4HE		
DIMENSIONS: mm		CHK S. PARLOW 13/12/05			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD F. WHEELER-KING 13/12/05	NAME BNC INSULATED BULKHEAD ADAPTOR J - J 50 OHM		
0 PLC ±0.5 1 PLC ±0.5 2 PLC ±0.5 3 PLC ±0.5 4 PLC ±0.5 ANGLES ±0.5 FINISH -		PRODUCT SPEC -	SIZE A300779		
MATERIAL SEE TABLE		APPLICATION SPEC -	DRAWING NO C-1337454		
		WEIGHT -	RESTRICTED TO -		
		CUSTOMER DRAWING	SCALE NTS		
			SHEET 1 OF 1		
			REV D		