

Test plugs - PS-UK 2,5 B/Z-6 - 3001239

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Test plugs, Color: red

Why buy this product

- The test plug reliably makes contact in the bridge shaft and in all test sockets with a 2.3 mm or 4 mm diameter
- Individual test adapters can be combined using the modular PS-...2,3MM test plug.



Key commercial data

Packing unit	1 pc
GTIN	 4 017918 089856
Weight per Piece (excluding packing)	51.8 g
Custom tariff number	85366990
Country of origin	Poland
Note	Made to Order (non-returnable)

Technical data

Length	19.6 mm
Width	5 mm

General

Color	red
Material	PA
Minimum temperature	-40 °C
Maximum temperature	115 °C

Classifications

eCl@ss

eCl@ss 4.0	27141127
------------	----------

Test plugs - PS-UK 2,5 B/Z-6 - 3001239

Classifications

eCl@ss

eCl@ss 4.1	27141127
eCl@ss 5.0	27141127
eCl@ss 5.1	27141111
eCl@ss 6.0	27141148
eCl@ss 7.0	27141148

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC002255
ETIM 5.0	EC002555

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC

Drawings

Test plugs - PS-UK 2,5 B/Z-6 - 3001239

Dimensioned drawing

