

THIS DRAWING IS UNPUBLISHED.
DIFFUSION RESTREINTE

RELEASED FOR PUBLICATION
LIBRE A LA DIFFUSION

20

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.
TOUS DROITS RESERVES

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION
MODIFICATIONS

DATE

DWN
DESS.

APVD
APP.

F

7

H

CLARIFIE NOTE 3

12MAR2004

J.D

Y.P

J

MATERIAL

09MAY2006

J.D

Y.P

K

NOTES 5, 6 ADDED

30SEP2008

GM

PEG

HE1402
XXYYDZ

DATE CODE MARKING
SEE NOTE 6

HEADER TYPE
MARKING
SEE NOTE 5

8.8

0
-0.2

7

0
-0.5

2.6±0.1

2.9 ±0.3

SECTION A - A

PERCAGE CARTE DE C.I.
PCB LAYOUT HOLES

2.54 typ.

Ø1

+0.1
-0.05

Ø0.1

SCALE 3:1

SCALE 3:1

45.72

43.18

18

1-281695-8 *

43.18

40.64

17

1-281695-7

38.10

35.56

15

1-281695-5 *

30.48

27.94

12

1-281695-2 *

25.40

22.86

10

1-281695-0 *

20.32

17.78

8

0-281695-8 *

17.78

15.24

7

0-281695-7

15.24

12.70

6

0-281695-6 *

12.70

10.16

5

0-281695-5 *

10.16

7.62

4

0-281695-4 *

7.62

5.08

3

0-281695-3 *

5.08

2.54

2

0-281695-2

C

A

Nb
DE
POS

PART NUMBER

DIMENSIONS

NOTES:

1. CES EMBASES SONT PREVUES POUR ETRE ACCOUPLEES AVEC LES FICHES "HE1402" SIMPLE RANGEE.
(These headers are designed to be mated with "HE1402" connectors single row)

2. LES REFERENCES SUIVIES D'UN * SONT LES VERSIONS NORMALISEES SELON LA NORME CEI 603-8
(The parts numbers followed by * are covered by the international standard IEC 603-8)

3. REVETEMENT DES CONTACTS: ETAIN PUR SUR NICKEL
(Contacts plating: lead free tin over nickel)

4. MATIERE PLASTIQUE: TERMO-PLASTIQUE HAUTE TEMPERATURE, UL-94V0, COULEUR BLEUE
(Plastic material: High temperature thermoplastic, UL-94V0, Blue color
MATIERE DES CONTACTS: BRONZE PHOSPHOREUX
(Contacts material: phosphor bronze)

5. MARQUAGE DU TYPE D'EMBASE (HE1402) A L'ENCRE NOIRE
(header type marking (HE1402) with black ink)

6. MARQUAGE DE LA DATE A L'ENCRE NOIRE :
(date code marking with black ink)

XXYYDZ

JOUR (1 A 7)
day (1 to 7)

"D" POUR L'EQUIPE JOUR et "N" POUR CELLE DE NUIT
1 letter "D" for day & "N" for night team

ANNEE
year

SEMAINE
week

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.
CE PLAN EST UN DOCUMENT CONTROLE PAR AMP INCORPORATED.
IL EST SUSCEPTIBLE D'ETRE REVISE. CONTACTER LE SERVICE
TECHNIQUE D'AMP DE FRANCE POUR OBTENIR LA DERNIERE REVISION.

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
(SUIV NB DE DECIMALES)
0 PLC/DEC: ±
1 PLC/DEC: ±0.3
2 PLC/DEC: ±0.13
3 PLC/DEC: ±0.013
4 PLC/DEC: ±0.001
ANGLES ±9°

FINISH/FINITION
SEE/VOIR
NOTE 3

APVD/APPROVE
Y PETRONIN

PRODUCT SPEC
108-15053

APPLICATION SPEC
SPEC. APPLICATION

WEIGHT
MASSE APPROX. -

CUSTOMER DRAWING

/PLAN CLIENT

UNIQUEMENT
POUR REFERENCE

SCALE
ECHELLE 5:1

SHEET
FEUILLE 1

OF
DE 1

REV
K

DWN/DESSINE
C. COMBEDOUZON

CHK/VERIFIE
T. CORRIOL

APVD/APPROVE
Y PETRONIN

NAME
TITRE
HEADERS HE14,
SINGLE ROW, STRAIGHT

SIZE
FORMAT
A2

CAGE CODE
00779

DRAWING NO
No PLAN
C-281695

RESTRICTED TO
RESERVE A
-

AMP 1471-9 REV 31MAR2000

Pro/ENGINEER DRAWING