

UTS Series

Technical information

Tooling

Standard contacts

Contact size	Part number	Head	Handles	Extraction tools	
#20 1mm	RM/RC 24W3 -	S20RCM	SHANDLES	RX20D44	
	RM/RC 20W3 -				
	RM/RC 18W3 -				
	SM 24W3S-(1) SC 24W3S-(1)	S20SCM20			
	SM 24WL3S-(2) SC 24WL3S-(2)				
	SM/SC 20W3S-(1) SM/SC 20WL3S-(2)				
#16 1.6mm	RM/RC 28M1-	S16RCM20		SHANDLES	RX2025GE1
	RM/RC 24M9-				
	RM/RC 20M13-				
	RM/RC 20M12-				
	RM/RC 16M23-	S16RCM16			
	RM/RC 14M30-	S16RCM14			
	SM/SC 24M1- SM/SC 24ML1-	S16SCM20			
	SM/SC 20M1- SM/SC 20ML1-				
	SM/SC 16M1- SM/SC 16ML1-	S16SCML1			
	SM/SC 14M1- SM/SC 14ML1-				
	SM/SC 16M11- SM/SC 16ML11-	S16SCML11			

(1) contact reeled (2) loose contact

Note: endurance of SHANDLES tool = 5,000 cycles.

Contact size	Part number	Tool with separate locator			Extraction tools
		Hand tool	Positioner + locator setting		
#8 3.6mm	8291 3601A / 8291 3600A	M317	VGE10078A	3	51060210936
	8291 3603A / 8291 3602A			3	
	8291 3605A / 8291 3604A			4	
	8291 3607A / 8291 3606A			5	
	8291 3609A / 8291 3608A			6/7	

Specific contacts

Contact size	Part number	Hand tools (SHANDLES) head	Tool with separate locator			Extraction tools	
			Hand tool	Positioner + locator setting			
#16 Ø 1.6mm Longer RM contact	RM28M1GE1-	S16RCM20	MH860	MH86186	6/8		
	RM24M9GE1-						
	RM20M13GE1-						
	RM16M23 GE1-	S16RCM16					
	RM14M30 GE1-	S16RCM14					
#16 Ø 1.6mm Shorter RC contact	RC28M1GE7-	S16RCM20	MH860	MH86164G	4/6		
	RC24M9GE7-				5/6		
	RC20M13GE7- RC20M12GE7-				5/7		
	RC16M23GE7-	6/8					
	RC14M50GE7-	S16RCM1450			M317	UH25	3
	RC14M30GE7-	S16RCM14					