

INDUSTRIAL AUTOMATION CONNECTOR SYSTEMS



**CONNECTING TOMORROW'S
TECHNOLOGY, TODAY.**



Woodhead Connectivity

SST[™] ▪ Brad Harrison[®] ▪ mPm[™]

BRAD HARRISON® AND mPm® CONNECTOR SYSTEMS

Brad Harrison® originally started manufacturing moulded connectors in 1946 for the steel, automotive and mining industries. It was acquired by Woodhead Industries Inc. in 1969 after which the Mini-Change® connector was introduced. It's development was as a direct

result of working with the automotive industry to produce a quick disconnect solution to hard wired control devices such as proximity and limit switches, valves and other devices.


Similarly, mPm® a family owned company was founded in 1973, evolved to service the expanding solenoid valve market. They rapidly developed into the market leader for DIN 43650 style connectors, and joined the group in 1998.

The two market leading brands provide a solid foundation of robust and reliable products from a flexible and supportive manufacturer for both end users and OEMs in industrial segments. Our range has been developed to provide the same high quality product and design for other market sectors such as instrumentation, transportation and materials handling to name just a few.

This catalogue has been specifically designed to cover the connector requirements of customers using industrial automation products – solenoid valves, proximity, photoelectric, capacitive, reed, hall effect and limit switches together with our latest offering in Multi-Port Splitter Boxes – but is not the limit of our capability or product range. Shown are some examples of customised solutions designed for specific applications.



1



2



3



4

- 1 Mini-Change® receptacles with integral wiring of Nano-Change® Mini-Change® and mPm® connectors for control functions. This provided a through panel connection system, which provides a water proof (IP67) solution for control systems in harsh operating conditions.
- 2 The Multi-In-Line Splitter is a complete wiring system built into one connector. In this case it has been used to provide a solution for wiring proximity switches and solenoid valves with the choice of either a home run connector or panel mounted receptacle for the control installation.
- 3 The ultimate wiring systems, this is a model of a complete plug and play solution for wiring a complex mixing machine. This comprises a variety of connector types together with a shielded circuit for drive motors.
- 4 Finally, a range of PCB and panel mount multi-pole Mini-Change® receptacles for integration into a control system, where environmental protection is required and a robust design.

In order to choose the correct connectors for your system, it is important to note the various type of connectors available. Below is a short introduction to guide you to the correct part of the catalogue.


Nano-Change® (M8) Multi-Port Systems

The Nano-Change® 3 and 4 pole connectors are not interchangeable, so care has to be taken in selecting the correct product.

Typically, inductive, reed and Hall effect switches and a limited range of photoelectric sensors use 3 pole connectors. Where as many photoelectric switches use the 4 pole connector, in this case pin 2 is typically used for programming the device or as an alarm output.

Using the In-line Splitter, a 4 pole twin I/O unit can be used to connect two devices per port, so doubling the capacity of the system.

- 3 Pole – Single I/O units 5
- 4 Pole – Twin I/O units 6
- M16 Home Run Connectors 7
- M8 to M8 Sensor/Input Jumpers 8
- M12 to M8 Sensor/Input Jumpers 9
- Solenoid Valve to M8 Output Jumpers 10
- M12 to M8 Adapters and Splitters 13
- Solenoid Valve to M8 Adapters 14




Micro-Change® (M12) Multi-Port Systems

The single I/O or 4 wire units, have common power and earth circuits, plus I/O from each port. These are fully compatible with all sensors and solenoids with the additional choice of either PNP or NPN LED indication of power and status.

The twin I/O or 5 wire units allow for two devices (input or output) to be connected per port doubling the capacity of the unit. Using a 4 pole, 4 wire jumper cable with these units completes the connection for switches with programming functions or complementary outputs.

- 4 Wire – Top-Mount – Single I/O Units 16
- 5 Wire – Top-Mount – Twin I/O Units 17
- 4 Wire – Side-Mount – Single I/O Units 18
- M23 Home Run Connectors 19
- Mini-Change® Home Run Connectors 20
- M8 to M12 Sensor Jumpers 21
- M12 to M12 Sensor Jumpers 22
- Solenoid Valve to M12 Output Jumpers 23
- M8 to M12 Adapters and Splitters 26
- Solenoid Valve to M12 Adapters 27




Nano-Change® (M8) 3, 4 and 5 pole connectors

Nano-Change® is available in 3, 4 and 5 pole designs with either a snap fit or M8 threaded coupling nut. Versions with LED indication show power to the device while a separate LED reports the signal status (on or off).

The range is complemented by panel mount receptacles either with PCB or wire tails.

- Moulded Snap Connectors 29
- Moulded Coupler Connectors 30
- Attachable Connectors 31
- Female and Male Receptacles 31




Micro-Change® (M12) 3, 4, 5 and 8 pole connectors

Micro-Change® single key way connectors are available as 3, 4, 5 or 8 pole. The 3, 4 and 5 poles devices are fully interchangeable for maximum flexibility.

Female and male attachable connectors with screw terminals and choice of gland size on the straight versions, plus a range of panel and PCB mount receptacles, complete the range.

- Moulded Connectors 33
- Attachable Connectors 34
- Female and Male Receptacles 35




mPm® DIN 43650 Form A, B and C connectors

The mPm® Din 43650 Form A, B and C connectors provide the option of fully moulded or field attachable versions.

In each case, choice of either connectors with or without indication and suppression circuits are available.


- Moulded Connectors 37
- Attachable Connectors 39
- Part Number Matrixes and Connector Specification 40
- Multi-Port and Cable Specification 41
- Dimensional Information 42




NANO-CHANGE® MULTI-PORT SPLITTER BOX SYSTEMS



- **Compact design fits into small and previously inaccessible spaces helping to minimise overall machine size**
- **Factory built and tested units, cuts the demand on highly skilled workforce and decreases machine built time, whilst eliminating wiring errors**
- **Simplifies control systems, reducing the size of cable trays, trunking and control cabinets by cutting the number of cables and terminals required**
- **Three case styles each providing choice of three mounting positions with twin I/O units providing connections for 100 devices in just over the space of a CD case**



3 pole – Single I/O Multi-Ports



Function	Cable Colour	M16 Connector Pin No	Function	Cable Colour	M16 Connector Pin No	Function	Cable Colour	M16 Connector Pin No
+V	Brown	A&M						
0V	Blue	L&U						
Port 1 P4	White	P	Port 5 P4	Pink	G	Port 9 P4	White/Blue	C
Port 2 P4	Green	J	Port 6 P4	Red	R	Port 10 P4	Brown/Blue	N
Port 3 P4	Yellow	T	Port 7 P4	Black	E			
Port 4 P4	Grey	S	Port 8 P4	Violet	O			









Integral End Cable Entry

4 Port

6 Port

8 Port

10 Port



PUR	5.0	BEY401P-FBP-05	BEY601P-FBP-05	BEY801P-FBP-05	BEYA01P-FBP-05
	10.0	BEY401P-FBP-10	BEY601P-FBP-10	BEY801P-FBP-10	BEYA01P-FBP-10
	20.0	BEY401P-FBP-20	BEY601P-FBP-20	BEY801P-FBP-20	BEYA01P-FBP-20









Integral Top Cable Entry

4 Port

6 Port

8 Port

10 Port



PUR	5.0	BNY401P-FBP-05	BNY601P-FBP-05	BNY801P-FBP-05	BNYA01P-FBP-05
	10.0	BNY401P-FBP-10	BNY601P-FBP-10	BNY801P-FBP-10	BNYA01P-FBP-10
	20.0	BNY401P-FBP-20	BNY601P-FBP-20	BNY801P-FBP-20	BNYA01P-FBP-20









Integral M16 Home Run Connector

4 Port

6 Port

8 Port

10 Port



See top of page 7 for connectors

BNY401P-FBC


BNY601P-FBC

BNY801P-FBC


BNYA01P-FBC

Nano-Change® (M8) Multi-Port Splitter Boxes

4 pole – Twin I/O Multi-Ports



Cable
Length (m)



Function	Cable Colour	M16 Connector Pin No	Function	Cable Colour	M16 Connector Pin No	Function	Cable Colour	M16 Connector Pin No	Function	Cable Colour	M16 Connector Pin No
+V	Brown	A									
0V	Blue	L									
Port 1 P4	White	U	Port 6 P4	Red	N	Port 1 P2	Grey/Pink	P	Port 6 P2	Yellow/Brown	C
Port 2 P4	Green	J	Port 7 P4	Black		Port 2 P2	Red/Blue	S	Port 7 P2	White/Grey	
Port 3 P4	Yellow	M	Port 8 P4	Violet		Port 3 P2	White/Green	T	Port 8 P2	Grey/Brown	
Port 4 P4	Grey	R	Port 9 P4	White/Blue		Port 4 P2	Brown/Green	G	Port 9 P2	White/Pink	
Port 5 P4	Pink	O	Port 10 P4	Brown/Blue		Port 5 P2	White/Yellow	E	Port 10 P2	Pink/Brown	








Integral End Cable Entry

4 Port

6 Port

8 Port

10 Port



PUR	5.0	BEY403P-FBP-05	BEY603P-FBP-05	BEY803P-FBP-05	BEYA03P-FBP-05
	10.0	BEY403P-FBP-10	BEY603P-FBP-10	BEY803P-FBP-10	BEYA03P-FBP-10
	20.0	BEY403P-FBP-20	BEY603P-FBP-20	BEY803P-FBP-20	BEYA03P-FBP-20








Integral Top Cable Entry

4 Port

6 Port

8 Port

10 Port







PUR	5.0	BNY403P-FBP-05	BNY603P-FBP-05	BNY803P-FBP-05	BNYA03P-FBP-05
	10.0	BNY403P-FBP-10	BNY603P-FBP-10	BNY803P-FBP-10	BNYA03P-FBP-10
	20.0	BNY403P-FBP-20	BNY603P-FBP-20	BNY803P-FBP-20	BNYA03P-FBP-20

Integral M16 Home Run Connector

4 Port

6 Port



See bottom of
page 7 for
connectors

BNY403P-FBC

BNY603P-FBC



Female Connector


Cable
Length (m)



Function	M16 Connector Pin No	Cable Colour	Function	M16 Connector Pin No	Cable Colour	Function	M16 Connector Pin No	Cable Colour
+V	A&M	Brown						
0V	L&U	Blue						
Port 1 P4	P	White	Port 5 P4	G	Pink	Port 9 P4	C	White/Blue
Port 2 P4	J	Green	Port 6 P4	R	Red	Port 10 P4	N	Brown/Blue
Port 3 P4	T	Yellow	Port 7 P4	E	Black			
Port 4 P4	S	Grey	Port 8 P4	O	Violet			

Home Run Connectors for Nano-Change® Single I/O Multi-Ports

Female Straight



PUR 5.0
10.0
20.0

BNY401P-FBC
3 Pole/4 Port

L04300P78M050
L04300P78M100
L04300P78M200

BNY601P-FBC
3 Pole/6 Port

L04200P78M050
L04200P78M100
L04200P78M200


BNY801P-FBC
3 Pole/8 Port

L04100P78M050
L04100P78M100
L04100P78M200

BNYA01P-FBC
3 Pole/10 Port

L04A00P78M050
L04A00P78M100
L04A00P78M200

Female 90°



PUR 5.0
10.0
20.0

L04301P78M050
L04301P78M100
L04301P78M200

L04201P78M050
L04201P78M100
L04201P78M200

L04101P78M050
L04101P78M100
L04101P78M200

L04A01P78M050
L04A01P78M100
L04A01P78M200




Function	M16 Connector Pin No	Cable Colour	Function	M16 Connector Pin No	Cable Colour	Function	M16 Connector Pin No	Cable Colour	Function	M16 Connector Pin No	Cable Colour
+V	A	Brown									
0V	L	Blue									
Port 1 P4	U	White	Port 4 P4	R	Grey	Port 1 P2	P	Grey/Pink	Port 4 P2	G	Brown/Green
Port 2 P4	J	Green	Port 5 P4	O	Pink	Port 2 P2	S	Red/Blue	Port 5 P2	E	White/Yellow
Port 3 P4	M	Yellow	Port 6 P4	N	Red	Port 3 P2	T	White/Green	Port 6 P2	C	Yellow/Brown

Female Connector

Cable
Length (m)

Home Run Connector for Nano-Change® Twin I/O Multi-Ports

Female Straight



PUR 5.0
10.0
20.0


BNY403P-FBC
4 Pole/4 Port

L044000P78M050
L044000P78M100
L044000P78M200

BNY603P-FBC
4 Pole/6 Port

L04000P78M050
L04000P78M100
L04000P78M200

Female 90°



PUR 5.0
10.0
20.0

L04401P78M050
L04401P78M100
L04401P78M200

L04001P78M050
L04001P78M100
L04001P78M200

Nano-Change® (M8) Jumper Cables


M8 3 Pole – Single I/O Multi-Port

M8 4 Pole – Twin I/O Multi-Port

Female Connector

Cable

Length (m)



WIRING CONFIGURATION




WIRING CONFIGURATION

Nano-Change® (M8) Straight




Cable	Length (m)	443030E03M006	443032E03M006	443430E03M006	443432E03M006
PVC	0.6	443030E03M006	443032E03M006	443430E03M006	443432E03M006
	1.0	443030E03M010	443032E03M010	443430E03M010	443432E03M010
	2.0	443030E03M020	443032E03M020	443430E03M020	443432E03M020
	3.0	443030E03M030	443032E03M030	443430E03M030	443432E03M030
PUR	0.6	443030P03M006	443032P03M006	443430P03M006	443432P03M006
	1.0	443030P03M010	443032P03M010	443430P03M010	443432P03M010
	2.0	443030P03M020	443032P03M020	443430P03M020	443432P03M020
	3.0	443030P03M030	443032P03M030	443430P03M030	443432P03M030

Nano-Change® (M8) 90°



Cable	Length (m)	443031E03M006	443033E03M006	443431E03M006	443433E03M006
PVC	0.6	443031E03M006	443033E03M006	443431E03M006	443433E03M006
	1.0	443031E03M010	443033E03M010	443431E03M010	443433E03M010
	2.0	443031E03M020	443033E03M020	443431E03M020	443433E03M020
	3.0	443031E03M030	443033E03M030	443431E03M030	443433E03M030
PUR	0.6	443031P03M006	443033P03M006	443431P03M006	443433P03M006
	1.0	443031P03M010	443033P03M010	443431P03M010	443433P03M010
	2.0	443031P03M020	443033P03M020	443431P03M020	443433P03M020
	3.0	443031P03M030	443033P03M030	443431P03M030	443433P03M030

Nano-Change® (M8) 90° PNP LED




Cable	Length (m)	4430P7E03M006	4430P9E03M006	4434P7E03M006	4434P9E03M006
PVC	0.6	4430P7E03M006	4430P9E03M006	4434P7E03M006	4434P9E03M006
	1.0	4430P7E03M010	4430P9E03M010	4434P7E03M010	4434P9E03M010
	2.0	4430P7E03M020	4430P9E03M020	4434P7E03M020	4434P9E03M020
	3.0	4430P7E03M030	4430P9E03M030	4434P7E03M030	4434P9E03M030
PUR	0.6	4430P7P03M006	4430P9P03M006	4434P7P03M006	4434P9P03M006
	1.0	4430P7P03M010	4430P9P03M010	4434P7P03M010	4434P9P03M010
	2.0	4430P7P03M020	4430P9P03M020	4434P7P03M020	4434P9P03M020
	3.0	4430P7P03M030	4430P9P03M030	4434P7P03M030	4434P9P03M030

Nano-Change® (M8) Straight



Cable	Length (m)	444330E03M006	444332E03M006	444030E03M006	444032E03M006
PVC	0.6	444330E03M006	444332E03M006	444030E03M006	444032E03M006
	1.0	444330E03M010	444332E03M010	444030E03M010	444032E03M010
	2.0	444330E03M020	444332E03M020	444030E03M020	444032E03M020
	3.0	444330E03M030	444332E03M030	444030E03M030	444032E03M030
PUR	0.6	444330P03M006	444332P03M006	444030P03M006	444032P03M006
	1.0	444330P03M010	444332P03M010	444030P03M010	444032P03M010
	2.0	444330P03M020	444332P03M020	444030P03M020	444032P03M020
	3.0	444330P03M030	444332P03M030	444030P03M030	444032P03M030

Nano-Change® (M8) 90°



Cable	Length (m)	444331E03M006	444333E03M006	444031E03M006	444033E03M006
PVC	0.6	444331E03M006	444333E03M006	444031E03M006	444033E03M006
	1.0	444331E03M010	444333E03M010	444031E03M010	444033E03M010
	2.0	444331E03M020	444333E03M020	444031E03M020	444033E03M020
	3.0	444331E03M030	444333E03M030	444031E03M030	444033E03M030
PUR	0.6	444331P03M006	444333P03M006	444031P03M006	444033P03M006
	1.0	444331P03M010	444333P03M010	444031P03M010	444033P03M010
	2.0	444331P03M020	444333P03M020	444031P03M020	444033P03M020
	3.0	444331P03M030	444333P03M030	444031P03M030	444033P03M030


M8 3 Pole – Single I/O Multi-Port

M8 4 Pole – Twin I/O Multi-Port

Female Connector

Cable

Length (m)



WIRING CONFIGURATION



WIRING CONFIGURATION


Micro-Change® (M12) Straight



- 1 Brown
- 2 White*
- 3 Blue
- 4 Black

PVC	0.6	843030E03M006	843032E03M006	844030E03M006	844032E03M006
	1.0	843030E03M010	843032E03M010	844030E03M010	844032E03M010
	2.0	843030E03M020	843032E03M020	844030E03M020	844032E03M020
	3.0	843030E03M030	843032E03M030	844030E03M030	844032E03M030
PUR	0.6	843030P03M006	843032P03M006	844030P03M006	844032P03M006
	1.0	843030P03M010	843032P03M010	844030P03M010	844032P03M010
	2.0	843030P03M020	843032P03M020	844030P03M020	844032P03M020
	3.0	843030P03M030	843032P03M030	844030P03M030	844032P03M030

Micro-Change® (M12) 90°



- 1 Brown
- 2 White*
- 3 Blue
- 4 Black

PVC	0.6	843031E03M006	843033E03M006	844031E03M006	844033E03M006
	1.0	843031E03M010	843033E03M010	844031E03M010	844033E03M010
	2.0	843031E03M020	843033E03M020	844031E03M020	844033E03M020
	3.0	843031E03M030	843033E03M030	844031E03M030	844033E03M030
PUR	0.6	843031P03M006	843033P03M006	844031P03M006	844033P03M006
	1.0	843031P03M010	843033P03M010	844031P03M010	844033P03M010
	2.0	843031P03M020	843033P03M020	844031P03M020	844033P03M020
	3.0	843031P03M030	843033P03M030	844031P03M030	844033P03M030

Micro-Change® (M12) PNP LED



- 1 Brown
- 2 White*
- 3 Blue
- 4 Black

PVC	0.6	8430P6E03M006	8430P8E03M006	8440P6E03M006	8440P8E03M006
	1.0	8430P6E03M010	8430P8E03M010	8440P6E03M010	8440P8E03M010
	2.0	8430P6E03M020	8430P8E03M020	8440P6E03M020	8440P8E03M020
	3.0	8430P6E03M030	8430P8E03M030	8440P6E03M030	8440P8E03M030
PUR	0.6	8430P6P03M006	8430P8P03M006	8440P6P03M006	8440P8P03M006
	1.0	8430P6P03M010	8430P8P03M010	8440P6P03M010	8440P8P03M010
	2.0	8430P6P03M020	8430P8P03M020	8440P6P03M020	8440P8P03M020
	3.0	8430P6P03M030	8430P8P03M030	8440P6P03M030	8440P8P03M030

Micro-Change® (M12) 90° PNP LED



- 1 Brown
- 2 White*
- 3 Blue
- 4 Black

PVC	0.6	8430P7E03M006	8430P9E03M006	8440P7E03M006	8440P9E03M006
	1.0	8430P7E03M010	8430P9E03M010	8440P7E03M010	8440P9E03M010
	2.0	8430P7E03M020	8430P9E03M020	8440P7E03M020	8440P9E03M020
	3.0	8430P7E03M030	8430P9E03M030	8440P7E03M030	8440P9E03M030
PUR	0.6	8430P7P03M006	8430P9P03M006	8440P7P03M006	8440P9P03M006
	1.0	8430P7P03M010	8430P9P03M010	8440P7P03M010	8440P9P03M010
	2.0	8430P7P03M020	8430P9P03M020	8440P7P03M020	8440P9P03M020
	3.0	8430P7P03M030	8430P9P03M030	8440P7P03M030	8440P9P03M030

* White not used on single I/O connectors

Options: NPN format LED indication, choice of cables, see page 40 for more information

Nano-Change® (M8) Jumper Cables



M8 3 Pole – Single I/O Multi-Port

M8 4 Pole – Twin I/O Multi-Port

Female Connector

Cable

Length (m)



Form A (18mm) 2 pole + earth



PVC

0.6

1.0

2.0

3.0

PUR

0.6

1.0

2.0

3.0

- 1 Brown
- 2 Blue
- 3 Yellow/Green*

E43000E12M006
E43000E12M010
E43000E12M020
E43000E12M030
E43000P12M006
E43000P12M010
E43000P12M020
E43000P12M030

E43002E12M006
E43002E12M010
E43002E12M020
E43002E12M030
E43002P12M006
E43002P12M010
E43002P12M020
E43002P12M030

E44000E12M006
E44000E12M010
E44000E12M020
E44000E12M030
E44000P12M006
E44000P12M010
E44000P12M020
E44000P12M030

E44002E12M006
E44002E12M010
E44002E12M020
E44002E12M030
E44002P12M006
E44002P12M010
E44002P12M020
E44002P12M030

Form A (18mm) 2 pole + earth – 24 V LED & VDR



PVC

0.6

1.0

2.0

3.0

PUR

0.6

1.0

2.0

3.0

- 1 Brown
- 2 Blue
- 3 Yellow/Green*

E430B0E12M006
E430B0E12M010
E430B0E12M020
E430B0E12M030
E430B0P12M006
E430B0P12M010
E430B0P12M020
E430B0P12M030

E430B2E12M006
E430B2E12M010
E430B2E12M020
E430B2E12M030
E430B2P12M006
E430B2P12M010
E430B2P12M020
E430B2P12M030

E440B0E12M006
E440B0E12M010
E440B0E12M020
E440B0E12M030
E440B0P12M006
E440B0P12M010
E440B0P12M020
E440B0P12M030

E440B2E12M006
E440B2E12M010
E440B2E12M020
E440B2E12M030
E440B2P12M006
E440B2P12M010
E440B2P12M020
E440B2P12M030

Form B Ind (11mm) 2 pole + 12 o'clock earth



PVC

0.6

1.0

2.0

3.0

PUR

0.6

1.0

2.0

3.0

- 1 Brown
- 2 Blue
- 3 Yellow/Green*

F43001E12M006
F43001E12M010
F43001E12M020
F43001E12M030
F43001P12M006
F43001P12M010
F43001P12M020
F43001P12M030

F43003E12M006
F43003E12M010
F43003E12M020
F43003E12M030
F43003P12M006
F43003P12M010
F43003P12M020
F43003P12M030

F44001E12M006
F44001E12M010
F44001E12M020
F44001E12M030
F44001P12M006
F44001P12M010
F44001P12M020
F44001P12M030

F44003E12M006
F44003E12M010
F44003E12M020
F44003E12M030
F44003P12M006
F44003P12M010
F44003P12M020
F44003P12M030

Form B Ind (11mm) 2 pole + 12 o'clock earth – 24 V LED & VDR



PVC

0.6

1.0

2.0

3.0

PUR

0.6

1.0

2.0

3.0

- 1 Brown
- 2 Blue
- 3 Yellow/Green*


F430B1E12M006
F430B1E12M010
F430B1E12M020
F430B1E12M030
F430B1P12M006
F430B1P12M010
F430B1P12M020
F430B1P12M030

F430B3E12M006
F430B3E12M010
F430B3E12M020
F430B3E12M030
F430B3P12M006
F430B3P12M010
F430B3P12M020
F430B3P12M030

F440B1E12M006
F440B1E12M010
F440B1E12M020
F440B1E12M030
F440B1P12M006
F440B1P12M010
F440B1P12M020
F440B1P12M030

F440B3E12M006
F440B3E12M010
F440B3E12M020
F440B3E12M030
F440B3P12M006
F440B3P12M010
F440B3P12M020
F440B3P12M030

* Yellow/Green not connected





Female Connector

Cable



Length (m)

M8 3 Pole – Single I/O Multi-Port

M8 4 Pole – Twin I/O Multi-Port





Form B Ind (11mm) 2 pole + 6 o'clock earth


1 Brown
2 Blue
3 Yellow/Green*



Cable	Length (m)	F43000E12M006	F43002E12M006	F44000E12M006	F44002E12M006
PVC	0.6	F43000E12M006	F43002E12M006	F44000E12M006	F44002E12M006
	1.0	F43000E12M010	F43002E12M010	F44000E12M010	F44002E12M010
	2.0	F43000E12M020	F43002E12M020	F44000E12M020	F44002E12M020
	3.0	F43000E12M030	F43002E12M030	F44000E12M030	F44002E12M030
PUR	0.6	F43000P12M006	F43002P12M006	F44000P12M006	F44002P12M006
	1.0	F43000P12M010	F43002P12M010	F44000P12M010	F44002P12M010
	2.0	F43000P12M020	F43002P12M020	F44000P12M020	F44002P12M020
	3.0	F43000P12M030	F43002P12M030	F44000P12M030	F44002P12M030

Form B Ind (11mm) 2 pole + 6 o'clock earth – 24 V LED & VDR


1 Brown
2 Blue
3 Yellow/Green*



Cable	Length (m)	F430B0E12M006	F430B2E12M006	F440B0E12M006	F440B2E12M006
PVC	0.6	F430B0E12M006	F430B2E12M006	F440B0E12M006	F440B2E12M006
	1.0	F430B0E12M010	F430B2E12M010	F440B0E12M010	F440B2E12M010
	2.0	F430B0E12M020	F430B2E12M020	F440B0E12M020	F440B2E12M020
	3.0	F430B0E12M030	F430B2E12M030	F440B0E12M030	F440B2E12M030
PUR	0.6	F430B0P12M006	F430B2P12M006	F440B0P12M006	F440B2P12M006
	1.0	F430B0P12M010	F430B2P12M010	F440B0P12M010	F440B2P12M010
	2.0	F430B0P12M020	F430B2P12M020	F440B0P12M020	F440B2P12M020
	3.0	F430B0P12M030	F430B2P12M030	F440B0P12M030	F440B2P12M030

Form B DIN (10mm) 2 pole + 12 o'clock earth


1 Brown
2 Blue
3 Yellow/Green*

Cable	Length (m)	D43001E12M006	D43003E12M006	D44001E12M006	D44003E12M006
PVC	0.6	D43001E12M006	D43003E12M006	D44001E12M006	D44003E12M006
	1.0	D43001E12M010	D43003E12M010	D44001E12M010	D44003E12M010
	2.0	D43001E12M020	D43003E12M020	D44001E12M020	D44003E12M020
	3.0	D43001E12M030	D43003E12M030	D44001E12M030	D44003E12M030
PUR	0.6	D43001P12M006	D43003P12M006	D44001P12M006	D44003P12M006
	1.0	D43001P12M010	D43003P12M010	D44001P12M010	D44003P12M010
	2.0	D43001P12M020	D43003P12M020	D44001P12M020	D44003P12M020
	3.0	D43001P12M030	D43003P12M030	D44001P12M030	D44003P12M030

Form B DIN (10mm) 2 pole + 12 o'clock earth – 24 V LED & VDR


1 Brown
2 Blue
3 Yellow/Green*

* Yellow/Green
not connected

Cable	Length (m)	D430B1E12M006	D430B3E12M006	D440B1E12M006	D440B3E12M006
PVC	0.6	D430B1E12M006	D430B3E12M006	D440B1E12M006	D440B3E12M006
	1.0	D430B1E12M010	D430B3E12M010	D440B1E12M010	D440B3E12M010
	2.0	D430B1E12M020	D430B3E12M020	D440B1E12M020	D440B3E12M020
	3.0	D430B1E12M030	D430B3E12M030	D440B1E12M030	D440B3E12M030
PUR	0.6	D430B1P12M006	D430B3P12M006	D440B1P12M006	D440B3P12M006
	1.0	D430B1P12M010	D430B3P12M010	D440B1P12M010	D440B3P12M010
	2.0	D430B1P12M020	D430B3P12M020	D440B1P12M020	D440B3P12M020
	3.0	D430B1P12M030	D430B3P12M030	D440B1P12M030	D440B3P12M030

Nano-Change® (M8) Jumper Cables



M8 3 Pole – Single I/O Multi-Port

M8 4 Pole – Twin I/O Multi-Port



Female Connector

Cable

Length (m)





Form B DIN (10mm) 2 pole + 6 o'clock earth



- 1 Brown
- 2 Blue
- 3 Yellow/Green*

Cable	Length (m)	D43000E12M006	D43002E12M006	D44000E12M006	D44002E12M006
PVC	0.6	D43000E12M006	D43002E12M006	D44000E12M006	D44002E12M006
	1.0	D43000E12M010	D43002E12M010	D44000E12M010	D44002E12M010
	2.0	D43000E12M020	D43002E12M020	D44000E12M020	D44002E12M020
	3.0	D43000E12M030	D43002E12M030	D44000E12M030	D44002E12M030
PUR	0.6	D43000P12M006	D43002P12M006	D44000P12M006	D44002P12M006
	1.0	D43000P12M010	D43002P12M010	D44000P12M010	D44002P12M010
	2.0	D43000P12M020	D43002P12M020	D44000P12M020	D44002P12M020
	3.0	D43000P12M030	D43002P12M030	D44000P12M030	D44002P12M030



Form B DIN (10mm) 2 pole + 6 o'clock earth – 24 V LED & VDR



- 1 Brown
- 2 Blue
- 3 Yellow/Green*

Cable	Length (m)	D430B0E12M006	D430B2E12M006	D440B0E12M006	D440B2E12M006
PVC	0.6	D430B0E12M006	D430B2E12M006	D440B0E12M006	D440B2E12M006
	1.0	D430B0E12M010	D430B2E12M010	D440B0E12M010	D440B2E12M010
	2.0	D430B0E12M020	D430B2E12M020	D440B0E12M020	D440B2E12M020
	3.0	D430B0E12M030	D430B2E12M030	D440B0E12M030	D440B2E12M030
PUR	0.6	D430B0P12M006	D430B2P12M006	D440B0P12M006	D440B2P12M006
	1.0	D430B0P12M010	D430B2P12M010	D440B0P12M010	D440B2P12M010
	2.0	D430B0P12M020	D430B2P12M020	D440B0P12M020	D440B2P12M020
	3.0	D430B0P12M030	D430B2P12M030	D440B0P12M030	D440B2P12M030



Form C DIN (8mm) 2 pole + earth



- 1 Brown
- 2 Blue
- 3 Yellow/Green*

Cable	Length (m)	H43000E12M006	H43002E12M006	H44000E12M006	H44002E12M006
PVC	0.6	H43000E12M006	H43002E12M006	H44000E12M006	H44002E12M006
	1.0	H43000E12M010	H43002E12M010	H44000E12M010	H44002E12M010
	2.0	H43000E12M020	H43002E12M020	H44000E12M020	H44002E12M020
	3.0	H43000E12M030	H43002E12M030	H44000E12M030	H44002E12M030
PUR	0.6	H43000P12M006	H43002P12M006	H44000P12M006	H44002P12M006
	1.0	H43000P12M010	H43002P12M010	H44000P12M010	H44002P12M010
	2.0	H43000P12M020	H43002P12M020	H44000P12M020	H44002P12M020
	3.0	H43000P12M030	H43002P12M030	H44000P12M030	H44002P12M030


Form C DIN (8mm) 2 pole + earth – 24 V LED & VDR



- 1 Brown
- 2 Blue
- 3 Yellow/Green*

Cable	Length (m)	H430B0E12M006	H430B2E12M006	H440B0E12M006	H440B2E12M006
PVC	0.6	H430B0E12M006	H430B2E12M006	H440B0E12M006	H440B2E12M006
	1.0	H430B0E12M010	H430B2E12M010	H440B0E12M010	H440B2E12M010
	2.0	H430B0E12M020	H430B2E12M020	H440B0E12M020	H440B2E12M020
	3.0	H430B0E12M030	H430B2E12M030	H440B0E12M030	H440B2E12M030
PUR	0.6	H430B0P12M006	H430B2P12M006	H440B0P12M006	H440B2P12M006
	1.0	H430B0P12M010	H430B2P12M010	H440B0P12M010	H440B2P12M010
	2.0	H430B0P12M020	H430B2P12M020	H440B0P12M020	H440B2P12M020
	3.0	H430B0P12M030	H430B2P12M030	H440B0P12M030	H440B2P12M030

* Yellow/Green not connected




Female Connector


Cable

Length (m)



M8 3 Pole – Single I/O Multi-Port



M8 4 Pole – Twin I/O Multi-Port



Form C Ind (9.4mm) 2 pole + earth



- 1 Brown
- 2 Blue
- 3 Yellow/Green*

PVC 0.6

1.0

2.0

3.0

PUR 0.6

1.0

2.0

3.0

G43000E12M006

G43000E12M010

G43000E12M020

G43000E12M030

G43000P12M006

G43000P12M010

G43000P12M020

G43000P12M030

G43002E12M006

G43002E12M010

G43002E12M020

G43002E12M030

G43002P12M006

G43002P12M010

G43002P12M020

G43002P12M030

G44000E12M006

G44000E12M010

G44000E12M020

G44000E12M030

G44000P12M006

G44000P12M010

G44000P12M020

G44000P12M030

G44002E12M006

G44002E12M010

G44002E12M020

G44002E12M030



G44002P12M006

G44002P12M010

G44002P12M020

G44002P12M030

Form C Ind (9.4mm) 2 pole + earth – 24 V LED & VDR



- 1 Brown
- 2 Blue
- 3 Yellow/Green*

PVC 0.6

1.0

2.0

3.0

PUR 0.6

1.0

2.0

3.0

G430B0E12M006

G430B0E12M010

G430B0E12M020

G430B0E12M030

G430B0P12M006

G430B0P12M010

G430B0P12M020

G430B0P12M030

G430B2E12M006

G430B2E12M010

G430B2E12M020

G430B2E12M030

G430B2P12M006

G430B2P12M010

G430B2P12M020

G430B2P12M030

G440B0E12M006

G440B0E12M010

G440B0E12M020

G440B0E12M030

G440B0P12M006

G440B0P12M010

G440B0P12M020

G440B0P12M030

G440B2E12M006

G440B2E12M010

G440B2E12M020

G440B2E12M030

G440B2P12M006

G440B2P12M010

G440B2P12M020

G440B2P12M030

* Yellow/Green not connected

Nano-Change (M8) Adapters and In-Line Splitters

M8 3 Pole – Single I/O Multi-Port

M8 4 Pole – Twin I/O Multi-Port

Female Connector



- 1 Brown
- 2 Blue
- 3 Black



- 1 Brown
- 2 White
- 3 Blue
- 4 Black




- 1 Brown
- 2 Black B
- 3 Blue
- 4 Black A

In-line splitter M8 to M8




- 1 Brown
- 2 Blue
- 3 Black


Adapter M12 to M8




- 1 Brown
- 2 White
- 3 Blue
- 4 Black



853030



854030




444A30



M8 3 Pole – Single I/O Multi-Port

M8 4 Pole – Twin I/O Multi-Port

Female Connector




Circuit


WIRING CONFIGURATION

WIRING CONFIGURATION


Form A (18mm) 2 pole + earth




None
24 V LED & VDR




E53000
E530B0



E53002
E530B2




E54000
E540B0




E54002
E540B2


Form B (11mm) 2 pole + 12 o'clock earth




None
24 V LED & VDR




F53001
F530B1



F53003
F530B3




F54001
F540B1




F54003
F540B3


Form B (11mm) 2 pole + 6 o'clock earth




None
24 V LED & VDR




F53000
F530B0



F53002
F530B2




F54000
F540B0




F54002
F540B2


Form B (10mm) 2 pole + 12 o'clock earth




None
24 V LED & VDR




D53001
D530B1



D53003
D530B3




D54001
D540B1




D54003
D540B3


Form B (10mm) 2 pole + 6 o'clock earth




None
24 V LED & VDR




D53000
D530B0



D53002
D530B2




D54000
D540B0




D54002
D540B2


Form C (8mm) 2 pole + earth



None
24 V LED & VDR




H53000
H530B0




H54000
H540B0


Form C (9.4mm) 2 pole + earth



None
24 V LED & VDR



G53000
G530B0



G54000
G540B0

MICRO-CHANGE® MULTI-PORT SPLITTER BOX SYSTEMS





- **Frees up skilled workforce for more demanding tasks, whilst reducing the risk of wiring errors and increasing factory throughput**
- **Quick disconnect solution enables installation or maintenance by semiskilled operators, especially when unscheduled down time occurs through device or cable failure.**
- **Twin I/O versions increases the density of control devices per unit with LED indication of power and signals for fast fault finding**
- **Unique choice of either top or side mounted I/O connections for compact or low profile installations, all provided in a robust design sealed waterproof up to IP68**



Micro-Change® (M12) Multi-Port Splitter Boxes

5 pole 4 Wire – Single I/O Top-Mount Multi-Ports



Function	Cable Colour	M23 Connector Pin No	Mini-Change Pin No	Function	Cable Colour	M23 Connector Pin No	Mini-Change Pin No
+V	Brown	11	10	Earth	Green/Yellow	12	9
0V	Blue	9 & 10	11				
Port 1 P4	White	1	1	Port 5 P4	Pink	5	5
Port 2 P4	Green	2	2	Port 6 P4	Red	6	6
Port 3 P4	Yellow	3	3	Port 7 P4	Black	7	7
Port 4 P4	Grey	4	4	Port 8 P4	Violet	8	8

Cable




Length (m)

Integral Cable Entry

4 Port

6 Port

8 Port






PVC	5.0	BTY400P-FBE-05	BTY600P-FBE-05	BTY800P-FBE-05
	10.0	BTY400P-FBE-10	BTY600P-FBE-10	BTY800P-FBE-10
	20.0	BTY400P-FBE-20	BTY600P-FBE-20	BTY800P-FBE-20
PUR	5.0	BTY400P-FBP-05	BTY600P-FBP-05	BTY800P-FBP-05
	10.0	BTY400P-FBP-10	BTY600P-FBP-10	BTY800P-FBP-10
	20.0	BTY400P-FBP-20	BTY600P-FBP-20	BTY800P-FBP-20

Integral M23 12 Pole Home Run Connector

4 Port

6 Port

8 Port



See top of page 19 for connectors

BTY401P-FBC

BTY601P-FBC




BTY801P-FBC

Integral Mini-Change® 12 Pole Home Run Connector

4 Port

6 Port

8 Port



See top of page 20 for connectors


BTY401P-FBB

BTY601P-FBB

BTY801P-FBB



5 pole 5 Wire – Twin I/O Top-Mount Multi-Ports






Function	Cable Colour	M23 Connector Pin No	Mini-Change Pin No	Attachable	Function	Cable Colour	M23 Connector Pin No	Mini-Change Pin No	Attachable
+V	Brown	19	7	17	Earth	Green/Yellow	12	12	19
0V	Blue	6	5	18					
Port 1 P4	White	15	15	1	Port 1 P2	Grey/Pink	7	19	9
Port 2 P4	Green	5	6	2	Port 2 P2	Red/Blue	4	4	10
Port 3 P4	Yellow	16	16	3	Port 3 P2	White/Green	8	8	11
Port 4 P4	Grey	3	3	4	Port 4 P2	Brown/Green	14	14	12
Port 5 P4	Pink	17	17	5	Port 5 P2	White/Yellow	9	9	13
Port 6 P4	Red	2	2	6	Port 6 P2	Yellow/Brown	13	13	14
Port 7 P4	Black	11	11	7	Port 7 P2	White/Grey	10	10	15
Port 8 P4	Violet	1	1	8	Port 8 P2	Grey/Brown	18	18	16

Integral Cable Entry

4 Port

6 Port

8 Port



PVC

5.0

BTY405P-FBE-05

BTY605P-FBE-05

BTY805P-FBE-05

10.0

BTY405P-FBE-10

BTY605P-FBE-10

BTY805P-FBE-10

20.0

BTY405P-FBE-20

BTY605P-FBE-20

BTY805P-FBE-20

PUR

5.0

BTY405P-FBP-05

BTY605P-FBP-05

BTY805P-FBP-05

10.0

BTY405P-FBP-10

BTY605P-FBP-10

BTY805P-FBP-10

20.0

BTY405P-FBP-20

BTY605P-FBP-20




BTY805P-FBP-20

Integral M23 19 Pole Home Run Connector

4 Port

6 Port

8 Port

See bottom of
page 19 for connectors

BTY403P-FBC

BTY603P-FBC




BTY803P-FBC

Integral Mini-Change® 19 Pole Home Run Connector

4 Port

6 Port

8 Port

See bottom of
page 20 for connectors

BTY403P-FBB

BTY603P-FBB




BTY803P-FBB

Field Attachables

4 Port

6 Port

8 Port

Includes removeable
cable terminals for
ease of assembly

BTY403P-FBA


BTY603P-FBA

BTY803P-FBA

Standard: Power and two status LEDs per port, identification labels, two sealing caps
Options: NPN format LED indication, choice of cable see page 40 for more information

Micro-Change® (M12) Multi-Port Splitter Boxes

5 pole 3 Wire – Single I/O Side-Mount Multi-Ports



Function	Cable	Mini-Change Colour	Function	Cable	Mini-Change Pin No
+V	Brown	10	Earth*	Green/Yellow	9
0V	Blue	11			
Port 1 P4	White	1	Port 5 P4	Pink	5
Port 2 P4	Green	2	Port 6 P4	Red	6
Port 3 P4	Yellow	3	Port 7 P4	Black	7
Port 4 P4	Grey	4	Port 8 P4	Violet	8






Standard: Power and single status LED per port, identification labels, two sealing caps
Options: NPN format LED indication, choice of cable see page 40 for more information

Integral Cable Entry

4 Port

6 Port

8 Port



* Earth (pin 5) not connected on this model







PVC	5.0	BSY404P-FBE-05	BSY604P-FBE-05	BSY804P-FBE-05
	10.0	BSY404P-FBE-10	BSY604P-FBE-10	BSY804P-FBE-10
	20.0	BSY404P-FBE-20	BSY604P-FBE-20	BSY804P-FBE-20
PUR	5.0	BSY404P-FBP-05	BSY604P-FBP-05	BSY804P-FBP-05
	10.0	BSY404P-FBP-10	BSY604P-FBP-10	BSY804P-FBP-10
	20.0	BSY404P-FBP-20	BSY604P-FBP-20	BSY804P-FBP-20

Integral Mini-Change® 12 Pole Home Run Connector

4 Port

6 Port

8 Port




* Earth (pin 5) connected on this model

BSY401P-FBB

BSY601P-FBB

BSY801P-FBB

5 pole 5 Wire – Twin I/O Side-Mount Multi-Ports



Function	Cable	Mini-Change Pin No	Function	Cable	Mini-Change Pin No
+V	Brown	7	Earth	Green/Yellow	12
0V	Blue	5			
Port 1 P4	White	15	Port 1 P2	Grey/Pink	19
Port 2 P4	Green	6	Port 2 P2	Red/Blue	4
Port 3 P4	Yellow	16	Port 3 P2	White/Green	8
Port 4 P4	Grey	3	Port 4 P2	Brown/Green	14
Port 5 P4	Pink	17	Port 5 P2	White/Yellow	9
Port 6 P4	Red	2	Port 6 P2	Yellow/Brown	13
Port 7 P4	Black	11	Port 7 P2	White/Grey	10
Port 8 P4	Violet	1	Port 8 P2	Grey/Brown	18







Standard: Power and two status LED per port, identification labels, two sealing caps
Options: NPN format LED indication, choice of cable see page 40 for more information

Integral Cable Entry

4 Port

6 Port

8 Port









PVC	5.0	BSY403P-FBE-05	BSY603P-FBE-05	BSY803P-FBE-05
	10.0	BSY403P-FBE-10	BSY603P-FBE-10	BSY803P-FBE-10
	20.0	BSY403P-FBE-20	BSY603P-FBE-20	BSY803P-FBE-20
PUR	5.0	BSY403P-FBP-05	BSY603P-FBP-05	BSY803P-FBP-05
	10.0	BSY403P-FBP-10	BSY603P-FBP-10	BSY803P-FBP-10
	20.0	BSY403P-FBP-20	BSY603P-FBP-20	BSY803P-FBP-20

Integral Mini-Change® 18 Pole Home Run Connector

4 Port

6 Port

8 Port




BSY403P-FBB

BSY603P-FBB

BSY803P-FBB




Female Connector



Function	M23 Connector Pin No	Cable Colour	Function	M23 Connector Pin No	Cable Colour
+V	11	Brown	Earth	12	Green/Yellow
0V	9 & 10	Blue			
Port 1 P4	1	White	Port 5 P4	5	Pink
Port 2 P4	2	Green	Port 6 P4	6	Red
Port 3 P4	3	Yellow	Port 7 P4	7	Black
Port 4 P4	4	Grey	Port 8 P4	8	Violet


M23 12 Pole Moulded Connector

M23 Straight




		BTY401P-FBC 5 Pole/4 Wire - 4 Port	BTY601P-FBC 5 Pole/4 Wire - 6 Port	BNY801P-FBC 5 Pole/4 Wire - 8 Port		
PVC	5.0	K02300E80M050	K02200E80M050	K02100E80M050		
	10.0	K02300E80M100	K02200E80M100	K02100E80M100		
	20.0	K02300E80M200	K02200E80M200	K02100E80M200		
PUR	5.0	K02300P80M050	K02200P80M050	K02100P80M050		
	10.0	K02300P80M100	K02200P80M100	K02100P80M100		
	20.0	K02300P80M200	K02200P80M200	K02100P80M200		

M23 90°



PVC	5.0	K02301E80M050	K02201E80M050	K02101E80M050		
	10.0	K02301E80M100	K02201E80M100	K02101E80M100		
	20.0	K02301E80M200	K02201E80M200	K02101E80M200		
PUR	5.0	K02301P80M050	K02201P80M050	K02101P80M050		
	10.0	K02301P80M100	K02201P80M100	K02101P80M100		
	20.0	K02301P80M200	K02201P80M200	K02101P80M200		



Function	M23 Connector Pin No	Cable Colour	Function	M23 Connector Pin No	Cable Colour
+V	19	Brown	Earth	12	Green/Yellow
0V	6	Blue			
Port 1 P4	15	White	Port 1 P2	7	Grey/Pink
Port 2 P4	5	Green	Port 2 P2	4	Red/Blue
Port 3 P4	16	Yellow	Port 3 P2	8	White/Green
Port 4 P4	3	Grey	Port 4 P2	14	Brown/Green
Port 5 P4	17	Pink	Port 5 P2	9	White/Yellow
Port 6 P4	2	Red	Port 6 P2	13	Yellow/Brown
Port 7 P4	11	Black	Port 7 P2	10	White/Grey
Port 8 P4	1	Violet	Port 8 P2	18	Grey/Brown


M23 19 Pole Moulded Connector

M23 Straight



		BTY403P-FBC 5 Pole/5 Wire - 4 Port	BTY603P-FBC 5 Pole/5 Wire - 6 Port	BNY803P-FBC 5 Pole/5 Wire - 8 Port		
PVC	5.0	K03300E80M050	K03200E80M050	K03000E80M050		
	10.0	K03300E80M100	K03200E80M100	K03000E80M100		
	20.0	K03300E80M200	K03200E80M200	K03000E80M200		
PUR	5.0	K03300P80M050	K03200P80M050	K03000P80M050		
	10.0	K03300P80M100	K03200P80M100	K03000P80M100		
	20.0	K03300P80M200	K03200P80M200	K03000P80M200		


M23 90°



PVC	5.0	K03301E80M050	K03201E80M050	K03001E80M050		
	10.0	K03301E80M100	K03201E80M100	K03001E80M100		
	20.0	K03301E80M200	K03201E80M200	K03001E80M200		
PUR	5.0	K03301P80M050	K03201P80M050	K03001P80M050		
	10.0	K03301P80M100	K03201P80M100	K03001P80M100		
	20.0	K03301P80M200	K03201P80M200	K03001P80M200		



Female Connector




Function	Mini-Change Pin No	Cable Colour	Function	Mini-Change Pin No	Cable Colour
+V	10	Brown	Earth	9	Green/Yellow
0V	11	Blue			
Port 1 P4	1	White	Port 5 P4	5	Pink
Port 2 P4	2	Green	Port 6 P4	6	Red
Port 3 P4	3	Yellow	Port 7 P4	7	Black
Port 4 P4	4	Grey	Port 8 P4	8	Violet

Cable
Length (m)


Mini-Change® 12 pole Moulded Connector

Mini-Change® Straight




		BTY401P-FBB BSY401P-FBB 5 Pole/4 Wire - 4 Port	BTY601P-FBB BSY601P-FBB 5 Pole/4 Wire - 6 Port	BTY801P-FBB BSY801P-FBB 5 Pole/4 Wire - 8 Port		
PVC	5.0	302300E80M050	302200E80M050	302100E80M050		
	10.0	302300E80M100	302200E80M100	302100E80M100		
	20.0	302300E80M200	302200E80M200	302100E80M200		
PUR	5.0	302300P80M050	302200P80M050	302100P80M050		
	10.0	302300P80M100	302200P80M100	302100P80M100		
	20.0	302300P80M200	302200P80M200	302100P80M200		

Mini-Change® 90°




PVC	5.0	302301E80M050	302201E80M050	302101E80M050		
	10.0	302301E80M100	302201E80M100	302101E80M100		
	20.0	302301E80M200	302201E80M200	302101E80M200		
PUR	5.0	302301P80M050	302201P80M050	302101P80M050		
	10.0	302301P80M100	302201P80M100	302101P80M100		
	20.0	302301P80M200	302201P80M200	302101P80M200		



Function	Mini-Change Pin No	Cable Colour	Function	Mini-Change Pin No	Cable Colour
+V	7	Brown	Earth	12	Green/Yellow
0V	5	Blue			
Port 1 P4	15	White	Port 1 P2	19	Grey/Pink
Port 2 P4	6	Green	Port 2 P2	4	Red/Blue
Port 3 P4	16	Yellow	Port 3 P2	8	White/Green
Port 4 P4	3	Grey	Port 4 P2	14	Brown/Green
Port 5 P4	17	Pink	Port 5 P2	9	White/Yellow
Port 6 P4	2	Red	Port 6 P2	13	Yellow/Brown
Port 7 P4	11	Black	Port 7 P2	10	White/Grey
Port 8 P4	1	Violet	Port 8 P2	18	Grey/Brown


Mini-Change® 19 pole Moulded Connector

Mini-Change® Straight




		BTY403P-FBB 5 Pole/5 Wire - 4 Port	BTY603P-FBB 5 Pole/5 Wire - 6 Port	BTY803P-FBB 5 Pole/5 Wire - 8 Port		
PVC	5.0	303300E80M050	303200E80M050	303000E80M050		
	10.0	303300E80M100	303200E80M100	303000E80M100		
	20.0	303300E80M200	303200E80M200	303000E80M200		
PUR	5.0	303300P80M050	303200P80M050	303000P80M050		
	10.0	303300P80M100	303200P80M100	303000P80M100		
	20.0	303300P80M200	303200P80M200	303000P80M200		


Mini-Change® 90°



PVC	5.0	303301E80M050	303201E80M050	303001E80M050		
	10.0	303301E80M100	303201E80M100	303001E80M100		
	20.0	303301E80M200	303201E80M200	303001E80M200		
PUR	5.0	303301P80M050	303201P80M050	303001P80M050		
	10.0	303301P80M100	303201P80M100	303001P80M100		
	20.0	303301P80M200	303201P80M200	303001P80M200		




M12 Single I/O Multi-Port



WIRING CONFIGURATION

M12 Twin I/O Multi-Port



WIRING CONFIGURATION


Nano-Change® (M8) Straight



1 Brown
3 Blue
4 Black

PVC	0.6	483030E03M006	483032E03M006
	1.0	483030E03M010	483032E03M010
	2.0	483030E03M020	483032E03M020
	3.0	483030E03M030	483032E03M030
PUR	0.6	483030P03M006	483032P03M006
	1.0	483030P03M010	483032P03M010
	2.0	483030P03M020	483032P03M020
	3.0	483030P03M030	483032P03M030

Nano-Change® (M8) 90°




Pin No. Wire
1 Brown
3 Blue
4 Black

PVC	0.6	483031E03M006	483033E03M006
	1.0	483031E03M010	483033E03M010
	2.0	483031E03M020	483033E03M020
	3.0	483031E03M030	483033E03M030
PUR	0.6	483031P03M006	483033P03M006
	1.0	483031P03M010	483033P03M010
	2.0	483031P03M020	483033P03M020
	3.0	483031P03M030	483033P03M030

Also
compatible
with Twin I/O
Multi-Ports

484A30E03M006
484A30E03M010
484A30E03M020
484A30E03M030
484A30P03M006
484A30P03M010
484A30P03M020
484A30P03M030

Nano-Change® (M8) 90° PNP LED




1 Brown
3 Blue
4 Black

PVC	0.6	4830P7E03M006	4830P9E03M006
	1.0	4830P7E03M010	4830P9E03M010
	2.0	4830P7E03M020	4830P9E03M020
	3.0	4830P7E03M030	4830P9E03M030
PUR	0.6	4830P7P03M006	4830P9P03M006
	1.0	4830P7P03M010	4830P9P03M010
	2.0	4830P7P03M020	4830P9P03M020
	3.0	4830P7P03M030	4830P9P03M030

484AP7E03M006
484AP7E03M010
484AP7E03M020
484AP7E03M030
484AP7P03M006
484AP7P03M010
484AP7P03M020
484AP7P03M030


Nano-Change® (M8) Straight



1 Brown
2 White*
3 Blue
4 Black

PVC	0.6		484030E03M006	484032E03M006	484C30E03M006
	1.0		484030E03M010	484032E03M010	484C30E03M010
	2.0		484030E03M020	484032E03M020	484C30E03M020
	3.0		484030E03M030	484032E03M030	484C30E03M030
PUR	0.6		484030P03M006	484032P03M006	484C30P03M006
	1.0		484030P03M010	484032P03M010	484C30P03M010
	2.0		484030P03M020	484032P03M020	484C30P03M020
	3.0		484030P03M030	484032P03M030	484C30P03M030

Nano-Change® (M8) 90°



1 Brown
2 White*
3 Blue
4 Black

PVC	0.6		484031E03M006	484033E03M006	484C31E03M006
	1.0		484031E03M010	484033E03M010	484C31E03M010
	2.0		484031E03M020	484033E03M020	484C31E03M020
	3.0		484031E03M030	484033E03M030	484C31E03M030
PUR	0.6		484031P03M006	484033P03M006	484C31P03M006
	1.0		484031P03M010	484033P03M010	484C31P03M010
	2.0		484031P03M020	484033P03M020	484C31P03M020
	3.0		484031P03M030	484033P03M030	484C31P03M030

Also
compatible
with
Single I/O
Multi-Ports

* White not used on in-line
splitter connectors

Micro-Change® (M12) Jumper Cables



Female Connector


Cable

Length (m)

M12 Single I/O Multi-Port



Male Straight



Male 90°




- 1 Brown
- 2 Blue
- 3 Black
- 4 Black

WIRING CONFIGURATION

M12 Twin I/O Multi-Port



Male Straight



Male 90°




- 1 Brown
- 2 White
- 3 Blue
- 4 Black

WIRING CONFIGURATION




- 1 Brown
- 2 Black B
- 3 Blue
- 4 Black A

Micro-Change® (M12) Straight




PVC	0.6	883030E03M006	883032E03M006	884030E03M006	884032E03M006	884A30E03M006
	1.0	883030E03M010	883032E03M010	884030E03M010	884032E03M010	884A30E03M010
	2.0	883030E03M020	883032E03M020	884030E03M020	884032E03M020	884A30E03M020
	3.0	883030E03M030	883032E03M030	884030E03M030	884032E03M030	884A30E03M030
PUR	0.6	883030P03M006	883032P03M006	884030P03M006	884032P03M006	884A30P03M006
	1.0	883030P03M010	883032P03M010	884030P03M010	884032P03M010	884A30P03M010
	2.0	883030P03M020	883032P03M020	884030P03M020	884032P03M020	884A30P03M020
	3.0	883030P03M030	883032P03M030	884030P03M030	884032P03M030	884A30P03M030

Micro-Change® (M12) 90°




PVC	0.6	883031E03M006	883033E03M006	884031E03M006	884033E03M006	884A31E03M006
	1.0	883031E03M010	883033E03M010	884031E03M010	884033E03M010	884A31E03M010
	2.0	883031E03M020	883033E03M020	884031E03M020	884033E03M020	884A31E03M020
	3.0	883031E03M030	883033E03M030	884031E03M030	884033E03M030	884A31E03M030
PUR	0.6	883031P03M006	883033P03M006	884031P03M006	884033P03M006	884A31P03M006
	1.0	883031P03M010	883033P03M010	884031P03M010	884033P03M010	884A31P03M010
	2.0	883031P03M020	883033P03M020	884031P03M020	884033P03M020	884A31P03M020
	3.0	883031P03M030	883033P03M030	884031P03M030	884033P03M030	884A31P03M030

Micro-Change® (M12) PNP LED



PVC	0.6	8830P6E03M006	8830P8E03M006	8840P6E03M006	8840P8E03M006	884AP6E03M006
	1.0	8830P6E03M010	8830P8E03M010	8840P6E03M010	8840P8E03M010	884AP6E03M010
	2.0	8830P6E03M020	8830P8E03M020	8840P6E03M020	8840P8E03M020	884AP6E03M020
	3.0	8830P6E03M030	8830P8E03M030	8840P6E03M030	8840P8E03M030	884AP6E03M030
PUR	0.6	8830P6P03M006	8830P8P03M006	8840P6P03M006	8840P8P03M006	884AP6P03M006
	1.0	8830P6P03M010	8830P8P03M010	8840P6P03M010	8840P8P03M010	884AP6P03M010
	2.0	8830P6P03M020	8830P8P03M020	8840P6P03M020	8840P8P03M020	884AP6P03M020
	3.0	8830P6P03M030	8830P8P03M030	8840P6P03M030	8840P8P03M030	884AP6P03M030

Micro-Change® (M12) 90° PNP LED



PVC	0.6	8830P7E03M006	8830P9E03M006	8840P7E03M006	8840P9E03M006	884AP7E03M006
	1.0	8830P7E03M010	8830P9E03M010	8840P7E03M010	8840P9E03M010	884AP7E03M010
	2.0	8830P7E03M020	8830P9E03M020	8840P7E03M020	8840P9E03M020	884AP7E03M020
	3.0	8830P7E03M030	8830P9E03M030	8840P7E03M030	8840P9E03M030	884AP7E03M030
PUR	0.6	8830P7P03M006	8830P9P03M006	8840P7P03M006	8840P9P03M006	884AP7P03M006
	1.0	8830P7P03M010	8830P9P03M010	8840P7P03M010	8840P9P03M010	884AP7P03M010
	2.0	8830P7P03M020	8830P9P03M020	8840P7P03M020	8840P9P03M020	884AP7P03M020
	3.0	8830P7P03M030	8830P9P03M030	8840P7P03M030	8840P9P03M030	884AP7P03M030

* White not used on Single I/O and in-line splitter connectors




Female Connector


Cable

Length (m)

M12 Single I/O Multi-Port





Male Straight



Male 90°



WIRING CONFIGURATION

M12 Twin I/O Multi-Port



WIRING CONFIGURATION



Form A (18mm) 2 pole + earth



- 1 Brown
2 Blue
3 Yellow/Green

PVC	0.6	E85000E12M006	E85002E12M006		E85A00E12M006
	1.0	E85000E12M010	E85002E12M010		E85A00E12M010
	2.0	E85000E12M020	E85002E12M020		E85A00E12M020
	3.0	E85000E12M030	E85002E12M030		E85A00E12M030
PUR	0.6	E85000P12M006	E85002P12M006		E85A00P12M006
	1.0	E85000P12M010	E85002P12M010		E85A00P12M010
	2.0	E85000P12M020	E85002P12M020		E85A00P12M020
	3.0	E85000P12M030	E85002P12M030		E85A00P12M030



Form A (18mm) 2 pole + earth – 24 V LED & VDR



- 1 Brown
2 Blue
3 Yellow/Green

PVC	0.6	E850B0E12M006	E850B2E12M006		E85AB0E12M006
	1.0	E850B0E12M010	E850B2E12M010		E85AB0E12M010
	2.0	E850B0E12M020	E850B2E12M020		E85AB0E12M020
	3.0	E850B0E12M030	E850B2E12M030		E85AB0E12M030
PUR	0.6	E850B0P12M006	E850B2P12M006		E85AB0P12M006
	1.0	E850B0P12M010	E850B2P12M010		E85AB0P12M010
	2.0	E850B0P12M020	E850B2P12M020		E85AB0P12M020
	3.0	E850B0P12M030	E850B2P12M030		E85AB0P12M030

Form B Ind (11mm) 2 pole + 12 o'clock earth





- 1 Brown
2 Blue
3 Yellow/Green

PVC	0.6	F85001E12M006	F85003E12M006		F85A01E12M006
	1.0	F85001E12M010	F85003E12M010		F85A01E12M010
	2.0	F85001E12M020	F85003E12M020		F85A01E12M020
	3.0	F85001E12M030	F85003E12M030		F85A01E12M030
PUR	0.6	F85001P12M006	F85003P12M006		F85A01P12M006
	1.0	F85001P12M010	F85003P12M010		F85A01P12M010
	2.0	F85001P12M020	F85003P12M020		F85A01P12M020
	3.0	F85001P12M030	F85003P12M030		F85A01P12M030

Also
compatible
with Twin I/O
Multi-Ports

Form B Ind (11mm) 2 pole + 12 o'clock earth – 24 V LED & VDR



- 1 Brown
2 Blue
3 Yellow/Green

PVC	0.6	F850B1E12M006	F850B3E12M006		F85AB1E12M006
	1.0	F850B1E12M010	F850B3E12M010		F85AB1E12M010
	2.0	F850B1E12M020	F850B3E12M020		F85AB1E12M020
	3.0	F850B1E12M030	F850B3E12M030		F85AB1E12M030
PUR	0.6	F850B1P12M006	F850B3P12M006		F85AB1P12M006
	1.0	F850B1P12M010	F850B3P12M010		F85AB1P12M010
	2.0	F850B1P12M020	F850B3P12M020		F85AB1P12M020
	3.0	F850B1P12M030	F850B3P12M030		F85AB1P12M030




Female Connector


Cable

Length (m)

M12 Single I/O Multi-Port



Male Straight





Male 90°





WIRING CONFIGURATION

M12 Twin I/O Multi-Port



WIRING CONFIGURATION



Form B DIN (10mm) 2 pole + 6 o'clock earth



- 1 Brown
2 Blue
3 Yellow/Green

Cable	Length (m)	Form B DIN (10mm) 2 pole + 6 o'clock earth	Form B DIN (10mm) 2 pole + 6 o'clock earth – 24 V LED & VDR	Form C DIN (8mm) 2 pole + earth	Form C DIN (8mm) 2 pole + earth – 24 V LED & VDR
PVC	0.6	D85000E12M006	D85002E12M006	H85000E12M006	H85002E12M006
	1.0	D85000E12M010	D85002E12M010	H85000E12M010	H85002E12M010
	2.0	D85000E12M020	D85002E12M020	H85000E12M020	H85002E12M020
	3.0	D85000E12M030	D85002E12M030	H85000E12M030	H85002E12M030
PUR	0.6	D85000P12M006	D85002P12M006	H85000P12M006	H85002P12M006
	1.0	D85000P12M010	D85002P12M010	H85000P12M010	H85002P12M010
	2.0	D85000P12M020	D85002P12M020	H85000P12M020	H85002P12M020
	3.0	D85000P12M030	D85002P12M030	H85000P12M030	H85002P12M030



Form B DIN (10mm) 2 pole + 6 o'clock earth – 24 V LED & VDR



- 1 Brown
2 Blue
3 Yellow/Green

Cable	Length (m)	Form B DIN (10mm) 2 pole + 6 o'clock earth – 24 V LED & VDR	Form C DIN (8mm) 2 pole + earth	Form C DIN (8mm) 2 pole + earth – 24 V LED & VDR
PVC	0.6	D850B0E12M006	H850B2E12M006	D85AB0E12M006
	1.0	D850B0E12M010	H850B2E12M010	D85AB0E12M010
	2.0	D850B0E12M020	H850B2E12M020	D85AB0E12M020
	3.0	D850B0E12M030	H850B2E12M030	D85AB0E12M030
PUR	0.6	D850B0P12M006	H850B2P12M006	D85AB0P12M006
	1.0	D850B0P12M010	H850B2P12M010	D85AB0P12M010
	2.0	D850B0P12M020	H850B2P12M020	D85AB0P12M020
	3.0	D850B0P12M030	H850B2P12M030	D85AB0P12M030



Form C DIN (8mm) 2 pole + earth



- 1 Brown
2 Blue
3 Yellow/Green

Cable	Length (m)	Form C DIN (8mm) 2 pole + earth	Form C DIN (8mm) 2 pole + earth – 24 V LED & VDR
PVC	0.6	H85000E12M006	H850B2E12M006
	1.0	H85000E12M010	H850B2E12M010
	2.0	H85000E12M020	H850B2E12M020
	3.0	H85000E12M030	H850B2E12M030
PUR	0.6	H85000P12M006	H850B2P12M006
	1.0	H85000P12M010	H850B2P12M010
	2.0	H85000P12M020	H850B2P12M020
	3.0	H85000P12M030	H850B2P12M030

Form C DIN (8mm) 2 pole + earth – 24 V LED & VDR




- 1 Brown
2 Blue
3 Yellow/Green


Cable	Length (m)	Form C DIN (8mm) 2 pole + earth – 24 V LED & VDR
PVC	0.6	H850B0E12M006
	1.0	H850B0E12M010
	2.0	H850B0E12M020
	3.0	H850B0E12M030
PUR	0.6	H850B0P12M006
	1.0	H850B0P12M010
	2.0	H850B0P12M020
	3.0	H850B0P12M030

Also
compatible
with Twin I/O
Multi-Ports

Micro-Change® (M12) Jumper Cables




M12 Single I/O Multi-Port Jumpers




WIRING CONFIGURATION

M12 Twin I/O Multi-Port Jumpers



WIRING CONFIGURATION

Form C Ind (9.4mm) 2 pole + earth




- 1 Brown
- 3 Blue
- 4 Black

PVC	0.6	G85000E12M006	G85002E12M006
	1.0	G85000E12M010	G85002E12M010
	2.0	G85000E12M020	G85002E12M020
	3.0	G85000E12M030	G85002E12M030
PUR	0.6	G85000P12M006	G85002P12M006
	1.0	G85000P12M010	G85002P12M010
	2.0	G85000P12M020	G85002P12M020
	3.0	G85000P12M030	G85002P12M030

G85A00E12M006
G85A00E12M010
G85A00E12M020
G85A00E12M030
G85A00P12M006
G85A00P12M010
G85A00P12M020
G85A00P12M030

Form C Ind (9.4mm) 2 pole + earth – 24 V LED & VDR



- 1 Brown
- 3 Blue
- 4 Black


PVC	0.6	G850B0E12M006	G850B2E12M006
	1.0	G850B0E12M010	G850B2E12M010
	2.0	G850B0E12M020	G850B2E12M020
	3.0	G850B0E12M030	G850B2E12M030
PUR	0.6	G850B0P12M006	G850B2P12M006
	1.0	G850B0P12M010	G850B2P12M010
	2.0	G850B0P12M020	G850B2P12M020
	3.0	G850B0P12M030	G850B2P12M030

G85AB0E12M006
G85AB0E12M010
G85AB0E12M020
G85AB0E12M030
G85AB0P12M006
G85AB0P12M010
G85AB0P12M020
G85AB0P12M030

Also compatible with Twin I/O Multi-Ports



Micro-Change® (M12) Adapters and In-Line Splitters

M12 Single I/O Multi-Port





Female Connector


Adapter & In-line Splitter M8 to M12







Adapter M8 to M12



In-line Splitter M12 to M12



M12 Twin I/O Multi-Port






Female Connector

Circuit




WIRING CONFIGURATION


Form A (18mm) 2 pole + earth



None
24 V LED & VDR




E85000
E850B0




E85002
E850B2


Form B (11mm) 2 pole + 12 o'clock earth



None
24 V LED & VDR




F85001
F850B1




F85003
F850B3


Form B (11mm) 2 pole + 6 o'clock earth



None
24 V LED & VDR




F85000
F850B0




F85002
F850B2


Form B (10mm) 2 pole + 12 o'clock earth



None
24 V LED & VDR




D85001
D850B1




D85003
D850B3


Form B (10mm) 2 pole + 6 o'clock earth



None
24 V LED & VDR



D85000
D850B0



D85002
D850B2

NANO-CHANGE® CONNECTORS



- **Quick disconnect provides simple and fast connection for the easy replacement and installation of control devices such as proximity switches**
- **Lightweight and compact, factory assembled and tested connectors reduce the risk of costly wiring errors**
- **Anti-vibration couplings ensure the connector remains secure in harsh environments, maintaining the IP67 waterproof seal and integrity of the system**



Female Connector



3 Pole

- 1 Brown
- 3 Blue
- 4 Black



4 Pole

- 1 Brown
- 2 White
- 3 Blue
- 4 Black




5 Pole

- 1 Brown
- 2 White
- 3 Blue
- 4 Black
- 5 Grey


WIRING CONFIGURATION

Nano-Change® (M8) Straight




PVC	2.0	503000E03M020	504000E03M020		
	5.0	503000E03M050	504000E03M050		
	10.0	503000E03M100	504000E03M100		
PUR	2.0	503000P03M020	504000P03M020	505000P02M020	
	5.0	503000P03M050	504000P03M050	505000P02M050	
	10.0	503000P03M100	504000P03M100	505000P02M100	

Nano-Change® (M8) 90°



PVC	2.0	503001E03M020	504001E03M020		
	5.0	503001E03M050	504001E03M050		
	10.0	503001E03M100	504001E03M100		
PUR	2.0	503001P03M020	504001P03M020	505001P02M020	
	5.0	503001P03M050	504001P03M050	505001P02M050	
	10.0	503001P03M100	504001P03M100	505001P02M100	

Nano-Change® (M8) 90° PNP LED



PVC	2.0	5030P1E03M020			
	5.0	5030P1E03M050			
	10.0	5030P1E03M100			
PUR	2.0	5030P1P03M020			
	5.0	5030P1P03M050			
	10.0	5030P1P03M100			



3 Pole

- 1 Brown
- 3 Blue
- 4 Black



4 Pole

- 1 Brown
- 2 White
- 3 Blue
- 4 Black

WIRING CONFIGURATION

Nano-Change® (M8) Straight



PVC	2.0	503006E03M020	504006E03M020		
	5.0	503006E03M050	504006E03M050		
	10.0	503006E03M100	504006E03M100		
PUR	2.0	503006P03M020	504006P03M020		
	5.0	503006P03M050	504006P03M050		
	10.0	503006P03M100	504006P03M100		



3 Pole

- 1 Brown
- 3 Blue
- 4 Black



4 Pole

- 1 Brown
- 2 White
- 3 Blue
- 4 Black



5 Pole

- 1 Brown
- 2 White
- 3 Blue
- 4 Black
- 5 Grey

Female Connector

Cable
Length (m)


WIRING CONFIGURATION

Nano-Change® (M8) Straight




PVC	2.0	403000E03M020	404000E03M020		
	5.0	403000E03M050	404000E03M050		
	10.0	403000E03M100	404000E03M100		
PUR	2.0	403000P03M020	404000P03M020	405000P02M020	
	5.0	403000P03M050	404000P03M050	405000P02M050	
	10.0	403000P03M100	404000P03M100	405000P02M100	

Nano-Change® (M8) 90°



PVC	2.0	403001E03M020	404001E03M020		
	5.0	403001E03M050	404001E03M050		
	10.0	403001E03M100	404001E03M100		
PUR	2.0	403001P03M020	404001P03M020	405001P02M020	
	5.0	403001P03M050	404001P03M050	405001P02M050	
	10.0	403001P03M100	404001P03M100	405001P02M100	

Nano-Change® (M8) 90° PNP LED



PVC	2.0	4030P1E03M020			
	5.0	4030P1E03M050			
	10.0	4030P1E03M100			
PUR	2.0	4030P1P03M020			
	5.0	4030P1P03M050			
	10.0	4030P1P03M100			



3 Pole

- 1 Brown
- 3 Blue
- 4 Black



4 Pole

- 1 Brown
- 2 White
- 3 Blue
- 4 Black



5 Pole

- 1 Brown
- 2 White
- 3 Blue
- 4 Black
- 5 Grey

Male Connector

Cable
Length (m)


WIRING CONFIGURATION

Nano-Change® (M8) Straight



PVC	2.0	403006E03M020	404006E03M020		
	5.0	403006E03M050	404006E03M050		
	10.0	403006E03M100	404006E03M100		
PUR	2.0	403006P03M020	404006P03M020	405006P02M020	
	5.0	403006P03M050	404006P03M050	405006P02M050	
	10.0	403006P03M100	404006P03M100	405006P02M100	

Nano-Change® (M8) 90°




PVC	2.0	403007E03M020	404007E03M020		
	5.0	403007E03M050	404007E03M050		
	10.0	403007E03M100	404007E03M100		
PUR	2.0	403007P03M020	404007P03M020	405007P02M020	
	5.0	403007P03M050	404007P03M050	405007P02M050	
	10.0	403007P03M100	404007P03M100	405007P02M100	


3 Pole

1 Brown
3 Blue
4 Black


4 Pole

1 Brown 3 Blue
2 White 4 Black


3 Pole

1 Brown
3 Blue
4 Black



4 Pole

1 Brown 3 Blue
2 White 4 Black

Female Attachable

WIRING CONFIGURATION


Nano-Change® (M8) Straight



N03FA03124

N04FA03124

Nano-Change® (M8) 90°




N03FA04124

N04FA04124

Male Attachable

WIRING CONFIGURATION


Nano-Change® (M8) Straight



N03MA03124

N04MA03124

Nano-Change® (M8) 90°



N03MA04124

N04MA04124

Nano-Change® (M8) Receptacles

Female Receptacle

Wire length (mm)


3 Pole

1 Brown
3 Blue
4 Black


4 Pole


1 Brown 3 Blue
2 White 4 Black


5 Pole

1 Brown 4 Black
2 White 5 Grey
3 Blue

WIRING CONFIGURATION

Nano-Change® M8 Mounting Thread




300.0

4R3F30E02C3003

4R4F30E02C3003

4R5F30E02C3003

Nano-Change® PG7 Through Panel




300.0

4R3H40E02C3003

4R4H40E02C3003

4R5H40E02C3003

Nano-Change® PG7 PCB Mount



n/a

4R3H400013

4R4H400013

4R5H400013

Male Receptacle

Wire length (mm)


3 Pole

1 Brown
3 Blue
4 Black


4 Pole


1 Brown 3 Blue
2 White 4 Black


5 Pole

1 Brown 4 Black
2 White 5 Grey
3 Blue

WIRING CONFIGURATION

Nano-Change® M8 Mounting Thread




300.0

4R3F06E02C3003

4R4F06E02C3003

4R5F06E02C3003

MICRO-CHANGE® CONNECTORS



- **Weld splatter resistant coupling nuts and cables ensure reliability and serviceability in harsh operating conditions**
- **Compact and robust design sealed waterproof to IP68, with additional optional benefit of plastic or stainless steel couplings for corrosion resistance in wash down environments**
- **Choice of cable type and length reduces stock variations of I/O devices and provides solutions for food processing, machining and applications demanding shielded or halogen free cables**



Female Connector

Cable

Length (m)


1 Brown
3 Blue
4 Black

5 Pole/3 Wire


1 Brown 3 Blue
2 White 4 Black

5 Pole/4 Wire


1 Brown 4 Black
2 White 5 Grey
3 Blue

5 Pole/5 Wire


1 White 5 Grey
2 Brown 6 Pink
3 Green 7 Blue
4 Yellow 8 Red

8 Pole

WIRING CONFIGURATION


WIRING CONFIGURATION

Micro-Change® (M12) Straight



PVC	2.0	803000E03M020	804000E03M020	805000E03M020	
	5.0	803000E03M050	804000E03M050	805000E03M050	
	10.0	803000E03M100	804000E03M100	805000E03M100	
PUR	2.0	803000P03M020	804000P03M020	805000P03M020	808000P02M020
	5.0	803000P03M050	804000P03M050	805000P03M050	808000P02M050
	10.0	803000P03M100	804000P03M100	805000P03M100	808000P02M100
SJTO	2.0	803000S20M020	804000S20M020	805000S26M020	
	5.0	803000S20M050	804000S20M050	805000S26M050	
	10.0	803000S20M100	804000S20M100	805000S26M100	

Micro-Change® (M12) 90°




PVC	2.0	803001E03M020	804001E03M020	805001E03M020	
	5.0	803001E03M050	804001E03M050	805001E03M050	
	10.0	803001E03M100	804001E03M100	805001E03M100	
PUR	2.0	803001P03M020	804001P03M020	805001P03M020	808001P02M020
	5.0	803001P03M050	804001P03M050	805001P03M050	808001P02M050
	10.0	803001P03M100	804001P03M100	805001P03M100	808001P02M100
SJTO	2.0	803001S20M020	804001S20M020	805001S26M020	
	5.0	803001S20M050	804001S20M050	805001S26M050	
	10.0	803001S20M100	804001S20M100	805001S26M100	

Micro-Change® (M12) PNP LED




PVC	2.0	8030P0E03M020	8040P0E03M020		
	5.0	8030P0E03M050	8040P0E03M050		
	10.0	8030P0E03M100	8040P0E03M100		
PUR	2.0	8030P0P03M020	8040P0P03M020		
	5.0	8030P0P03M050	8040P0P03M050		
	10.0	8030P0P03M100	8040P0P03M100		
SJTO	2.0	8030P0S20M020	8040P0S20M020		
	5.0	8030P0S20M050	8040P0S20M050		
	10.0	8030P0S20M100	8040P0S20M100		

Micro-Change® (M12) 90° PNP LED




PVC	2.0	8030P1E03M020	8040P1E03M020		
	5.0	8030P1E03M050	8040P1E03M050		
	10.0	8030P1E03M100	8040P1E03M100		
PUR	2.0	8030P1P03M020	8040P1P03M020		
	5.0	8030P1P03M050	8040P1P03M050		
	10.0	8030P1P03M100	8040P1P03M100		
SJTO	2.0	8030P1S20M020	8040P1S20M020		
	5.0	8030P1S20M050	8040P1S20M050		
	10.0	8030P1S20M100	8040P1S20M100		


Micro-Change® (M12) Moulded Connectors




Male Connector




5 Pole/3 Wire



5 Pole/4 Wire




5 Pole/5 Wire




8 Pole

Micro-Change® (M12) Straight




Cable Length (m)	WIRING CONFIGURATION			WIRING CONFIGURATION		
	5 Pole/3 Wire	5 Pole/4 Wire	5 Pole/5 Wire	5 Pole/3 Wire	5 Pole/4 Wire	5 Pole/5 Wire
PVC 2.0	803006E03M020	804006E03M020	805006E03M020			
5.0	803006E03M050	804006E03M050	805006E03M050			
10.0	803006E03M100	804006E03M100	805006E03M100			
PUR 2.0	803006P03M020	804006P03M020	805006P03M020	808006P02M020		
5.0	803006P03M050	804006P03M050	805006P03M050	808006P02M050		
10.0	803006P03M100	804006P03M100	805006P03M100	808006P02M100		
SJTO 2.0	803006S20M020	804006S20M020	805006S26M020			
5.0	803006S20M050	804006S20M050	805006S26M050			
10.0	803006S20M100	804006S20M100	805006S26M100			

Micro-Change® (M12) 90°




Cable Length (m)	WIRING CONFIGURATION			WIRING CONFIGURATION		
	5 Pole/3 Wire	5 Pole/4 Wire	5 Pole/5 Wire	5 Pole/3 Wire	5 Pole/4 Wire	5 Pole/5 Wire
PVC 2.0	803007E03M020	804007E03M020	805007E03M020			
5.0	803007E03M050	804007E03M050	805007E03M050			
10.0	803007E03M100	804007E03M100	805007E03M100			
PUR 2.0	803007P03M020	804007P03M020	805007P03M020	808007P02M020		
5.0	803007P03M050	804007P03M050	805007P03M050	808007P02M050		
10.0	803007P03M100	804007P03M100	805007P03M100	808007P02M100		
SJTO 2.0	803007S20M020	804007S20M020	805007S26M020			
5.0	803007S20M050	804007S20M050	805007S26M050			
10.0	803007S20M100	804007S20M100	805007S26M100			

Micro-Change® (M12) Field Attachable Connectors




4 Pole



5 Pole



4 Pole




5 Pole

Female Attachables


Gland size

Micro-Change® (M12) Straight



Gland size	4 Pole	5 Pole
PG7	8A4000-315	8A5000-315
PG9	8A4000-325	8A5000-325

Micro-Change® (M12) 90°




Gland size	4 Pole	5 Pole
PG7	8A4001-315	8A5001-315

Male Attachable


Gland size

Micro-Change® (M12) Straight



Gland size	4 Pole	5 Pole
PG7	8A4006-315	8A5006-315
PG9	8A4006-325	8A5006-325

Micro-Change® (M12) 90°




Gland size	4 Pole	5 Pole
PG7	8A4007-315	8A5007-315




Female Receptacle

Wire length (mm)




1 Brown 3 Blue
2 White 4 Black

4 Pole



1 Brown 4 Black
2 White 5 Grey
3 Blue

5 Pole




1 White 5 Grey
2 Brown 6 Pink
3 Green 7 Blue
4 Yellow 8 Red

8 Pole

WIRING CONFIGURATION

Micro-Change® Female M14 Panel Mount




300.0

8R4E30E03C3003

8R5E30E03C3003

8R8E30E03C3003

Micro-Change® Female PG9 Panel Mount




300.0

8R4J30E03C3003

8R5J30E03C3003

8R8J30E03C3003

Micro-Change® Female PG9 PCB Mount




n/a

8R4J400013

8R5J400013

n/a

Micro-Change® Female PG9 Through Panel



300.0

8R4J40E03C3003

8R5J40E03C3003

n/a


Male Receptacle

Wire Length (mm)




1 Brown 3 Blue
2 White 4 Black

4 Pole



1 Brown 4 Black
2 White 5 Grey
3 Blue

5 Pole




1 White 5 Grey
2 Brown 6 Pink
3 Green 7 Blue
4 Yellow 8 Red

8 Pole

WIRING CONFIGURATION

Micro-Change® Male M14 Panel Mount




300.0

8R4E36E03C3003

8R5E36E03C3003

8R8E36E03C3003

Micro-Change® Male PG9 Panel Mount




300.0

8R4J36E03C3003

8R5J36E03C3003

8R8J36E03C3003

Micro-Change® Male PG9 PCB Mount




n/a

8R4J460003

8R5J460003*

n/a

Micro-Change® Male PG9 Through Panel




300.0

8R4J46E03C3003

8R5J46E03C3003

n/a

Micro-Change® Male PG13.5 Short Sensor Mount



300.0

8R4D26E03C3003


8R5D26E03C3003

n/a




* Check sales office for availability

Choice of coupling materials, see page 40 for more information

mPm® DIN 43650 CONNECTORS



- **Integral LED indication and suppression, provide indication of function and elimination of potentially damaging induced spikes**
- **Simple screw termination of field attachable connectors or factory moulded and tested connectors for simple installation of devices**
- **Choice of Form A, B and C connectors to both DIN 43650 and industrial standards are compatible with solenoid valves from all leading manufacturers**






Moulded Connector

Cable

Length (m)

WIRING INFORMATION & CIRCUIT

		None	AC/DC 24 V VDR & LED	AC/DC 24 V Zener Diode & LED		
Form A (18mm) 2 pole + earth						
1 Brown 2 Blue 3 Yellow/ Green	PVC	2.0	E152N20011	E452N20011C4H	E452N20011SOH	
		5.0	E152N50011	E452N50011C4H	E452N50011SOH	
		10.0	E152N10K11	E452N10K11C4H	E452N10K11SOH	
	PUR/PVC	2.0	E152P20011	E452P20011C4H	E452P20011SOH	
		5.0	E152P50011	E452P50011C4H	E452P50011SOH	
		10.0	E152P10K11	E452P10K11C4H	E452P10K11SOH	
Form B Ind (11mm) 2 pole + 12 o'clock earth						
1 Brown 2 Blue 3 Yellow/ Green	PVC	2.0	E162N20021	E462N20021C4H	E462N20021SOH	
		5.0	E162N50021	E462N50021C4H	E462N50021SOH	
		10.0	E162N10K21	E462N10K21C4H	E462N10K21SOH	
	PUR/PVC	2.0	E162P20021	E462P20021C4H	E462P20021SOH	
		5.0	E162P50021	E462P50021C4H	E462P50021SOH	
		10.0	E162P10K21	E462P10K21C4H	E462P10K21SOH	
Form B Ind (11mm) 2 pole + 6 o'clock earth						
1 Brown 2 Blue 3 Yellow/ Green	PVC	2.0	E162N20061	E462N20061C4H	E462N20061SOH	
		5.0	E162N50061	E462N50061C4H	E462N50061SOH	
		10.0	E162N10K61	E462N10K61C4H	E462N10K61SOH	
	PUR/PVC	2.0	E162P20061	E462P20061C4H	E462P20061SOH	
		5.0	E162P50061	E462P50061C4H	E462P50061SOH	
		10.0	E162P10K61	E462P10K61C4H	E462P10K61SOH	
Form B DIN (10mm) 2 pole + 12 o'clock earth						
1 Brown 2 Blue 3 Yellow/ Green	PVC	2.0	E072N20021	E472N20021C4H	E472N20021SOH	
		5.0	E072N50021	E472N50021C4H	E472N50021SOH	
		10.0	E072N10K21	E472N10K21C4H	E472N10K21SOH	
	PUR/PVC	2.0	E072P20021	E472P20021C4H	E472P20021SOH	
		5.0	E072P50021	E472P50021C4H	E472P50021SOH	
		10.0	E072P10K21	E472P10K21C4H	E472P10K21SOH	




Moulded Connector

Cable

Length (m)


WIRING INFORMATION & CIRCUIT

Form B DIN (10mm) 2 pole + 6 o'clock earth




		None	AC/DC 24 V VDR & LED	AC/DC 24 V Zenner Diode & LED
1 Brown 3 Blue 4 Black	PVC 2.0	E072N20061	E472N20061C4H	E472N20061SOH
	5.0	E072N50061	E472N50061C4H	E472N50061SOH
	10.0	E072N10K61	E472N10K61C4H	E472N10K61SOH
	PUR/PVC 2.0	E072P20061	E472P20061C4H	E472P20061SOH
	5.0	E072P50061	E472P50061C4H	E472P50061SOH
	10.0	E072P10K61	E472P10K61C4H	E472P10K61SOH

Form C DIN (8.0mm) 2 pole + earth



1 Brown 3 Blue 4 Black	PVC 2.0	E432N20011	E492N20011C4H	E492N20011SOH
	5.0	E432N50011	E492N50011C4H	E492N50011SOH
	10.0	E432N10K11	E492N10K11C4H	E492N10K11SOH
	PUR/PVC 2.0	E432P20011	E492P20011C4H	E492P20011SOH
	5.0	E432P50011	E492P50011C4H	E492P50011SOH
	10.0	E432P10K11	E492P10K11C4H	E492P10K11SOH

Form C Ind (9.4mm) 2 pole + earth






1 Brown 3 Blue 4 Black	PVC 2.0	E332N20011	E392N20011C4H	E392N20011SOH
	5.0	E332N50011	E392N50011C4H	E392N50011SOH
	10.0	E332N10K11	E392N10K11C4H	E392N10K11SOH
	PUR/PVC 2.0	E332P20011	E392P20011C4H	E392P20011SOH
	5.0	E332P50011	E392P50011C4H	E392P50011SOH
	10.0	E332P10K11	E392P10K11C4H	E392P10K11SOH










Attachable Connector

Gland Size



WIRING INFORMATION & CIRCUIT

	None	AC/DC 24 V VDR & LED	AC/DC 24 V Zenner Diode & LED		
Form A (18mm) 2 pole + earth					
					
					
PG9	C18209N21	S18209TC421	S18209TS021		
PG11	C18211N21	S18211TC421	S18211TS021		
Form B Ind (11mm) 2 pole + earth					
					
					
PG7	C12207N21	S02207TC421	S02207TS021		
PG9	C12209N21	S02209TC421	S02209TS021		
Form B DIN (10mm) 2 pole + earth					
					
					
PG7	C62207N21	S62207TC421	S62207TS021		
PG9	C62209N21	S62209TC421	S62209TS021		
Form C DIN (8.0mm) 2 pole + earth					
					
					
PG7	C05207N62	S05207TC422	n/a		
Form C Ind (9.4mm) 2 pole + earth					
					
					
PG7	C19207N62	S19207TC422	n/a		

OPTIONS

Multi-Port Splitter Box Matrix

B T Y 8 0 0 P - F B P - 0 5

Nano-Change® Multi-Ports
BEY - End Cable Entry
BNY - Top Cable Entry & Connector
Micro-Change® Multi-Ports
BTY - Top Mount
BSY - Side Mount

Length
05 - 5 metres
10 - 10 metres
20 - 20 metres

Number of Ports
4 - 4 Ports 8 - 8 Ports
6 - 6 Ports A - 10 Ports

Wiring Configuration
00/01 - 5 Pole/4 Wire - Single I/O per port
03/05 - 5 Pole/5 Wire - Twin I/O per port
04 - 4 Pole/3 Wire - Single I/O per port - no earth

LED Configuration
P - PNP Format N - NPN Format** 0 - No LEDs**

Termination Options
Pre-wired versions*
E - PVC Cable
P - PUR Cable
M - PUR/PVC Cable
Connectorised versions
B - Mini-Change® Connector
C - M16 or M23 Connector

Receptacle Material
FB - Standard
FX - Plastic**
FS - Stainless Steel**

Connector Matrix

8 0 3 0 0 0 E 0 3 M 0 2 0

Options:

Not all are available on standard delivery terms, please consult our sales office before ordering

* Refer to cable specification and use code indicated in matrix above

**NPN or no LED indication, select from above part number matrixes, minimum order quantity 25 pieces for Connectors and 5 pieces for Multi-Ports

**Coupling materials and connector colour minimum quantities apply to all orders

**Choice of suppression and LED colour for mPm® product, please request separate catalogue

Connector Type
Nano-Change® M8 Snap
50 - Moulded Connector
55 - Nano Jumper
58 - Nano to Micro Jumper

Nano-Change® M8 Coupler
40 - Moulded Connector
44 - Nano Jumper
48 - Nano to Micro Jumper

Micro-Change® M12 Coupler
80 - Moulded Connector
88 - Micro Jumper
84 - Micro to Nano Jumper

mPm® DIN 43650 Jumpers
D4 - Form B (10mm) to Nano
E4 - Form A (18mm) to Nano
F4 - Form B (11mm) to Nano
G4 - Form C (9.4mm) to Nano
H4 - Form C (8.0mm) to Nano
D8 - Form B (10mm) to Micro
E8 - Form A (18mm) to Micro
F8 - Form B (11mm) to Micro
G8 - Form C (9.8mm) to Micro
H8 - Form C (8.0mm) to Micro

Cable ID No.*
E03 - Yellow PVC 0.34mm²
P03 - Black PUR 0.34mm²
S20 - Yellow SJTO type 0.34mm²

Cable Length
M010 - 1.0 metres
M020 - 2.0 metres
M030 - 3.0 metres

Coupling Materials**
1 - Stainless Steel 5 - Plastic

Connector Colour**
A - Grey Head Moulding G - Black Head Moulding

Head Configuration
Moulded Connectors
000 - Female Straight
001 - Female 90°
0N0 - Female Straight NPN LED**
0N1 - Female 90° NPN LED**
0P0 - Female Straight PNP LED
0P1 - Female 90° PNP LED
006 - Male Straight
007 - Male 90°
Jumpers - Basic Brad® Only
030 - Female Straight to Male Straight
031 - Female 90° to Male Straight
032 - Female Straight to Male 90°
033 - Female 90° to Male 90°
0P6 - Female Straight PNP LED to Male Straight
0P7 - Female 90° PNP LED to Male Straight
0P8 - Female Straight PNP LED to Male 90°
0P9 - Female 90° PNP LED to Male 90°

Number of Poles
3 - 3 Pole 5 - 5 Pole
4 - 4 Pole 8 - 8 Pole

CONNECTOR SPECIFICATION

Series	40, 4R, 44, 50, 5R, 55	N03, N04	80, 8R, 88	8A	30		L0	K0
Product	Nano-Change®	Nano-Change®	Micro-Change®	Micro-Change®	Mini-Change®	mPm® DIN 43650	M16 Connector	M23 Connector
Connector Type	Moulded & Receptacles	Attachables	Moulded & Receptacles	Attachables	Moulded	Moulded & Attachable	Moulded	Moulded
Connector Size	M8 Coupler & Snap	M8 Coupler	M12 Coupler	M12 Coupler	1 1/8" UNF Coupler	Form A, B & C	M16 Coupler	M23 Coupler
Number of Poles	3 to 5	3 & 4	3, 4, 5 & 8	4 & 5	12 & 19	2 + earth	14	12 & 19
Contact Material	Female	Gold plated Brass	Gold plated Brass	Gold Plated Brass	Gold plated Brass	Silver plated Brass	Gold plated Brass	Gold plated Brass
	Male	Gold plated Brass	Gold plated Brass	Gold plated Brass	Gold plated Brass	n/a	n/a	Gold plated Brass
Insert Material	PUR	PA	PA	PA	PVC	PA (+G)	PPO	PUR
O-ring Material	Viton	Viton	Viton	Viton	n/a	Profiled NBR	EPDM - Rubber	NBR
Body Material	PVC	PA	PVC	PA	PVC	PP	PUR	PUR
Coupling Material	Nickel plated Brass	Nickel plated Brass	Epoxy Coated Zinc	Nickel plated Brass	Epoxy Coated Zinc	n/a	Aluminium	Nickel plated Brass
Voltage Rating	Standard	60 Vac/75 Vdc	3, 4 & 5 pole - 250 Vac/300 Vdc	4 pole - 250 Vac/300 Vdc	600 Vac/dc	250 Vac/dc	150 Vac/dc	63 Vac/dc
			8 pole - 30 Vac/36 Vdc	5 pole - 30 Vac/36 Vdc				
With LED	10 to 30 Vdc	n/a	10 to 30 Vdc	n/a	n/a	24 Vac/dc	n/a	n/a
Contact Current Rating	4 Amps	4 Amps	4 Amps	4 Amps	Ø 1.0mm - 4 Amps	Form A & B - 18 Amps Form C - 10 Amps	3 Amps	Ø 1.0mm - 6 Amps
					Ø 2.0mm - 13 Amps			Ø 1.5mm - 12 Amps
Protection Class	IP67	IP67	IP68	IP68	IP68	IP65	IP67	IP67

Environmental Rating - IP68. To avoid confusion, we at Woodhead Connectivity have defined IP68 as immersion in water at a pressure of 100 pounds per square inch for a duration of one hour, and wash down at a pressure of 1000 pounds per square inch. When used with a mating pair of Brad Harrison® connectors.

MULTI-PORT SPECIFICATION


Series	BEY & BNY	BEY & BNY	BTY	BTY	BSY
Product	Nano-Change - Single I/O	Nano-Change - Twin I/O	Micro-Change Top Mount Single I/O	Micro-Change Top Mount Twin I/O	Micro-Change Side Mount Single I/O
I/O Connectors	M8 Coupler	M8 Coupler	M12 Coupler	M12 Coupler	M12 Coupler
Number of I/O	4, 6, 8 & 10	8, 12, 16 & 20	4, 6 & 8	8, 12 & 16	4, 6 & 8
Contact Material	Gold plated Brass	Gold plated Brass	Gold plated Brass	Gold plated Brass	Gold plated Brass
Insert Material	PUR	PUR	PBT	PBT	PA
O-ring Material	Viton	Viton	Viton	Viton	Viton
Body Material	PBT	PBT	PBT	PBT	PA
Coupling Material	Nickel plated Brass	Nickel plated Brass	Nickel plated Brass	Nickel plated Brass	Epoxy coated Zinc
Voltage Rating with LED	10 to 30 Vdc	10 to 30 Vdc	10 to 30 Vdc	10 to 30 Vdc	10 to 30 Vdc
Current Rating Per I/O	2 Amps	1 Amps	2 Amps	2 Amps	2 Amps
Total Unit - Cable Version	6 Amps	6 Amps	12 Amps	12 Amps	12 Amps
Total Unit - Connector Version	6 Amps	3 Amps	12 Amps	12 Amps	12 Amps
Protection Class	Cable - IP68 M16 Connector - IP67	Cable - IP68 M16 Connector - IP67	Cable - IP68 M23 Connector - IP67 Mini-Change - IP68	Cable - IP68 M23 Connector - IP67 Mini-Change - IP68 Attachable - IP67	Cable - IP68 Mini-Change - IP68

CABLE SPECIFICATION

ID No	No of Cores	Jacket Colour	Cross Section	Stranding Group	Screen	Nominal Diameter	Nano-Change	Micro-Change	Mini-Change	M23 Connctr.	M16 Connctr.	mPm DIN 43650	Nano Multi Ports	Micro Multi Ports
PVC - General Purpose - Conveyors, Food Processing, etc - 300 V, -5°C to +70°C, PVC Outer Jacket over PVC Insulation														
E02	3 & 4	Yellow	0.25mm ²	B	None	4.5mm	✓	✓						
E03	3 & 4	Yellow	0.34mm ²	C	None	5.0mm	✓	✓						
	5					5.5mm		✓						
E12	3	Black	0.50mm ²	E	None	5.5mm	✓	✓				✓		
E18	3 & 4	Yellow	0.20mm ²	C	80% Braid	5.0mm	✓	✓						
E51	4	Grey	0.25mm ²	B	None	4.5mm	✓	✓						
E52	3 & 4	Grey	0.34mm ²	C	None	5.0mm	✓	✓						
	5					5.5mm		✓						
PVC for Multi-Ports - General Purpose - Conveyors, Food Processing, etc - 300 V, -5°C to +70°C, PVC Outer Jacket over PVC Insulation														
E80	7	Yellow	4x0.34 & 3x0.75mm ²	C & E	None	8.4mm			✓	✓				✓
	9					9.5mm			✓	✓				✓
	11					9.5mm			✓	✓				✓
	15					9.8mm			✓	✓				✓
	19					11.4mm			✓	✓				✓
CEI PVC - IEC332.3A - Self Extinguishing, Flame Retardant Oil Resistant PVC - 300 V, -5°C to +70°C, CEI PVC Outer Jacket over CEI PVC Insulation														
I02	3 & 4	Grey	0.25mm ²	B	None	4.5mm	✓	✓						
I03	3 & 4	Grey	0.34mm ²	C	None	5.0mm	✓	✓						
	5					5.5mm		✓						
I20	3	Grey	0.34mm ²	C	80% Braid	5.0mm		✓						
	4					6.3mm		✓						
SJTO Type - UL listed/CSA Approved - Self Extinguishing & Flame Retardant - Good weld splatter resistance & rough duty use - 300 V, -40°C to +105°C, UL/CSA PVC Outer Jacket over UL/CSA PVC Insulation														
S20	3 & 4	Yellow	0.34mm ²	D	50% Braid	6.3mm		✓				✓		
S26	5	Yellow	0.34mm ²	D	50% Braid	6.5mm		✓				✓		
PUR - General Purpose, Oil resistant for machining applications - 300 V, -5°C to +90°C, PUR Outer Jacket over PVC Insulation														
P03	3 & 4	Black	0.34mm ²	C	None	5.0mm	✓	✓						
	5					5.5mm		✓						
P08	3 & 4	Yellow	0.25mm ²	A	None	4.5mm	✓	✓						
P09	3 & 4	Black	0.34mm ²	A	None	5.0mm		✓						
P12	3	Black	0.50mm ²	E	None	5.5mm	✓	✓				✓		
P18	4 & 5	Black	0.20mm ²	C	80% Braid	5.0mm	✓	✓						
PUR for Multi-Ports - General Purpose, Oil resistant for machining applications - 300 V, -5°C to +90°C, PUR Outer Jacket over PVC Insulation														
P80	7	Yellow	4x0.34 & 3x0.75mm ²	C & E	None	8.4mm			✓	✓				✓
	9					9.5mm			✓	✓				✓
	11					9.5mm			✓	✓				✓
	15					9.8mm			✓	✓				✓
	19					11.4mm			✓	✓				✓
P78	6	Black	4x0.34 & 2x0.75mm ²	C & C	None	8.4mm			✓	✓	✓		✓	✓
	8					9.5mm			✓	✓	✓		✓	✓
	10					9.8mm			✓	✓	✓		✓	✓
	12					9.8mm			✓	✓	✓		✓	✓
	14					9.8mm			✓	✓	✓		✓	✓
	18					11.4mm			✓	✓	✓		✓	✓
P75	22		20x0.25 & 2x0.50mm ²	C & C		11.4mm			✓	✓	✓		✓	✓
LSOH PUR - Low Smoke Zero Halogen - Baggage handling, public building use - 300 V, -40°C to +70°C, LSOH PUR Outer Jacket over Polyethylene Insulation														
H03	4	Yellow	0.34mm ²	C	None	5.0mm	✓	✓						
H69	4	Grey	0.20mm ²	C	Foil with Drain	4.5mm	✓	✓						
P20	3	Black	0.34mm ²	C	80% Braid	5.0mm		✓						
	4					5.5mm		✓						
	5					5.8mm		✓						
Irradiated PUR - Machine tool and welding applications - 300 V, -5°C to +105°C, Irradiated PUR Outer Jacket over PVC Insulation														
P82	3 & 4	Orange	0.34mm ²	E	None	5.0mm		✓						


Stranding and Cross Sectional Area Table

Stranding Group	0.20mm ²	0.25mm ²	0.34mm ²	0.50mm ²	0.75mm ²	Diameter of Strands
A		128	174			0.05mm
B		65				0.07mm
C	27	32	42	64	95	0.10mm
D			26			0.13mm
E			19	28	42	0.15mm




Nano-Change® M16 Con Multi-Port

No. of Ports	Length A (mm)	Length B (mm)
4	88	79
6	113	104
8	138	129
10	163	154




M16 Home Run Connectors for Nano-Change® Multi-Port




Micro-Change® Top Mount Mini-Change

No. of Ports	Length A (mm)
4	120
6	125
8	152




Micro-Change® Cable End Multi-Port

No. of Ports	Length A (mm)	Length B (mm)
4	78	68
6	104	94
8	129	119




M23 Home Run Connectors for Micro-Change® Multi-Port

Mini-Change® Home Run Connectors for Micro-Change® Multi-Port




Nano-Change (M8) Snap Moulded Connectors




Micro-Change® (M12) Moulded Connectors - Female

Micro-Change® (M12) Moulded Connectors - Male




Micro-Change® (M12) Field Attachable Connectors - Female

Micro-Change® (M12) Field Attachable Connectors - Male



mPm® DIN 43650 Moulded Connectors



mPm® DIN 43650 Attachable Connectors

United Kingdom

Woodhead Connectivity Ltd.
Factory No. 9
Rassau Industrial Estate
Ebbw Vale, Gwent,
Wales NP23 5SD
Tel. 01495-350436
Fax. 01495-350877

France

Woodhead Connectivity S.A.
57, Rue Jacquard Z.I.
77400 Lagny Sur Marne
Tel. 01 64 30 91 36
Fax. 01 64 30 91 05

Germany

Woodhead Connectivity GmbH
Gewerbestraße 60
75015 Bretten-Gölshausen
Tel. 07252-9496-0
Fax. 07252-9496-99

Italy

mPm S.r.l.
Via Zucchi
39 int. G
20095 Cusano Milanino (MI)
Tel. 02-66400321
Fax. 02-66400334

USA

Woodhead Connectivity N.A.
3411 Woodhead Drive
Northbrook
IL 60062
Tel. 847-272-7990
Fax. 847-272-8133

Woodhead Connectivity N.A.
130 Constitution Boulevard
Franklin
MA 02038
Tel. 508-541-3400
Fax. 508-541-3419

Woodhead Connectivity N.A.
11501 James Watt Drive
El Paso
TX 79936
Tel. 915-591-5600
Fax. 915-598-1718

Canada

SST
50 Northland Road
Waterloo
Ontario, N2V 1N3
Tel. 519-725-5136
Fax. 519-725-1515

Woodhead Canada Limited
1090 Brevik Place
Mississauga
Ontario, L4W 3Y5
Tel. 905-624-6518
Fax. 905-624-9151

Mexico

Woodhead de
Mexico S.A. de C.V.
Parque Industrial
Internacional Mexicano
Calle Intermex No. 1351
Cd. Juarez, Chih. 32340
Tel. 52-1624-2504
Fax. 52-1624-4029

Singapore

Woodhead Asia Pte. Ltd.
8 Chia Ping Road,
#05-09/10
JTC Flatted Factory
Jorung Town, 619973
Tel. 261-6533
Fax. 265-6605

Japan

Woodhead Japan Corporation
Unit 4309
Yokohama Landmark Tower
2-2-1 Minatomirai
Nishi-ku, Yokohama-shi
Kanagwa-ken 220-8143
Tel. 04-5224-3560
Fax. 04-5224-3561

Woodhead Connectivity

SST® ▪ Brad Harrison® ▪ mPm®

The Global Leader in Industrial Communications

www.woodheadconnectivity.com

Nano-Change®, Micro-Change®, Mini-Change®, MPIS®, Brad®, Brad Harrison® and mPm® are all registered trademarks of Woodhead Industries, Inc.

Every effort has been made to ensure that the information contained within the catalogue is correct and as accurate as possible, no warranty as to this accuracy of this information is implied in any way. With our policy of continuous development, we reserve the right to change any detail within the catalogue without further notice.

All detailed contained within the catalogue are the sole copyright of Aero-Motive (UK) Limited, a Woodhead Industries, Inc. subsidiary and may not be copied or reproduced in any way without prior written consent. All other trade names and designs acknowledged.