



Price\* : 9.00 GBP



### Main

Range	TeSys
Device short name	GVAE
Product or component type	Auxiliary contact block
Product compatibility	GV2L GV2LE GV2ME GV2P GV2RT GV3L GV3P LS1D323
Mounting location	Front side
Pole contact composition	1 NO + 1 NC
Connections - terminals	Spring terminals 2 cable 0.75...1.5 mm <sup>2</sup> - cable stiffness: flexible - without cable end
Quantity per set	Set of 10

### Complementary

[Ui] rated insulation voltage	300 V - conforming to UL 508 300 V - conforming to CSA C22.2 No 14 250 V - conforming to IEC 60947-1
[Ue] rated operational voltage	24...240 V AC 24...60 V DC
[Ith] conventional free air thermal current	2.5 A
Protection type	GG fuse 10 A GB2CB06 circuit breaker 10 A
Mechanical durability	100000 cycles
Minimum switching current	5 mA
Minimum switching voltage	17 V
Rated operational power in VA	120 VA at 110...120 V AC-15 - electrical durability: 100000 cycles

	120 VA at 230...240 V AC-15 - electrical durability: 100000 cycles 48 VA at 24 V AC-15 - electrical durability: 100000 cycles 60 VA at 48 V AC-15 - electrical durability: 100000 cycles
Rated operational power in W	15 W at 48 V DC-13 - electrical durability: 100000 cycles 24 W at 24 V DC-13 - electrical durability: 100000 cycles 9 W at 60 V DC-13 - electrical durability: 100000 cycles
Height	13 mm
Width	44.5 mm
Depth	31.5 mm
Product weight	0.05 kg

## Environment

Environmental characteristic	Normal environment
------------------------------	--------------------

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0701 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------