

## Mini-Lynx GLS

ML GLS 827 E27 11W SLV

0035501

### Range features



CE

### PRODUCT OVERVIEW

Ordering number	0035501
Technology	Compact Fluorescent
Light colour	827 Homelight
Energy class	A
Average life (Rated) (h)	10000
Lamp shape	GLS
Lamp finish	FROSTED
Dimmable	No
Cap/Base	E27
Type	GLS
EAN code	5410288355016
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	630
Efficacy (Rated) (lm/w)	57.272727273
Watt (Nominal) (W)	11
Equivalent watt (W)	50
Voltage (V)	220-240

# Mini-Lynx GLS

ML GLS 827 E27 11W SLV

0035501

## DATA TABLE

### General data

Ordering number	0035501
Dry applications use only	Yes
Technology	Compact Fluorescent
Energy saving lamp	Yes
Energy class	A
Average life (Rated) (h)	10000
Average life (Nominal) (h)	10000
Lamp finish	FROSTED
Lamp shape	GLS
Dimmable	No
Cap/Base	E27
Type	GLS
EAN code	5410288355016
E-number FI	4940414
E-number SE	8357582
Product name	ML GLS 827 E27 11W SLV
Lamp mercury content (mg)	<2
Starting time (max) (s)	< 1.0 Sec
Warm-up time to 60% of full light (max) (s)	< 100 s
Control gear required	NO
Intended purpose	General lighting
No. of switching cycles before premature failure (min)	30000
Special purpose lamp	No
Transformer required	No
Sales pack quantity	10
Optimal operating condition (°C)	25° C, cap-up, Stated lumen output may vary if operated in non-standard position

### Optical data

Light colour	827 Homelight
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	630
Lumen maintenance at end of nominal life (%)	=60%
Luminous flux (Nominal) (lm)	630

# Mini-Lynx GLS

*ML GLS 827 E27 11W SLV*

**0035501**

## Electrical data

<b>kWh per 1000 hours burning time</b>	11
<b>Efficacy (Rated) (lm/w)</b>	57.272727273
<b>Watt (Rated) (W)</b>	11
<b>Watt (Nominal) (W)</b>	11
<b>Equivalent watt (W)</b>	50
<b>Voltage (V)</b>	220-240
<b>Lamp power factor</b>	> 0.55

## Physical data

<b>Lamp Length (mm) - C/L</b>	123
<b>Lamp Diameter (mm) - D</b>	60


## Mini-Lynx GLS

ML GLS 827 E27 11W SLV

0035501

### TECHNICAL DRAWINGS

---



### ENERGY LABEL

---

