





ASSEMBLY PROCEDURE:

- STEP 1: PULL MOUNT TO PANEL - GRIP BREAKS-AWAY AFTER FIXING
- STEP 2: LOCATE AND ASSEMBLE FAN HOUSING

REV.	MODIFICATION.	DATE	DRN
01	Production Release	24/04/07	TC
02	ECN 2007-110	04/07/07	TC
03	ECN 2007-189	29/10/07	SF



PART No	PANEL HOLE DIAMETER	PANEL THICKNESS	FAN HOLE DIAMETER	FAN CASE THICKNESS
FMB-1	4.5 - 5.0mm [0.18 - 0.20]	0.8 - 1.6mm [0.03 - 0.06]	4.0 - 4.5mm [0.16 - 0.18]	25 - 51mm [0.98 - 2.01]
FMB-2	4.5 - 5.0mm [0.18 - 0.20]	0.8 - 1.6mm [0.03 - 0.06]	3.2 - 3.5mm [0.13 - 0.14] 4.0 - 4.5mm [0.16 - 0.18]	Up to 10mm [0.40] Max Up to 25mm [0.98]




INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT.



ALL DIMENSIONS IN mm & [INCH]
GENERAL TOLERANCES ±0.25 [0.01]
UNLESS OTHERWISE STATED
1 DECIMAL PLACE ±0.25 [0.01]
2 DECIMAL PLACES ± 0.10 [0.004]
ANGULAR ±1°

THIRD ANGLE



MATERIAL: SILICONE RUBBER 35 Sh A (RMS-316)				COLOUR: BLACK	
DESCRIPTION: BREAK AWAY FAN MOUNT				PART No: FMB-1 / FMB-2	
DRG No: 07-033		NPR No: 2006-312		Mass:(g) FMB-1 = 1.5g FMB-2 = 1.1g	SHEET SIZE A4
DRN TC	DATE 25/10/06	CHKD TC	DATE 28/11/06	SCALE NTS	SHEET No. 2 OF 2