


Kraftform Kompakt VDE




Kraftform Kompakt VDE

Versatile tools for work on live wiring



The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

Each Kraftform Kompakt VDE set has been tested individually in a water bath at 10,000 volts, in accordance with DIN EN 60900 (IEC 60900:2004). This ten-times-higher testing load guarantees safe working at their maximum permitted load of 1,000 volts.



Kraftform Kompakt VDE sets come with an insulated handle and insulated interchangeable blades, that can be exchanged without any special tools.



The tools can be stored and carried in a robust belt pouch, keeping them always to hand.



The 18-/16-piece set includes blades for PlusMinus screws, various keys for switch cabinets and a voltage tester.



Kraftform Kompakt VDE

Versatile tools for work on live wiring

Kraftform Kompakt VDE 60 i/7



1 Kraftform hand-held bit holder 817 VDE for Wera interchangeable blades
VDE interchangeable blades (each 154 mm long)

7-piece set

| Code | | | |
|-------------|-----------|---|---|
| 05003470001 | ● 817 VDE | 1 x 9x102 | 1 |
| | ● KK 60 i | 1 x 0,4x2,5x154; 1 x 0,6x3,5x154; 1 x 0,8x4,0x154; 1 x 1,0x5,5x154 | |
| | ⊕ KK 62 i | 1 x PH 1x154; 1 x PH 2x154 | |

Kraftform Kompakt VDE 60 i/68 i/7



1 Kraftform hand-held bit holder 817 VDE for Wera VDE interchangeable blades
VDE interchangeable blades (each 154 mm long)

7-piece set

| Code | | | |
|-------------|---------------|----------------------------------|---|
| 05003473001 | ● 817 VDE | 1 x 9x102 | 1 |
| | ● KK 60 i | 1 x 0,6x3,5x154; 1 x 1,0x5,5x154 | |
| | ⊕ KK 62 i | 1 x PH 1x154; 1 x PH 2x154 | |
| | ○ KK VDE 68 i | 1 x # 1x154; 1 x # 2x154 | |

Kraftform Kompakt VDE 60 i/65 i/7



1 Kraftform hand-held bit holder 817 VDE for Wera interchangeable blades
VDE interchangeable blades (each 154 mm long)

7-piece set

| Code | | | |
|-------------|--------------|---|---|
| 05003472001 | ● 817 VDE | 1 x 9x102 | 1 |
| | ● KK 60 i | 1 x 0,4x2,5x154; 1 x 0,6x3,5x154; 1 x 0,8x4,0x154; 1 x 1,0x5,5x154 | |
| | ⊕ KK 65 i PZ | 1 x PZ 1x154; 1 x PZ 2x154 | |



How to avoid bruising and injuries to the hands



Screwdriving by hand can actually be quite painful, and Wera developed the Kraftform handle with this in mind. Its design fits exactly to the hand. And the materials used combine to prevent blisters, calluses and strain. This is particularly noticeable when changing the position of grip. This makes the concept of ergonomics "graspable".

Kraftform Kompakt VDE

Versatile tools for work on live wiring

Kraftform Kompakt VDE 60 i/65 i/67 I/16



1 Kraftform hand-held bit holder 817 VDE for Wera VDE interchangeable blades

VDE interchangeable blades (each 154 mm long)

Single-pole voltage tester

16-piece set

| Code | Icon | Item | Quantity | Unit |
|-------------|------|---------------|---|------|
| 05003474001 | ● | 817 VDE | 1 x 9x102 | 1 |
| | ● | 247 | 1 x 0,5x3,0x70 | |
| | ● | KK 60 i | 1 x 0,4x2,5x154; 1 x 0,6x3,5x154; 1 x 0,8x4,0x154; 1 x 1,0x5,5x154 | |
| | ⊕ | KK 62 i | 1 x PH 1x154; 1 x PH 2x154 | |
| | ⊕ | KK 65 i PZ | 1 x PZ 1x154; 1 x PZ 2x154 | |
| | ⊕ | KK 65 i PZ/S | 1 x # 1x154; 1 x # 2x154 | |
| | ⊕ | KK 67 i TORX® | 1 x TX 25x154; 1 x TX 10x154; 1 x TX 15x154; 1 x TX 20x154 | |

Kraftform Kompakt VDE 60 i/62 i/65 i/18



1 Kraftform hand-held bit holder 817 VDE for Wera VDE interchangeable blades

VDE interchangeable blades (each 154 mm long)

Single-pole voltage tester

18-piece set

| Code | Icon | Item | Quantity | Unit |
|-------------|------|--------------|---|------|
| 05003471001 | ● | 817 VDE | 1 x 9x102 | 1 |
| | ● | 247 | 1 x 0,5x3,0x70 | |
| | ● | KK 60 i | 1 x 0,4x2,5x154; 1 x 0,6x3,5x154; 1 x 0,8x4,0x154; 1 x 1,0x5,5x154 | |
| | ⊕ | KK 62 i | 1 x PH 1x154; 1 x PH 2x154 | |
| | ⊕ | KK 62 i PH/S | 1 x # 1x154; 1 x # 2x154 | |
| | ⊕ | KK 65 i PZ | 1 x PZ 1x154; 1 x PZ 2x154 | |
| | ⊕ | KK 65 i PZ/S | 1 x # 1x154; 1 x # 2x154 | |
| | ● | KK 96 VK 6,3 | 1 x 6,3x89 | |
| | ● | KK 97 VK 8,1 | 1 x 8,1x89 | |
| | ⊕ | KK 98 DK | 1 x 89 | |
| | ⊕ | KK 99 FL | 1 x 89 | |



How to avoid bruising and injuries to the hands



Screwdriving by hand can actually be quite painful, particularly during extended use. Wera developed the Kraftform handle with this in mind. Its design fits exactly to the hand, and this ergonomic handle, which perfectly fits the hand, and the

materials used combine to prevent blisters, calluses and strain. This is particularly noticeable when changing the position of grip. This makes the concept of ergonomics "graspable".

817 VDE Kraftform hand-held bit holder



Application: Wera interchangeable VDE blades

Handle: Kraftform with non-roll feature, multi-component

| Code | Icon | mm | Unit |
|-------------|------|-------|------|
| 05003990001 | ● | 9 102 | 1 |

Kraftform Kompakt VDE 60 i



- Application:** Slotted screws
Blade: Insulated, individually tested as per IEC 60900 : 2004
Drive: 9 mm hexagonal with entry chamfer
Design: Conical blade, zinc-phosphated, Black Point

| Code | mm | mm | mm | | | |
|-------------|-----|-----|-----|------------------|--------------------|---|
| 05003400001 | 0,4 | 2,5 | 154 | $\frac{3}{32}$ " | $6 \frac{1}{16}$ " | 5 |
| 05003401001 | 0,5 | 3,0 | 154 | $\frac{1}{8}$ " | $6 \frac{1}{16}$ " | 5 |
| 05003402001 | 0,6 | 3,5 | 154 | $\frac{9}{64}$ " | $6 \frac{1}{16}$ " | 5 |
| 05003403001 | 0,8 | 4,0 | 154 | $\frac{5}{32}$ " | $6 \frac{1}{16}$ " | 5 |
| 05003404001 | 1,0 | 5,5 | 154 | $\frac{7}{32}$ " | $6 \frac{1}{16}$ " | 5 |
| 05003405001 | 1,2 | 6,5 | 154 | $\frac{1}{4}$ " | $6 \frac{1}{16}$ " | 5 |

Kraftform Kompakt VDE 62 i



- Application:** Phillips screws
Blade: Insulated, individually tested as per IEC 60900 : 2004
Drive: 9 mm hexagonal with entry chamfer
Design: Zinc-phosphated, Black Point

| Code | mm | | | |
|-------------|------|-----|--------------------|---|
| 05003410001 | PH 0 | 154 | $6 \frac{1}{16}$ " | 5 |
| 05003411001 | PH 1 | 154 | $6 \frac{1}{16}$ " | 5 |
| 05003412001 | PH 2 | 154 | $6 \frac{1}{16}$ " | 5 |

Kraftform Kompakt VDE 65 i



- Application:** Pozidriv^{*)} screws
Blade: Insulated, individually tested as per IEC 60900 : 2004
Drive: 9 mm hexagonal with entry chamfer
Design: Zinc-phosphated, Black Point

| Code | mm | | | |
|-------------|------|-----|--------------------|---|
| 05003450001 | PZ 0 | 154 | $6 \frac{1}{16}$ " | 5 |
| 05003451001 | PZ 1 | 154 | $6 \frac{1}{16}$ " | 5 |
| 05003452001 | PZ 2 | 154 | $6 \frac{1}{16}$ " | 5 |

*) Pozidriv = reg. trademark of European Industrial Service Ltd.

Kraftform Kompakt VDE 62 i PH/S



- Application:** PlusMinus screws, slotted/Phillips
Blade: Insulated, individually tested as per IEC 60900 : 2004
Drive: 9 mm hexagonal with entry chamfer
Design: PlusMinus, slotted/Phillips, zinc-phosphated, Black Point

| Code | mm | | | |
|-------------|-----|-----|--------------------|---|
| 05003440001 | # 1 | 154 | $6 \frac{1}{16}$ " | 5 |
| 05003441001 | # 2 | 154 | $6 \frac{1}{16}$ " | 5 |

Kraftform Kompakt VDE 65 i PZ/S



- Application:** PlusMinus screws, slotted/Pozidriv^{*)}
Blade: Insulated, individually tested as per IEC 60900 : 2004
Drive: 9 mm hexagonal with entry chamfer
Design: PlusMinus, slotted/Pozidriv, zinc-phosphated, Black Point

| Code | mm | | | |
|-------------|-----|-----|--------------------|---|
| 05003445001 | # 1 | 154 | $6 \frac{1}{16}$ " | 5 |
| 05003446001 | # 2 | 154 | $6 \frac{1}{16}$ " | 5 |

*) Pozidriv = reg. trademark of European Industrial Service Ltd.

Kraftform Kompakt VDE 68 i



- Application:** Square socket head screws
Blade: Insulated, individually tested as per IEC 60900 : 2004
Drive: 9 mm hexagonal with entry chamfer
Design: Zinc-phosphated, Black Point

| Code | mm | | | |
|-------------|-----|-----|--------------------|---|
| 05003415001 | # 1 | 154 | $6 \frac{1}{16}$ " | 5 |
| 05003416001 | # 2 | 154 | $6 \frac{1}{16}$ " | 5 |

Kraftform Kompakt VDE

Versatile tools for work on live wiring

Kraftform Kompakt VDE 64 i



Application: Hexagon socket screws
Blade: Insulated, individually tested as per IEC 60900 : 2004
Drive: 9 mm hexagonal with entry chamfer
Design: Zinc-phosphated, Black Point

| Code | mm | mm | mm | |
|-------------|-----|-----|---------|---|
| 05003420001 | 2,5 | 154 | 6 1/16" | 5 |
| 05003421001 | 3,0 | 154 | 6 1/16" | 5 |
| 05003422001 | 4,0 | 154 | 6 1/16" | 5 |
| 05003423001 | 5,0 | 154 | 6 1/16" | 5 |
| 05003424001 | 6,0 | 154 | 6 1/16" | 5 |

Kraftform Kompakt VDE 67 i TORX®



Application: TORX® socket screws
Blade: Insulated, individually tested as per IEC 60900 : 2004
Drive: 9 mm hexagonal with entry chamfer
Design: Zinc-phosphated, Black Point

| Code | mm | mm | mm | |
|-------------|-------|-----|---------|---|
| 05003430001 | TX 9 | 154 | 6 1/16" | 5 |
| 05003431001 | TX 10 | 154 | 6 1/16" | 5 |
| 05003432001 | TX 15 | 154 | 6 1/16" | 5 |
| 05003433001 | TX 20 | 154 | 6 1/16" | 5 |
| 05003434001 | TX 25 | 154 | 6 1/16" | 5 |
| 05003435001 | TX 27 | 154 | 6 1/16" | 5 |
| 05003436001 | TX 30 | 154 | 6 1/16" | 5 |

Kraftform Kompakt 96 VK 6,3



Switch cabinet key, 6.3 mm □ = 6 mm

| Code | mm | mm | mm | |
|-------------|-----|----|---------|---|
| 05003460001 | 6,3 | 89 | 3 9/16" | 5 |

Kraftform Kompakt 97 VK 8,1



Switch cabinet key, 8.1 mm □ = 8 mm

| Code | mm | mm | mm | |
|-------------|-----|----|---------|---|
| 05003461001 | 8,1 | 89 | 3 9/16" | 5 |

Kraftform Kompakt 98 DK



Switch cabinet key △ = 8 mm

| Code | mm | mm | mm | |
|-------------|----|----|---------|---|
| 05003462001 | | 89 | 3 9/16" | 5 |


Kraftform Kompakt 99 FL




Switch cabinet key ⊘ = 14 mm

| Code | mm | mm | mm | |
|-------------|----|----|---------|---|
| 05003463001 | | 89 | 3 9/16" | 5 |

The Kraftform **Comfort VDE** series offers a wide and diverse range of screwdrivers for universal use, with the distinctive Kraftform handle.



Multi-component Kraftform handle, **for quick and low-exertion working.**



Kraftform **Classic VDE** also offers the distinctive Kraftform handle, in a single-component variant.



Screw symbol and tip size identification markings on the handle **make it easier to find** the right screwdriver in the tool case or at the workplace.




Hexagonal non-roll feature **prevents any annoying rolling away** at the workplace.



Wera Black Point tips and a refined hardening process ensure **long service life of the tip, improved corrosion protection and an exact fit.**



The bit material used for manufacturing is subjected to a specific Wera hardening process, ensuring **longer product service life.**



VDE tools: The **individual testing in a water bath at 10,000 volts**, in accordance with DIN EN 60900 (IEC 60900:2004), ensures safe working under a load of up to 1,000 volts.



Kraftform Comfort VDE

1160 i VDE Insulated slotted screwdriver



Application: Slotted screws

Blade: Insulated, individually tested as per IEC 60900 : 2004

Design: Conical tip, chrome-plated, Black Point

Handle: Kraftform Comfort with non-roll feature, multi-component

| Code | mm | mm | mm | mm | mm | mm | mm | mm |
|-------------|-----|------|-----|-----|-------|--------|----|----|
| 05031580001 | 0,4 | 2,5 | 80 | 81 | 3/32" | 3 1/8" | | 10 |
| 05031581001 | 0,5 | 3,0 | 100 | 81 | 1/8" | 4" | | 10 |
| 05031582001 | 0,6 | 3,5 | 100 | 81 | 9/64" | 4" | | 10 |
| 05031583001 | 0,8 | 4,0 | 100 | 98 | 5/32" | 4" | | 10 |
| 05031584001 | 0,8 | 4,0 | 150 | 98 | 5/32" | 6" | | 5 |
| 05031587001 | 1,0 | 5,5 | 125 | 98 | 7/32" | 5" | | 10 |
| 05031585001 | 1,0 | 5,5 | 200 | 98 | 7/32" | 8" | | 5 |
| 05031588001 | 1,2 | 6,5 | 150 | 105 | 1/4" | 6" | | 10 |
| 05031586001 | 1,2 | 6,5 | 200 | 105 | 1/4" | 8" | | 5 |
| 05031589001 | 1,2 | 8,0 | 175 | 112 | 5/16" | 7" | | 5 |
| 05031590001 | 1,6 | 8,0 | 200 | 112 | 5/16" | 8" | | 5 |
| 05031591001 | 1,6 | 10,0 | 200 | 112 | 3/8" | 8" | | 5 |

1165 i PZ VDE Insulated screwdriver for Pozidriv screws



Application: Suitable for Pozidriv® screws

Blade: Insulated, individually tested as per IEC 60900 : 2004

Design: Chrome-plated, Black Point

Handle: Kraftform Comfort with non-roll feature, multi-component

| Code | mm | mm | mm | mm | mm | mm |
|-------------|------|-----|-----|--------|----|----|
| 05031610001 | PZ 0 | 80 | 81 | 3 1/8" | | 5 |
| 05031611001 | PZ 1 | 80 | 98 | 3 1/8" | | 5 |
| 05031612001 | PZ 1 | 150 | 98 | 6" | | 5 |
| 05031613001 | PZ 2 | 100 | 105 | 4" | | 5 |
| 05031614001 | PZ 2 | 200 | 105 | 8" | | 5 |
| 05031615001 | PZ 3 | 150 | 112 | 6" | | 5 |

*) Pozidriv = reg. trademark of European Industrial Service Ltd.

1162 i PH VDE Insulated screwdriver for Phillips screws



Application: Phillips screws

Blade: Insulated, individually tested as per IEC 60900 : 2004

Design: Chrome-plated, Black Point

Handle: Kraftform Comfort with non-roll feature, multi-component

| Code | mm | mm | mm | mm | mm | mm |
|-------------|------|-----|-----|--------|----|----|
| 05031600001 | PH 0 | 80 | 81 | 3 1/8" | | 5 |
| 05031601001 | PH 1 | 80 | 98 | 3 1/8" | | 5 |
| 05031602001 | PH 1 | 150 | 98 | 6" | | 5 |
| 05031603001 | PH 2 | 100 | 105 | 4" | | 5 |
| 05031604001 | PH 2 | 200 | 105 | 8" | | 5 |
| 05031605001 | PH 3 | 150 | 112 | 6" | | 5 |
| 05031606001 | PH 4 | 200 | 112 | 8" | | 2 |

1160 i/7 Safety screwdriver set Krafform Comfort VDE and voltage tester



Application: Slotted and Phillips screws

Content: 7-piece set in display carton

| Code | | | |
|-------------|-----------------|--|---|
| 05031575001 | ● 1160 i VDE | 1 x 0,4x2,5x80; 1 x 0,6x3,5x100; 1 x 0,8x4,0x100; 1 x 1,0x5,5x125 | 1 |
| | ⊕ 1162 i PH VDE | 1 x PH 1x80; 1 x PH 2x100 | |
| | ● 4115 | 1 x 0,5x3,0x65 | |

1160 i/1165 i/7 Screwdriver set Krafform Comfort VDE and voltage tester



Application: Slotted and Pozidriv[®] screws


Content: 7-piece set in display carton

| Code | | | |
|-------------|-----------------|--|---|
| 05031576001 | ● 1160 i VDE | 1 x 0,4x2,5x80; 1 x 0,6x3,5x100; 1 x 0,8x4,0x100; 1 x 1,0x5,5x125 | 1 |
| | ⊕ 1165 i PZ VDE | 1 x PZ 1x80; 1 x PZ 2x100 | |
| | ● 4115 | 1 x 0,5x3,0x65 | |

*) Pozidriv = reg. trademark of European Industrial Service Ltd.



Why is a VDE screwdriver safe?



A dielectric strength test under a 10,000-volt load in a water bath is the only way of reassuring users that their screwdrivers have been exhaustively tested for their most important feature: their insulation.

Each individual Wera VDE screwdriver

is subjected to this test to guarantee safe working up to 1,000 volts.

Kraftform Classic VDE

1760 i VDE Insulated screwdriver for slotted screws



Application: Slotted screws

Blade: Insulated, individually tested as per IEC 60900 : 2004

Design: Conical tip, zinc-phosphated, Black Point

Handle: Kraftform Classic with non-roll feature, single-component

| Code | mm | mm | mm | mm | | | |
|-------------|-----|-----|-----|-----|------------------|------------------|----|
| 05031240001 | 0,4 | 2,5 | 80 | 81 | $\frac{3}{32}$ " | $3\frac{1}{8}$ " | 10 |
| 05031239001 | 0,5 | 3,0 | 100 | 81 | $\frac{1}{8}$ " | 4" | 10 |
| 05031241001 | 0,6 | 3,5 | 100 | 81 | $\frac{9}{64}$ " | 4" | 10 |
| 05031242001 | 0,8 | 4,0 | 100 | 98 | $\frac{5}{32}$ " | 4" | 10 |
| 05031243001 | 1,0 | 5,5 | 125 | 98 | $\frac{7}{32}$ " | 5" | 10 |
| 05031244001 | 1,2 | 6,5 | 150 | 105 | $\frac{1}{4}$ " | 6" | 10 |
| 05031245001 | 1,6 | 8,0 | 200 | 112 | $\frac{3}{8}$ " | 8" | 5 |

1762 i PH VDE Insulated screwdriver for Phillips screws



Application: Phillips screws

Blade: Insulated, individually tested as per IEC 60900 : 2004

Design: Zinc-phosphated, Black Point

Handle: Kraftform Classic with non-roll feature, single-component

| Code | | mm | mm | | |
|-------------|------|-----|-----|------------------|----|
| 05031249001 | PH 0 | 80 | 81 | $3\frac{1}{8}$ " | 5 |
| 05031250001 | PH 1 | 80 | 98 | $3\frac{1}{8}$ " | 10 |
| 05031251001 | PH 2 | 100 | 105 | 4" | 10 |
| 05031252001 | PH 3 | 150 | 112 | 6" | 5 |

1765 i PZ VDE Insulated screwdriver for Pozidriv screws



Application: Suitable for Pozidriv® screws

Blade: Insulated, individually tested as per IEC 60900 : 2004

Design: Zinc-phosphated, Black Point

Handle: Kraftform Classic with non-roll feature, single-component

| Code | | mm | mm | | |
|-------------|------|-----|-----|------------------|----|
| 05031259001 | PZ 0 | 80 | 81 | $3\frac{1}{8}$ " | 5 |
| 05031260001 | PZ 1 | 80 | 98 | $3\frac{1}{8}$ " | 10 |
| 05031261001 | PZ 2 | 100 | 105 | 4" | 10 |
| 05031262001 | PZ 3 | 150 | 112 | 6" | 5 |

*) Pozidriv = reg. trademark of European Industrial Service Ltd.

1760 i/6 Screwdriver set Kraftform Classic VDE



Application: Slotted and Phillips screws

Content: 6-piece set in display carton

| Code | | | | |
|-------------|---------------|----------------------------------|--|---|
| 05031282001 | 1760 i VDE | 1 x 0,4x2,5x80; 1 x 0,6x3,5x100; | | 1 |
| | | 1 x 0,8x4,0x100; 1 x 1,0x5,5x125 | | |
| | 1762 i PH VDE | 1 x PH 1x80; 1 x PH 2x100 | | |

1760 i/65 i/6 Screwdriver set Kraftform Classic VDE



Application: Slotted and Pozidriv® screws

Content: 6-piece set in display carton

| Code | | | | |
|-------------|---------------|----------------------------------|--|---|
| 05031283001 | 1760 i VDE | 1 x 0,4x2,5x80; 1 x 0,6x3,5x100; | | 1 |
| | | 1 x 0,8x4,0x100; 1 x 1,0x5,5x125 | | |
| | 1765 i PZ VDE | 1 x PZ 1x80; 1 x PZ 2x100 | | |

*) Pozidriv = reg. trademark of European Industrial Service Ltd.