

Lynx-S

SA LYNX-S 9W/827 G23 SLV 10 P

0025882



Range features

- Single pin-base compact lamps, suitable for wide range of applications
- Excellent colour rendering - (CRI=85)
- For use with magnetic ballast
- Available in Homelight (2700K), Warm White (3000K) and Cool white (4000K)
- Average rated life: 10000 hours



PRODUCT OVERVIEW

Ordering number	0025882
Technology	Compact Fluorescent
Light colour	827 Homelight
Energy class	A
Average life (Rated) (h)	10000
Lamp shape	Stick
Lamp finish	frosted
Dimmable	NO
Cap/Base	G23
Type	Lynx S
EAN code	5410288258829
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	600
Efficacy (Rated) (lm/w)	67
Watt (Nominal) (W)	9
Voltage (V)	60

Lynx-S

SA LYNX-S 9W/827 G23 SLV 10 P

0025882

DATA TABLE

General data

Ordering number	0025882
Dry applications use only	yes
Technology	Compact Fluorescent
Average life (Nominal) (h)	10000
Energy class	A
Average life (Rated) (h)	10000
Lamp shape	Stick
Lamp finish	frosted
Dimmable	NO
Cap/Base	G23
Type	Lynx S
EAN code	5410288258829
E-number FI	4944081
E-number SE	8357259
Long description	Single pin-base compact lamps, suitable for wide range of applications. Excellent colour rendering - (CRI=85). For use with magnetic ballast. Available in Homelight (2700K), Warm White (3000K) and Cool white (4000K). Average rated life: 10000 hours
Product name	SA LYNX-S 9W/827 G23 SLV 10 P
Lamp mercury content (mg)	< 2.50 mg
Starting time (max) (s)	10 Sec
Control gear required	Yes
Fixture rating	Open
IEC Reference	IEC 60901
IEC Reference 2	IEC 61199
IEC Reference 3	IEC 60921
Intended purpose	General lighting
Special purpose lamp	No
Transformer required	No
Sales pack quantity	10
Rated survival factor at 2000 h 50Hz	0.98
Rated survival factor at 4000 h 50Hz	0.9
Rated survival factor at 6000 h 50Hz	0.7
Rated survival factor at 8000 h 50Hz	0.5
Rated survival factor at 12000 h 50Hz	0.62

Lynx-S

SA LYNX-S 9W/827 G23 SLV 10 P

0025882

Optical data

Light colour	827 Homelight
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	600
Luminous flux (Nominal) (lm)	600
Ambient temperature for maximum luminous flux (°C)	25
Rated lumen maint. factor at 2000 h 50Hz	0.85
Rated lumen maint. factor at 4000 h 50Hz	0.78
Rated lumen maint. factor at 6000 h 50Hz	0.76
Rated lumen maint. factor at 8000 h 50Hz	0.75
Rated lumen maint. factor at 12000 h 50Hz	0.8

Electrical data

kWh per 1000 hours burning time	11
Rated lamp efficacy (lm/W) 100H 50Hz at optimum temp.	67
Efficacy (Rated) (lm/w)	67
Watt (Nominal) (W)	9
Watt (Rated) - High frequency (W)	50
Watt (Rated) (W)	8.7
Voltage (V)	60
Ignition voltage (V)	177
Current (A)	0.17

Physical data


Weight (kg)	0.03
Length base to base (mm) - A	168
Lamp Length (mm) - C/L	145
Max. Lamp Diameter (mm) - D	32.5
Single packaging type	Box/Sleeve
Single package dimensions (L x W x H) (cm)	2.20 x 3.80 x 15.90
Inner package dimensions (L x W x H) (cm)	12.20 x 8.80 x 18.00
Inner package net weight (kg)	0.26
Outer package dimensions (L x W x H) (cm)	45.50 x 26.10 x 19.50

Lynx-S

SA LYNX-S 9W/827 G23 SLV 10 P

0025882

TECHNICAL DRAWINGS



ENERGY LABEL

