




This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.



Customer drawing

DIM.S SHELL	A	B	C	D	Pitch
9	30.70	16.80	25.00	19.40	2.74
15	39.00	25.10	33.30	27.70	2.74
25	52.90	38.80	47.00	41.40	2.77
37	69.20	55.30	63.50	57.90	2.77

REVISIONS

SYM	ECN	DESCRIPTION	DATE	APPROVED
1			12/14/07	

D-SUB TECHNICAL DATA

SHELL : Steel 2.5um(100u") min tin over 1.25um(50u") min nickel
 BODY : Glass filled thermoplastic.
 Flame retardant to UL94 V-0Color Black
 CONTACTS : Brass
 0.4um(15u") min gold over 1.25um(50u") min nickel
 SCREWLOCK : Copper alloy (no plating)
 ELECTRICAL : Voltage rating : 300 V RMS at 50 Hz
 Current rating 7.5A.
 Insulation resistance >5000 M Ohms
 Contact resistance 20 mOhms max.
 CLIMATIC : Temperature range -55 °C up to 85°C, peak at 125°C
 Damp heat 21 days(40 °C-95% HR)
 MARKING : Amphenol...(Series No.)
 Commercial reference
 Manufacturing date

PRODUCT CODE

L 717D XXX P ST X

L: RoHS Compliance

717D: Male connector,
shell with dimples

Size and number
of contacts:
E09,A15,B25,C37

Contact type:
P:Male

Hood option:
1=DPPK
2=DSSK
3=DTZK
4=DVZK
Blank=no hood

Contact termination:
ST=Screw termination

UNLESS OTHERWISE SPECIFIED TOLERANCES		APPROVAL	DATE
U.S.	METRIC	DRAWN	Christine.cui 12/14/07
.X +/-	0.50	CHECKED	Lik.wang 12/14/07
.XX +/-	0.30	CHECKED	
.XXX +/-	0.20		
FRACTIONS +/-			
ANGLES +/-	2'		
FOR MATERIALS AND FINISHES SEE NOTES		DRAWING FILE :	
REMOVE SHARP EDGES		ANGLE OF PROJECTION	
DIMENSIONS			
U.S.	INCHES		
METRIC	MM		

Amphenol®

TITLE
machined contacts, D-ST series

SIZE	DRAWING NO.	REV.
A4	C L717DXXXPSTX	1
SCALE	NONE	SHEET 1 OF 2

REVISIONS

SYM	ECN	DESCRIPTION	DATE	APPROVED
1			12/14/07	

Plastic hoods



DPPK Straight cable entry



DSSK Angled cable entry

Kit connector+hood option:
(See following decscription)

X X ST X X

- 1=DPPK
- 2=DSSK
- 3=DTZK
- 4=DVZK

Metallic hoods



DTZK Straight cable entry



DVZK Angled cable entry

UNLESS OTHERWISE SPECIFIED TOLERANCES		APPROVAL		DATE		Amphenol®	
U.S. METRIC		DRAWN	Christine.cui	12/14/07			
.X +/-		CHECKED	Lik.wang	12/14/07			
.XX +/-		CHECKED					
.XXX +/-							
FRACTIONS +/-						TITLE	
ANGLES +/-		2°					
FOR MATERIALS AND FINISHES SEE NOTES		DRAWING FILE :					
REMOVE SHARP EDGES		ANGLE OF PROJECTION				SIZE DRAWING NO. REV	
DIMENSIONS							
U.S. INCHES							
METRIC MM		SCALE NONE				SHEET 2 OF 2	
						C L717DXXXXPSTX 1	