

Lynx-SE

SA LYNX-SE 9W/830 2G7 SLV 10

0025898



Range features

- Single-bend pin base compact lamp: Suitable for wide range of use
- Suitable for operation on electronic control gear
- Dimmable
- Extremely low profile
- Excellent colour rendering (CRI=85)
- Suitable for emergency lighting
- Dimmable with suitable ballast
- Available in Homelight (2700K), Warm White (3000K) and Cool White (4000K)
- Average rated life: 10000 hours



PRODUCT OVERVIEW

Ordering number	0025898
Technology	Compact Fluorescent
Light colour	830 Warm White
Energy class	A
Average life (Rated) (h)	10000
Lamp shape	Stick
Lamp finish	frosted
Dimmable	YES
Cap/Base	2G7
Type	Lynx SE
EAN code	5410288258980
CRI (Ra)	80
Colour temperature (K)	3000
Luminous flux (Rated) (lm)	600
Efficacy (Rated) (lm/w)	67
Watt (Nominal) (W)	9
Voltage (V)	60

Lynx-SE

SA LYNX-SE 9W/830 2G7 SLV 10

0025898

DATA TABLE

Lynx-SE

SA LYNX-SE 9W/830 2G7 SLV 10

0025898

General data

Dry applications use only	yes
Ordering number	0025898
Technology	Compact Fluorescent
Average life (Rated) (h)	10000
Average life (Nominal) (h)	10000
Energy class	A
Lamp shape	Stick
Lamp finish	frosted
Dimmable	YES
Cap/Base	2G7
Type	Lynx SE
EAN code	5410288258980
E-number FI	4944097
E-number SE	8357278
Long description	Single-bend pin base compact lamp: Suitable for wide range of use. Suitable for operation on electronic control gear. Dimmable. Extremely low profile. Excellent colour rendering (CRI=85). Suitable for emergency lighting. Dimmable with suitable ballast. Available in Homelight (2700K), Warm White (3000K) and Cool White (4000K). Average rated life: 10000 hours
Product name	SA LYNX-SE 9W/830 2G7 SLV 10
Lamp mercury content (mg)	< 2.50 mg
Starting time (max) (s)	10 Sec
Control gear required	Yes
IEC Reference	IEC 60901
IEC Reference 2	IEC 61199
IEC Reference 3	IEC 60921
Intended purpose	General lighting
Special purpose lamp	No
Transformer required	No
Sales pack quantity	10
Rated survival factor at 2000 h 50Hz	0.99
Rated survival factor at 2000 h High Frequency	0.99
Rated survival factor at 4000 h 50Hz	0.98
Rated survival factor at 4000 h High Frequency	0.98
Rated survival factor at 6000 h 50Hz	0.93
Rated survival factor at 6000 h High Frequency	0.95
Rated survival factor at 8000 h 50Hz	0.88
Rated survival factor at 8000 h High Frequency	0.92
Rated survival factor at 12000 h 50Hz	0.62
Rated survival factor at 12000 h High Frequency	0.67

Lynx-SE

SA LYNX-SE 9W/830 2G7 SLV 10

0025898

Optical data

Light colour	830 Warm White
CRI (Ra)	80
Colour temperature (K)	3000
Luminous flux (Rated) (lm)	600
Luminous flux (Nominal) (lm)	600
Ambient temperature for maximum luminous flux (°C)	25
Rated lumen maint. factor at 2000 h 50Hz	0.90
Rated lumen maint. factor at 4000 h 50Hz	0.84
Rated lumen maint. factor at 6000 h 50Hz	0.82
Rated lumen maint. factor at 8000 h 50Hz	0.81
Rated lumen maint. factor at 12000 h 50Hz	0.8
Rated lumen maint. factor at 2000 h High Frequency	0.92
Rated lumen maint. factor at 4000 h High Frequency	0.88
Rated lumen maint. factor at 6000 h High Frequency	0.85
Rated lumen maint. factor at 8000 h High Frequency	0.82
Rated lumen maint. factor at 12000 h High Frequency	0.8

Electrical data

kWh per 1000 hours burning time	11
Rated lamp efficacy (lm/W) 100H 50Hz at optimum temp.	67
Efficacy (Rated) (lm/w)	67
Watt (Rated) (W)	8.7
Watt (Nominal) (W)	9
Voltage (V)	60
Current (A)	0.170

Physical data


Weight (kg)	0.03
Length base to base (mm) - A	152
Lamp Length (mm) - C/L	145
Max. Lamp Diameter (mm) - D	37
Single packaging type	Box/Sleeve
Single package dimensions (L x W x H) (cm)	2.20 x 3.80 x 15.90
Inner package dimensions (L x W x H) (cm)	12.20 x 8.80 x 18.00
Inner package net weight (kg)	0.26
Outer package dimensions (L x W x H) (cm)	45.50 x 26.10 x 19.50

Lynx-SE

SA LYNX-SE 9W/830 2G7 SLV 10

0025898

TECHNICAL DRAWINGS



ENERGY LABEL

