




|                             |                      |
|-----------------------------|----------------------|
| <b>Product Name:</b>        | MIL-W-22759/11 26AWG |
| <b>Product Discription:</b> | MIL-W-22759/11 26AWG |
| <b>Specification No.:</b>   |                      |
| <b>Customer's Name:</b>     |                      |

| Description                                                                                           |                    |                |             |            | Construction                   |  |                               |                |                  |                                        |  |
|-------------------------------------------------------------------------------------------------------|--------------------|----------------|-------------|------------|--------------------------------|--|-------------------------------|----------------|------------------|----------------------------------------|--|
| Rated Voltage:                                                                                        |                    | 600V           |             |            | Conductor                      |  | Stranded Sliver plated copper |                |                  |                                        |  |
| Rated Temperature:                                                                                    |                    | 200℃           |             |            | Size(AWG)                      |  | 26                            |                |                  |                                        |  |
| Reference Standard:                                                                                   |                    | MIL-W-22759/11 |             |            | Construction(±0.008mm)         |  | 19/0.10                       |                |                  |                                        |  |
| Cross Section                                                                                         |                    |                |             |            | Stranded Dia.(mm)Ref.          |  | 0.5                           |                |                  |                                        |  |
|                      |                    |                |             |            | Insulation Material            |  | PTFE                          |                |                  |                                        |  |
|                                                                                                       |                    |                |             |            | Insulation Color               |  | ANY COLOR                     |                |                  |                                        |  |
|                                                                                                       |                    |                |             |            | Ave Thickness(mm)              |  | 0.25                          |                |                  |                                        |  |
|                                                                                                       |                    |                |             |            | Insulation Dia.(±0.08mm)       |  | 1.00                          |                |                  |                                        |  |
|                                                                                                       |                    |                |             |            |                                |  |                               |                |                  |                                        |  |
|                                                                                                       |                    |                |             |            |                                |  |                               |                |                  |                                        |  |
| Marking                                                                                               |                    |                |             |            | Remark:                        |  |                               |                |                  |                                        |  |
| No marking on the cable jacket                                                                        |                    |                |             |            | 8776190 Red                    |  | 8776196 Blue                  |                |                  |                                        |  |
|                                                                                                       |                    |                |             |            | 8776184 Black                  |  | 8776200 White                 |                |                  |                                        |  |
|                                                                                                       |                    |                |             |            | 8776193 Brown                  |  |                               |                |                  |                                        |  |
| Applications                                                                                          |                    |                |             |            | Characteristics                |  |                               |                | Customer Approve |                                        |  |
| These wires are ideal for internal wiring of appliances, electronic equipment and other applications. |                    |                |             |            | Test Item                      |  |                               | Standard Value |                  | <div>Seal &amp; Stamp</div>            |  |
|                                                                                                       |                    |                |             |            | Test Material                  |  |                               | PTFE(ROHS)     |                  |                                        |  |
|                                                                                                       |                    |                |             |            | Insulation resistance(20℃ MΩ*m |  |                               | 1000           |                  |                                        |  |
|                                                                                                       |                    |                |             |            | Vol. Tesr(AC.V.60S) (V)        |  |                               | 2000           |                  |                                        |  |
|                                                                                                       |                    |                |             |            | Flammability Test              |  |                               | VW-1           |                  |                                        |  |
| Revisions                                                                                             |                    |                |             |            | Max.DC Resistance(20℃ Ω/km)    |  |                               | 122.37(MAX)    |                  | <div>Signature:</div> <div>Date:</div> |  |
| Version                                                                                               | Description        | Drawn by       | Approved by | Date       |                                |  |                               |                |                  |                                        |  |
| 0                                                                                                     | New document issue | Danniel        | Jason       | 19/05/2015 |                                |  |                               |                |                  |                                        |  |
|                                                                                                       |                    |                |             |            |                                |  |                               |                |                  |                                        |  |
|                                                                                                       |                    |                |             |            |                                |  |                               |                |                  |                                        |  |
|                                                                                                       |                    |                |             |            |                                |  |                               |                |                  |                                        |  |
|                                                                                                       |                    |                |             |            |                                |  |                               |                |                  |                                        |  |