

4		3		2		1					
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION							
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION.				ALL INTERNATIONAL RIGHTS RESERVED.							
LOC AF		DIST 50		REVISIONS							
P		LTR		DESCRIPTION		DATE		DWN		APVD	
		L		REVISED PER ECR-08-008189		24NOV08		HMR		DD	

APPLICATOR CUT-OFF

1 CONTINUOUS STRIP ON REELS
2 8000 PER REEL

SECTION A-A
SCALE 10:1

SECTION B-B
SCALE 10:1

METRIC

TIN PLATING		1.22-1.98 DIA [.048-.078]		0.13mm ² -0.5mm ² [26-20] AWG		60123-3 2	
TIN PLATING		1.22-1.98 DIA [.048-.078]		0.13mm ² -0.5mm ² [26-20] AWG		60123-2	
FINISH		INSULATION RANGE		WIRE RANGE		PART NUMBER	

F OR O		2.79 [.110]		4.06 [.160]		F		2.03 [.080]		1.40[.055]		0.5mm ² [20]		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P FORTNEY 4/5/90		Tyco Electronics Corporation Harrisburg, PA 17105-3608			
										1.37[.054]		0.3mm ² [22]		CHK JR RUTH 4/5/90							
										1.30[.051]		0.2mm ² [24]		APVD -							
										1.27[.050]		0.13mm ² [26]		PRODUCT SPEC -							
TYPE		WIDTH		STRIP LENGTH ±0.38 [±.015]		TYPE		WIDTH		±0.051[±.002] HEIGHT		WIRE		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC -		NAME	
INSUL BARREL CRIMP						WIRE BARREL CRIMP								MATERIAL #2 HARD BRASS		FINISH SEE TABLE		WEIGHT -		RING	
												CUSTOMER DRAWING		SCALE 6:1		SHEET 1 OF 1		REV L			