


断面 A-A
SECT

断面 B-B
SECT

0.95	0.8 ±0.1 DIA, 1.2~1.6	—	POST-TINNED PHOS-BRO. 0.2t 焼青銅 錫めっき仕上げ 0.2t	172782-9
0.95	0.8 ±0.1 DIA, 1.2~1.6	—	POST-TINNED, HIGH HEAT RESISTANCE COPPER ALLOY 高耐熱性銅合金 錫めっき仕上げ 0.2t	1-172782-2
1.2	+0.05 / -0.1 DIA, 1.2~1.6	++	POST-TINNED BRASS 0.2t 黄銅 錫めっき 0.2t	172782-7
0.95	0.8 DIA, 1.2~1.6	—	PRE-TURNED BRASS 0.2t 黄銅 0.2t	172782-5
1.2	+0.05 / -0.1 DIA, 1.2~1.6	172798-2	PRE-TURNED BRASS 0.2t 黄銅 0.2t	172782-2
0.95	0.8 DIA, 1.2~1.6	172798-1	PRE-TURNED BRASS 0.2t 黄銅 0.2t	172782-1
A REF	APPLICABLE PCB HOLE AND THICK	LOOSE PIECE CONTACT	MATERIAL	PART NO
銅A子	適用基板穴径・厚さ	ピン状端子型番	材料	型番

NOTES.

1. APPLICABLE HDR HSG: 172520 (25 PITCH) 172890 (20 PITCH)
2. PRODUCT SPEC: 108-5163
3. CRIMPING SPEC: 114-5062
COMMON APPLICATOR FOR 2/25mm PITCH HDR HSG = P/M 755765-□
EXCLUSIVE APPLICATOR FOR 25mm PITCH HDR HSG = P/M 752830-□
4. INSTRUCTION SHEET: IS-206J, 207J, 208J

注:

1. 適用A子型番 = 172520 (25mmピッチ) 172890 (20mmピッチ)
2. 製品規格 = 108-5163
3. 取付適用規格 = 114-5062
2/25mmピッチA子-ハンダ付専用A子型番 = 755765-□
25mmピッチA子-ハンダ付専用A子型番 = 752830-□
4. 取扱説明書 = IS-206J, 207J, 208J

G	REVISED ECR-09-003857	J.S	N.Y	19FEB 09
F	REVISED	S.I	S.M	14JAN 08
E	REVISED FJDO-0004-03	K.K	M.S	28AUG 03
D	REVISED FJDO-0017-03	K.K	M.S	10FEB 03
C	変更 (REVISED) J-47	K.K	M.S	4FEB 02
B	改訂 (REVISED) J-10	K.K	M.S	14JAN 02
A	初版 (ORIGINAL)	K.K	M.S	14JAN 02
LTR	EE (REVISION RECORD)	DR	CHK	DATE

Tyco Electronics AMP K.K. Kawasaki, Japan		ロ-プロファイルミニアンパインコンタクト (LOW PROFILE MINI AMP-IN CONTACT)	
SIZE RANGE 0.8~1.6	INSULATION DIA. 1.4~1.5	SIZE (NAME) A3 J	REV. NO. C-172782
MATERIAL (SEE PAGE 1)	FINISH (SEE PAGE 1)	RE (SCALE) 10-1	SHEET G

寸法: 単位 寸法はmmで示す。DO NOT SCALE PRINT