


**66226-004LF - Clincher™ : 4 Positions
Single row Vertical Pin Connector**



www.fci.com

Mating Half

- [65801-004LF](#)
- [65801-033LF](#)
- [65801-104LF](#)
- [65801-133LF](#)

Specifications

Approvals / Certifications

UL File Number	E66906
CSA File Number	LR46923
Approvals / Certifications	UL and CSA Approved
Mechanical	
Durability (Mating cycles)	100
Insertion force	3N (300 gf) max.
Withdrawal Force	0.3N (30 gf) Per contact min.
Dimensional	
Diameter (Cable)	0.33 mm (0.013 in.) max. (Including insulation)
Thickness (Cable conductor)	0.076 mm (0.003 in.)
Width (Cable conductor)	1.57 mm (0.062 in.)
Electrical	
Current rating	2 amps
Resistance (Contact)	10 milli ohms
Resistance (Insulation)	5000 M ohms
Voltage rating	500 volts
General	
Applied to	Flat Conductor, Flat Cable
Number of contacts (Total)	4
Orientation	Vertical
Product Type	Cable Pin Connector
Application Equipment	PV-219E HT-0270
Cable Specification	IPC Standard, FC-220 B Cables Type A or B, Tolerance Class IV
Other Features	
Packaging (Type)	Tray

Literature	950526-001
Physical	
Color (Housing)	Blue
Material (Contact)	Copper Alloy
Material (Housing)	Polypropylene
Plating (Contact area)	2.54 μm (100 $\mu\text{in.}$) Pure Tin
Humidity (Relative)	09
Insulation material (Cable)	Polyester or Polyimide
Material (Spring)	Copper Alloy
Temperature (Operating - range)	-65°C to +105°C
Temperature (Operating)	85°C