


DO NOT SCALE

DIMENSIONS IN mm

METRIC



THIRD ANGLE

PROJECTION




NOTES

- 1 SNAP-IN POLARIZERS PN. 927636-2 OR 927637-2 CAN BE APPLIED.
- 2 THERE IS NO WINDOW FOR SNAP-IN POLARIZERS AT THIS END IN 10 AND 14 POS. HEADERS.
- 3 INDICATION OF FIRST POSITION.
- 4 SNAP-IN CONNECTOR "LATCH / EJECTOR" PN. 927176-2 OR 927215-2 CAN BE APPLIED.
- 5 THERE IS NO CENTER STAND-OFF IN 10-26 POS. HEADERS.
- 6 DIMENSION WITH EJECTOR : PN. 927176-2 H= 23 MM, PN. 927215-2 H= 27,3 MM.
H1= 20,2 MM H1= 24 MM
H2= 6 MM H2= 7 MM
- 7 PARTNUMBER AND PROD.- DATE ON SUITABLE SURFACE X-828 581-X
DD.MM.YY



RECOMMENDED PCB-HOLE PATTERN



2 PIN-CONTACT

BRASS

MATING SIDE: 0,8µm AU
OR 0,8µm AMP DURAGOLD®/
OVER 1,27µm NI
SOLDER SIDE: MIN. 3,0µm SN
OVER 1,27µm NI

1 HOUSING

GLASSFILLED POLYESTER

GREY

COMPONENT NAME

MATERIAL

PLATING/COLOUR

CUSTOMER DRAWING

FOR REFERENCE ONLY
WILL NOT BE UPDATED

© COPYRIGHT 19- BY AMP-HOLLAND B.V.
ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE
COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.

THIS DRAWING IS UNPUBLISHED
RELEASED FOR PUBLICATION - ,19 -

AMP-HOLLAND B.V.
's-Hertogenbosch,
The Netherlands.

NAME
AMP-LATCH HEADER 90 DEG. VERSION

100,6	90,4	96,5	86,4	78,7	64	6-828581-4
95,5	85,3	91,4	81,3	73,7	60	6-828581-0
82,8	72,6	78,7	68,6	61,0	50	5-828581-0
70,1	59,9	66,0	55,9	48,3	40	4-828581-0
62,5	52,3	58,4	48,3	40,6	34	3-828581-4
52,3	42,2	48,3	38,1	30,5	26	2-828581-6
44,7	34,5	40,6	30,5	22,9	20	2-828581-0
39,6	29,5	35,6	25,4	17,8	16	1-828581-6
37,1	26,9	33,0	22,9	15,2	14	1-828581-4
32,0	21,8	27,9	17,8	10,2	10	1-828581-0
DIM. "E"	DIM. "D"	DIM. "C"	DIM. "B"	DIM. "A"	NR. OF POSITIONS	PARTNUMBER
VARIABLE CONNECTOR DIMENSIONS						

DR.: J.v.LIEMPT
DATE: 29-11-93

CHK.: R. VERSTIJNEN
DATE: -

APP.: L.v.SOEEST
DATE: -

DWG.No. C-828581
LOC. AI
SHEET 1 OF 1
REV.LTR. A1

8

7

6

5

4

3

2

1