



NO	DESCRIPTION	DATE
⚠	MODIFY APPEARANCE OF ②	07.01.09'
⚠	ADD (P/N:5465193)	03.24.11'
⚠	50 OHMS → 75 OHMS	03.07.12'




03/07/2012

SPECIFICATIONS:  
 MECHANICAL CHARACTERISTICS:  
 MATING/UNMATING--500 CYCLES  
 ELECTRICAL CHARACTERISTICS:  
 NORMAL IMPEDANCE-- 75 OHMS ⚠  
 FREQUENCY RANGE-- 0-1 GHz  
 TESTING VOLTAGE-- 500 VOLTS RMS  
 DIELECTRIC WITHSTANDING VOLTAGE-- 1500 VOLTS RMS  
 INSULATION RESISTANCE-- 5000 MEGOHMS MIN.  
 ENVIRONMENTAL CHARACTERISTICS:  
 TEMPERATURE RANGE-- -40° C TO +60° C  
 THERMAL SHOCK-- MIL-STD-202,METHOD 107,COND.B.  
 PHYSICAL SHOCK-- MIL-STD-202,METHOD 204,COND.B.



MOUNTING HOLE



P.C.B. CONFIGURATION



(P/N:5465193) ⚠

APPROVED

by \_\_\_\_\_

DATE: \_\_\_\_\_

NO	DESCRIPTION	MATERIAL	Q'TY	FINISH
8	SOLDER PIN	COPPER WIRE	1	TIN
7	CENTER CONTACT	PHOSPHOR BRONZE WITH GOLD PLATING AT CONTACT AREA TIN/LEAD PLATING AT TAIL	1	GOLD TIN
5	INSULATION	POLYPROPYLENE UL 94HB	1	NONE
4	WASHER	S50C	1	NICKEL
3	NUT	BRASS	1	NICKEL
2	BODY	ZINC ALLOY	1	NICKEL
1	MOUNTING POST	BRASS	2	TIN

DESCRIPTION		BNC STRAIGHT PCB MOUNT JACK RECEPTACLE	
製圖	DRAWN	TOLERANCE	品名
檢圖	CHECK	單位	UNIT
認定	APPROVAL	比例	SCALE
	Yoko	.X ±0.2	13-60-7 D.G.Z
	Jase	.XX ±0.1	TITLE \ROHS COMPLIANT (75)
	Jenny	.XXX ±0.05	DATE 09'19.02
		ANGLE ±5°	版次 B-3
			DWG.NO. 13-0619