

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [171857-0002](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: 2.54mm Pitch, KK® 254 RPC Wire-to-Board Right-Angle Header with Friction Lock, Tin (Sn) Plating, Bag, 2 Circuits

Documents:

3D Model	Product Specification PS-171856-0002 (PDF)
Drawing (PDF)	Test Summary TS-171856-0001 (PDF)
Product Specification PS-171856-0001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	171857
Application	Power, Signal, Wire-to-Board
Overview	KK® Interconnect System - Molex
Product Name	KK® 254
UPC	887191376493

Physical

Breakaway	No
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-1, 94V-2
Glow-Wire Compliant	Yes
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Plating Mating	Tin
Material - Plating Termination	Nickel
Material - Resin	Nylon
Net Weight	0.250/g
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.54mm
Shrouded	Partial
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	4A
Voltage - Maximum	250V

Solder Process Data




image - Reference only

EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[171857Series](#)

Duration at Max. Process Temperature (seconds)	30
Lead-free Process Capability	SMC & Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	3
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Product Specification	PS-171856-0001, PS-171856-0002
Sales Drawing	SD-171857-0001
Test Summary	TS-171856-0001

This document was generated on 01/27/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION