



Save as PDF



Peli lights - submersible lights - Submersible worklights



This powerful torch was designed with one big goal: SAFETY. The SabreLite 2000 carries more approvals than any other torch on the market today making it extremely safe. The SabreLite is o-ring sealed with a twist on/off lens shroud and comes with a polarity battery guard tray that safeguards against dangerous "outgassing" of hydrogen from an accidentally reversed cell. It is powered by 3 C alkaline cells, submersible, and has an ABS resin body which resists chemicals, corrosion, and extreme temperatures. Unlike ordinary torches with yellowish beams, the SabreLite's incredibly bright Xenon lamp produces a powerful collimated white beam of light. Peli's SabreLite is the leader in quality and performance.



Materials

Body	Lens	Shroud	Switch Type
LEXAN EXL Resin	Nylon	Xenoy Polymer Resin	Twist On/Off Lens Shroud
Clip	Contact, Spring & Retainer	O-Ring	Night Vision Film
ABS Resin	Stainless Steel	Ethylene Propylene	N/A

Peli lights - submersible lights - Submersible worklights

ANSI FL1 Specifications

	High	
LIGHT SOURCE.	Xenon	
BATTERIES	3 C Alkaline (Not included)	
CHARGE TIME	N/A	
VOLTAGE	4.5	
LENGTH	19.8 cm (7.79")	
WEIGHT W/ BATTERIES	0.13 kg (4.5 oz.)	
WEIGHT W/O BATTERIES	0.15 kg (5.31 oz.)	

Configuration

Cat. #	Description

Peli lights - submersible lights - Submersible worklights Accessories

Cat. #	Description

	FL1 STANDARD	High	
LIGHT OUTPUT			
RUNTIME (hours/min)		5h	
BEAM DISTANCE (meters)		158m	
PEAK BEAM INTENSITY (candela)		6234cd	
WATER RESISTANT			

Approvals

- Class I, Div. 2; Gp ABCD, T3C; Class II; Div. 2; Gp G.
- Class I, II, Div. 2; Gp. ABCD/G , T3C.
- Listed 4567/E184884 Class I, Div. 1; Gp.C, D / Class I; Zone 1; Gp.IIA; IIB; T3C
- IECEX** - IEC Ex TSA 06.0021X Ex ib e IIC T4 IP67