





VCM 36/1/15

PCB transformer with mounting brackets


- Fixing points on the case
- Maximum power from minimum size
- Vacuum resin moulded (self extinguishing to UL 94 V-0)

Safety isolating transformer to IEC 61558-2-6, DIN EN 61558-2-6, VDE 0570 part 2-6

*Transformer to IEC 61558-2-1, DIN EN 61558-2-1, VDE 0570 part 2-1 (without VDE-Approval)



Dimensions in mm



VCM 36/1/15

PCB transformer with mounting brackets



Input data

Input voltage	230 V
Frequency range	50 - 60 Hz
No-load loss (typ.)	2.6 W

Output data

Output voltage	15 V
No-load voltage (ca. x factor)	1.11
Efficiency	83 %
Power	36.0 VA

Standards and security

Approvals	C-UL-US, ENEC 10 (VDE)
Short circuit strength	non-short-circuit proof
Protection index	IP 00
Safety class (prepared)	II
Ambient temperature max.	40 °C
Class of Insulation System	VDE=B, UL=105
Test voltage	5000 V, 50 Hz

Mechanical data

Type	encapsulated
Core type 2	EI 66/23,0
Terminals	pins for pcb
Fixing method	Fixing points on the case
Pin (ø)	0,8 mm
Weight	0.75 kg

Order numbers

Order Number	VCM 36/1/15
--------------	-------------

BLOCK Transformatoren-Elektronik GmbH
 Max-Planck-Straße 36-46
 27283 Verden
 Germany
 Phone +49 4231 678-0
 Fax +49 4231 678-177