

Fast Switching Emitter Controlled Diode




Feature

- 600V Emitter Controlled technology
- Fast recovery
- Soft switching
- Low reverse recovery charge
- Low forward voltage
- 175°C operating temperature
- Easy paralleling
- Pb-free lead plating; RoHS compliant
- Qualified according to JEDEC⁰⁾ for target applications

Product Summary

V_{RRM}	600	V
I_F	9	A
V_F	1.5	V
T_{jmax}	175	°C



Type	Package	Ordering Code	Marking	Pin 1	PIN 2,4	PIN 3
IDD09E60	PG-TO252-3	-	D09E60	NC	C	A

Maximum Ratings, at $T_j = 25^\circ\text{C}$, unless otherwise specified

Parameter	Symbol	Value	Unit
Repetitive peak reverse voltage	V_{RRM}	600	V
Continuous forward current $T_C = 25^\circ\text{C}$ $T_C = 90^\circ\text{C}$	I_F	19.3 13	A
Surge non repetitive forward current $T_C = 25^\circ\text{C}$, $t_p = 10\text{ ms}$, sine halfwave	I_{FSM}	40	A
Maximum repetitive forward current $T_C = 25^\circ\text{C}$, t_p limited by $t_{j,max}$, $D = 0.5$	I_{FRM}	29.5	A
Power dissipation $T_C = 25^\circ\text{C}$ $T_C = 90^\circ\text{C}$	P_{tot}	57.7 32.7	W
Operating junction temperature	T_j	-40...+175	°C
Storage temperature	T_{stg}	-55...+150	
Soldering temperature 1.6mm (0.063 in.) from case for 10 s	T_s	260	

Thermal Characteristics

Parameter	Symbol	Values			Unit
		min.	typ.	max.	
Characteristics					
Thermal resistance, junction - case	R_{thJC}	-	-	2.6	K/W
SMD version, device on PCB:	R_{thJA}				
@ min. footprint		-	-	75	
@ 6 cm ² cooling area ¹⁾		-	-	50	

Electrical Characteristics, at $T_j = 25^\circ\text{C}$, unless otherwise specified

Parameter	Symbol	Values			Unit
		min.	typ.	max.	
Static Characteristics					
Reverse leakage current	I_R				μA
$V_R=600\text{V}$, $T_j=25^\circ\text{C}$		-	-	50	
$V_R=600\text{V}$, $T_j=150^\circ\text{C}$		-	-	750	
Forward voltage drop	V_F				V
$I_F=9\text{A}$, $T_j=25^\circ\text{C}$		-	1.5	2	
$I_F=9\text{A}$, $T_j=150^\circ\text{C}$		-	1.5	-	

⁰J-STD20 and JESD22

¹Device on 40mm*40mm*1.5mm epoxy PCB FR4 with 6cm² (one layer, 70 μm thick) copper area for drain connection. PCB is vertical without blown air.


Electrical Characteristics, at $T_j = 25^\circ\text{C}$, unless otherwise specified

Parameter	Symbol	Values			Unit
		min.	typ.	max.	
Dynamic Characteristics					
Reverse recovery time $V_R=400V, I_F=9A, di_F/dt=800A/\mu s, T_j=25^{\circ}C$ $V_R=400V, I_F=9A, di_F/dt=800A/\mu s, T_j=125^{\circ}C$ $V_R=400V, I_F=9A, di_F/dt=800A/\mu s, T_j=150^{\circ}C$	t_{rr}	- - -	75 110 112	- - -	ns
Peak reverse current $V_R=400V, I_F=9A, di_F/dt=800A/\mu s, T_j=25^{\circ}C$ $V_R=400V, I_F=9A, di_F/dt=800A/\mu s, T_j=125^{\circ}C$ $V_R=400V, I_F=9A, di_F/dt=800A/\mu s, T_j=150^{\circ}C$	I_{rrm}	- - -	10.2 11.8 12.3	- - -	A
Reverse recovery charge $V_R=400V, I_F=9A, di_F/dt=800A/\mu s, T_j=25^{\circ}C$ $V_R=400V, I_F=9A, di_F/dt=800A/\mu s, T_j=125^{\circ}C$ $V_R=400V, I_F=9A, di_F/dt=800A/\mu s, T_j=150^{\circ}C$	Q_{rr}	- - -	343 585 612	- - -	nC
Reverse recovery softness factor $V_R=400V, I_F=9A, di_F/dt=800A/\mu s, T_j=25^{\circ}C$ $V_R=400V, I_F=9A, di_F/dt=800A/\mu s, T_j=125^{\circ}C$ $V_R=400V, I_F=9A, di_F/dt=800A/\mu s, T_j=150^{\circ}C$	S	- - -	4 5.5 5.7	- - -	

1 Power dissipation

$$P_{\text{tot}} = f(T_C)$$


parameter: $T_j \leq 175^\circ\text{C}$



2 Diode forward current


$$I_F = f(T_C)$$

parameter: $T_j \leq 175^\circ\text{C}$




3 Typ. diode forward current

$$I_F = f(V_F)$$



4 Typ. diode forward voltage


$$V_F = f(T_j)$$



5 Typ. reverse recovery time

$$t_{rr} = f(dI_F/dt)$$


parameter: $V_R = 400V$, $T_j = 125^\circ C$



6 Typ. reverse recovery charge

$$Q_{rr} = f(dI_F/dt)$$


parameter: $V_R = 400V$, $T_j = 125^\circ C$



7 Typ. reverse recovery current

$$I_{rr} = f(dI_F/dt)$$


parameter: $V_R = 400V$, $T_j = 125^\circ C$



8 Typ. reverse recovery softness factor

$$S = f(dI_F/dt)$$


parameter: $V_R = 400V$, $T_j = 125^\circ C$




9 Max. transient thermal impedance

$$Z_{thJC} = f(t_p)$$

parameter : $D = t_p/T$



PG-TO252 -3



*) mold flash not included

DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	2.16	2.41	0.085	0.095
A1	0.00	0.15	0.000	0.006
b	0.64	0.89	0.025	0.035
b2	0.65	1.15	0.026	0.045
b3	5.00	5.50	0.197	0.217
c	0.46	0.60	0.018	0.024
c2	0.46	0.98	0.018	0.039
D	5.97	6.22	0.235	0.245
D1	5.02	5.84	0.198	0.230
E	6.40	6.73	0.252	0.265
E1	4.70	5.21	0.185	0.205
e	2.29 (BSC)		0.090 (BSC)	
e1	4.57		0.180	
N	3		3	
H	9.40	10.48	0.370	0.413
L	1.18	1.70	0.046	0.067
L3	0.90	1.25	0.035	0.049
L4	0.51	1.00	0.020	0.039
F1	10.60		0.417	
F2	6.40		0.252	
F3	2.20		0.087	
F4	5.80		0.228	
F5	5.76		0.227	
F6	1.20		0.047	

DOCUMENT NO.
Z8B00003328

SCALE
0 2.0 4mm

EUROPEAN PROJECTION

ISSUE DATE
16-02-2011

REVISION
04

Published by
Infineon Technologies AG
81726 Munich, Germany
© 2013 Infineon Technologies AG
All Rights Reserved.

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

The Infineon Technologies component described in this Data Sheet may be used in life-support devices or systems and/or automotive, aviation and aerospace applications or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support, automotive, aviation and aerospace device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.