

10086118-001RLF - E
SATA+USB : 2 in 1 Reverse
Type Right Angle, DIP



www.fci.com

Specifications

General	
Number of contacts	11
Orientation	Right Angle
Retention Feature	Fork Style Metal Clip
Electrical	
Current rating	1.5A per Contact
Resistance (Contact)	45 M-ohms max./30 M-ohms max.
Resistance (Insulation)	1000 M-ohms min.
Voltage rating	12V AC
Mechanical	
Durability (Mating cycles)	1500 Mating Cycles
Mounting	
Termination	Through Hole
Physical	
Color (Housing)	Black
Material (Contact)	Copper Alloy
Material (Housing)	High Temp Thermoplastic (UL 94 V-O)
Plating (Contact)	15u" Gold
Temperature (Operating - range)	0°C to 50°C
Other Features	
Packaging (Type)	Tape and Reel
Type	Plug/Receptacle

