

Datasheet

RS Pro Buffer 160daN

RS Stock No: **811-2407**



Product Details

RS Pro stop buffer is a rigid buffer, used as an end stop or to limit the stroke of moving parts. It has a repeated shock reaction of 160 daN. This rubber buffer eliminates the drawbacks considerably, as they dampen noise and absorb energy. The high impact stresses to structures often cause visible deterioration and high noise levels, particularly when these impacts are repeated periodically. It has a flat surface and responds immediately to impact, without over-extending the stroke of the moving part. The progressive buffer has a conical form and makes contact on a progressive basis, increasing deflection with increasing load. This action provides gradual arrest of moving parts, absorbing considerable energy, prohibiting instant high impact stresses.

Features and Benefits

- Easy to install
- High efficiency when used as a mount or buffer
- Flexible in moving machines
- Used in limiting impact stress and supporting fragile material or machinery in packaging applications

**Specifications:**

Base Material	Metal
Base Plate Diameter	40 mm
Base Plate Dimensions	40 x 20 mm
Base Plate Length	20 mm
Damper Material	Rubber
Maximum Operating Temperature	+80°C
Minimum Operating Temperature	-40°C
Mounting Style	Threaded Stud
Overall Height	45 mm
Repeated Shock Deflection	5 mm
Repeated Shock Reaction	160 daN
Thread Size	M10
Type	Stop Buffer
Thread Length	25 mm