



Ex N bulkhead Lumaire Series 457 Range

Features

- ¥ Low projection for zone 2 narrow corridors and low ceiling applications
- ¥ High IP rating
- ¥ Ideal for sewerage, water treatment works, dockside, culvert lighting etc.

Certification & Approval

Certification Code:	EEx N II T3
Certification Standard:	B54533 Part 2 Section 2.1
Certificate Number:	Bas.Ex 79267
Degree of Protection:	IP 67/8 (5m. submersion) subject to appropriate cable glanding.

Technical Data

Supply voltage	<ul style="list-style-type: none">• 240v, 50Hz maximum
Lamp source options	<ul style="list-style-type: none">• Max 150w GLS• T3 @ Ta = 40oC• With ES (E27) lampholder
Cable entries	<ul style="list-style-type: none">• 1 x M 20 - ISO as standard (bottom)• 1 x M20 - ISO available top and bottom.
Terminals	<ul style="list-style-type: none">• Two terminals and earth. Cable size 4mm2 max
Operating temperature	<ul style="list-style-type: none">• -20oC to +40oC
Access for lamp change	<ul style="list-style-type: none">• Removable glass with threaded internal gasket for ingress protection.
Finish	<ul style="list-style-type: none">• Grey enamel paint on pre-treated and primed surface.• Alternative finishes available
Material	<ul style="list-style-type: none">• Cast Iron to BS1452
Protective guard	<ul style="list-style-type: none">• Plastic coated wire guard available at extra cost.
Weight	<ul style="list-style-type: none">• 8kg.