


Housing - HC-B 24-TFQ-60/M1PG21S - 1661480

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Sleeve housing, for double locking latch, height 60 mm, with screw connection, 1x Pg21, lateral cable entry



Key commercial data

Packing unit	10 pc
GTIN	 4 017918 155513
Weight per Piece (excluding packing)	215.72 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

Dimensions

Height	60 mm
Width	43 mm
Length	120 mm
Wrench size, union nut	28 mm
External cable diameter	10 mm ... 19 mm

Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	For contact inserts HC-B24, BB46, D64, DD108, M
Type	B24
Housing type	Sleeve housings
Locking type	For double locking latch
No. of cable exits	1
Cable exit	Lateral
Screw connection	with

Housing - HC-B 24-TFQ-60/M1PG21S - 1661480

Technical data

General

Type of the screw connection	1x Pg21
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray
Cable gland material	Nickel-plated brass
Cable seal material	NBR

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Approvals

Approvals

Approvals

GOST

Ex Approvals

Housing - HC-B 24-TFQ-60/M1PG21S - 1661480

Approvals

Approvals submitted

Approval details

GOST 

Drawings

Dimensioned drawing

