


#2250 - S-FTP Cat 7A LSZH (1200 MHz) 100m reel

Part NO: #2250
Product Code: S-FTP Cat 7A LSZH (1200 MHz)
Product Description
Application:
 Horizontal Wiring in LAN
Reference Standard
 IEC61156-5-2009
Multi-construction
 4 Pair
Cable Construction
Conductor **Solid Bare Copper**
 Construction 0.62±0.01
 Standard Dia.(mm) 0.62
Insulation **Skin-Foam-Skin**
 Average Thickness 0.4
 Insulation Dia.(mm) 1.45±0.1×2C Twist
 Each Pair is Twisted ,Unshielded.
Al-Pet shield(on each pair,Al-side ov **≥115%**
Braiding Shield
 Construction 0.12±0.003×8×6
Jacket **LSZH**
 Thickness(mm) 0.7
 Dia.(mm) 8.2±0.3
 Jacket Color Yellow
Color
Insulation color are:
 Blue, White/Blue
 Orange,White/Orange
 Green, White/Green
 Brown, White/Brown
Marking
 Category 7A #2250 S-FTP 22 AWG 4 Pair 70C 1200MHZ LSZH
 [MeterMark]
PACKAGING
 100M/Wooden Drum

Design



Characteristics

Max.Conductor DC Resistance at 20°C (Ω /Km)	<66.6
Rated Temperature(°C)	70
Velocity ratio	78%
Impedance(Ω)	1-100MHz 100±15 100-250MHz 100±20 250-500MHz 100±25 500-1000MHz 100±30 1000-1200MHz 100±32

Frequency (MHz)	Attenuation (dB)	NEXT (dB)	PS NEXT (dB)	Return loss (dB)
1.00	2.10	78.00	75.00	20.00
4.00	3.70	78.00	75.00	23.00
10.00	5.80	78.00	75.00	25.00
16.00	7.30	78.00	75.00	25.00
31.25	10.30	78.00	75.00	23.60
62.50	14.60	78.00	75.00	21.50
100.00	18.50	75.40	72.40	20.10
250.00	29.70	69.40	66.40	17.30
500.00	42.80	64.90	61.90	17.30
600.00	47.10	63.70	60.70	17.30
900.00	58.50	61.10	58.10	15.50
1000.00	61.90	60.40	57.40	15.10
1200.00	68.40	59.20	56.20	14.30

Frequency (MHz)	ELFEXT (dB)	PSELFEXT (dB)
1.00	78.00	75.00
4.00	78.00	75.00
10.00	75.30	72.30
16.00	71.20	68.20
31.25	65.40	62.40
62.50	59.40	56.40
100.00	55.30	52.30
250.00	47.30	44.30
500.00	41.30	38.30
600.00	39.70	36.70
900.00	36.20	33.20
1000.00	35.30	32.30
1200.00	33.70	30.70

RoHS GUIDELINE			
We operate according to the following standards			
Control Item	Standard	Testing Method	Testing Equipment
Cadmium content (Cd)	<0.01%	EN1122	ICP-AES
Lead content (Pb)	<0.1%	EPA3050B	ICP-AES
Mercury content (Hg)	<0.1%	EPA3052	ICP-AES
Chromium (VI) content	<0.1%	EPA3060(UN-VIS)	ICP-AES
Polybrominated Biphenyls(PBB)	Forbidden	GC/MS	
Polybrominated Diphenyl Ether (PBDE)	Forbidden	GC/MC	