



Main

| | |
|-----------------------------|--|
| Range of product | Opale |
| Product or component type | Enclosure |
| Enclosure type | Distribution enclosure |
| Nb of 18 mm modules per row | 13 |
| Nb of horizontal rows | 3 |
| Provided equipment | Phase and neutral terminal blocks (2) Phase and neutral terminal block support (1) Earth terminal block (1) Blanking plate (3) Marking kit (3) |
| Width | 252 mm |
| Height | 485 mm |
| Depth | 111 mm |

Complementary

| | |
|--|---|
| Enclosure mounting | Surface |
| Total number of 18 mm modules | 39 |
| [In] rated current | 90 A |
| Type of rail | DIN |
| Cable entry | 4 knock-outs |
| Comb busbar and distribution block compatibility | XE compatible |
| Number of terminal blocks | 1 earth terminal block with 28 2 phase / neutral terminal block with 8 |
| Distribution block outgoers | 24 x 2.5 mm ² for earth 14 x 16 mm ² for phase / neutral 4 x 25 mm ² for earth 2 x 35 mm ² for phase / neutral |
| Locking options description | 1 keylock + 1 key |
| Enclosure material | Self-extinguishing material |
| Colour | Enclosure : white (RAL 9003) |

Environment

| | |
|-------------------------|------------------------------------|
| Standards | NF C 61-910 |
| Fire resistance | 750 °C conforming to IEC 60695-2-1 |
| IP degree of protection | IP30 conforming to NF EN 60529 |
| IK degree of protection | IK07 conforming to NF EN 50102 |

Offer Sustainability

| | |
|----------------------------------|--|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 0701 - Schneider Electric declaration of conformity |
| REACH | Reference contains SVHC above the threshold - go to CaP for more details |
| Product environmental profile | Available Download Product Environmental |
| Product end of life instructions | Need no specific recycling operations |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Contractual warranty

| | |
|--------|-----------|
| Period | 18 months |
|--------|-----------|
