

Enamelled copper wire on mini bobbin
CUL 500/1,80



Advantages

Insulating varnish basis min. polyurethane, mod. current loading

Degree 1

TJ min. 155 °C

Solderable

Applications

Enamelled copper wire for the production of coils and winding and for general laboratory needs.

Approvals



Enamelled copper wire on mini bobbin **CUL 500/1,80**

Type	CUL 500/1,80	Type	CUL 500/1,80	
Electrical data	30		Operating data	
			current car. cap.	9.50 A
			Environment	
			Heat resistance	155 °C (CL.F)
			insulating varnish	min. Polyurethan, mod.
			Tin-plate	>350 °C
			Measures and weights	
			Wire diameter	1.80 mm
			Weight	0.50 kg
			Length m (min.)	17

Subjects to change.