

D1.5/6.ADO

ABB contact for United
States of America



General Information

Extended Product Type:	D1.5/6.ADO
Product ID:	1SNA199051R2600
EAN:	3472591990515
Catalog Description:	D1.5/6.ADO IDC Terminal Blocks - Feed-through ADO - ADO - Grey
Long Description:	D1.5/6.ADO IDC Terminal Blocks - Feed-through - Grey, 1.5mm ² RatedCrossSection, 6mm Spacing TH 35-7.5, TH 35-15 Rail

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » IDC Terminal Blocks

Ordering

EAN:	3472591990515
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Width:	6.0 mm
Product Net Height:	45.5 mm
Product Net Depth:	41.0 mm
Product Net Weight:	6.00 g

Container Information

Package Level 1 Units:	50 piece
Package Level 1 Width:	61 mm
Package Level 1 Height:	47 mm
Package Level 1 Length:	220 mm
Package Level 1 Gross Weight:	0.30000 kg
Package Level 1 EAN:	3472591990515
Package Level 2 Units:	1000 piece
Package Level 2 Width:	300 mm
Package Level 2 Height:	150 mm
Package Level 2 Length:	500 mm
Package Level 2 Gross Weight:	6.35 kg
Package Level 3 Units:	48000 piece
Product Packing Type:	Box

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Flammability According to UL94:	V0

Additional Information

Ambient Temperature:	-5 ... +40 °C
Color:	Grey
Connection Type:	ADO System
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Dielectric Test Voltage:	3500 V
Function:	Feed-through
IIT Publishing Status:	Level 0 - Information enabled
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Number of Levels:	1
Pollution Degree:	3
Product Main Type:	D1.5/6.ADO
Product Name:	Terminal block
Rated Cross-Section:	1.5 mm ²
Rated Current (I_n):	Main Circuit 17.5 A
Rated Impulse Withstand Voltage (U_{imp}):	8000 V
Rated Short-time Withstand Current (I_{cw}):	for 1.0s 180 A
Rated Voltage (U_r):	1000 V
RoHS Date:	Z
Spacing:	6 mm
Sub-Function:	2 connections

Certificates and Declarations (Document Number)

BV Certificate:	1SND163013A0200
CB Certificate:	1SND163011A0200
cUL Certificate:	1SND163001A0202
Declaration of Conformity - CE:	1SND225010C1007
GOST Certificate:	1SND161005A1104
RoHS Information:	1SND230472F0201

Classifications

E-nummer:	2925802
ETIM 4.0:	EC000897 - Feed-through terminal block
ETIM 5.0:	EC000897 - Feed-through terminal block
Object Classification Code:	X

