


**71363-202LF - Mini-Jump™ : 2.54 mm (0.1 in.) Centerline, Single Row, High Body Shunt 0.76 μm (30 μin.) Gold Plating**



[www.fci.com](http://www.fci.com)

## Specifications

<b>Approvals / Certifications</b>	UL Approved
<b>Mechanical</b>	
<b>Durability (Mating cycles)</b>	50
<b>Insertion force</b>	450gf (1lbf) max.
<b>Withdrawal Force</b>	30gf (0.06lbf) min.
<b>Dimensional</b>	
<b>Height (Housing)</b>	9.15 mm (0.36 in.)
<b>Dim A (in)</b>	0.198 in.
<b>Dim A (mm)</b>	5.03 mm
<b>Spacing (Center line)</b>	2.54 mm (0.1 in.)
<b>Electrical</b>	
<b>Current rating</b>	2.5 amps
<b>Resistance (Contact)</b>	15 milli ohms (Initial), 20 milli ohms (After test)
<b>Resistance (Insulation)</b>	50000 M-ohms min.
<b>Voltage rating</b>	800V AC rms (Sea level)
<b>General</b>	
<b>Number of contacts (Total)</b>	2
<b>Number of rows</b>	1
<b>Mating half</b>	0.64 Square Pins of 3.68 mm min. Height
<b>Series Number</b>	71363
<b>Other Features</b>	
<b>Packaging (Type)</b>	Bag
<b>Bus Bar</b>	No
<b>Physical</b>	
<b>Color (Housing)</b>	Black
<b>Material (Contact)</b>	Copper Alloy
<b>Material (Housing)</b>	Glass-Filled Thermoplastic Polyester (UL 94 V-0)
<b>Plating (Contact area)</b>	0.76 μm (30 μin.) Gold
<b>Underplating (Contact)</b>	1.27 μm (50 μin.) Nickel
<b>Temperature (Range)</b>	-55°C to +120°C