

**Ordering number** C12767_HB-SQ-A

Family	High Bay	FWHM	54 degrees
Type	Lens	Efficiency	86 %
LED	MK-R	cd/Im	1.000
Color	Clear	Gerber File	Available
Diameter	25 + 25 mm		
Height	12.9 mm		
Style	Square		
Optic Material	PMMA		
Holder Material	-		
Fastening	Screw, pin, glue		
Status	Ready		

NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.



PRODUCT DATASHEET

High Bay series

last update 3/1/2013

GENERAL INFORMATION

- Product series especially designed & optimized for MK-R series of LEDs.
- Special care taken to make light distribution as uniform as possible.
- Lens material optical grade PMMA with high UV and temperature resistance. Allows use of high current and temperature conditions.

Please find more information about used material from below:

http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20UL94_Yellow%20Card.pdf


<http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20PLEXIGLAS-Datasheet.pdf>

D

C


B

A




Isometric view


Position pins




Bottom view



PCB-Suggestion



Front view



Top view

Material: PMMA

Tolerances if not otherwise shown:
According to DIN ISO 2768-1
Linear measures:
Up to 30mm class F, otherwise class M.

According to DIN ISO 2768-2
Form and position:
class K

Control for SPC marked dimensions.

This drawing is our property.
It can't be reproduced
or communicated without
our written agreement.



Ledil Oy
Salorankatu 10
FIN 24240 SALO
Finland

DRAWING TITLE

Datasheet HB-SQ-A lens

DRAWN BY

mav

DATE

27.03.2012

CHECKED BY

pv

DATE

27.03.2012

DESIGNED BY

mav

DATE

27.03.2012

SIZE

A4

DRAWING NUMBER

C12767

REV

1

SCALE

1:1

WEIGHT (g)

SHEET

1/1


D

A

LEDiL Oy C12767_HB-SQ-A_(MKR) Eff.84.3% / LDC (Linear)

Luminaire: LEDiL Oy C12767_HB-SQ-A_(MKR) Eff.84.3%

Lamps: 1 x Cree MKR (368.505lm@250mA)



LEDiL Oy C12767_HB-SQ-A_(MKR) Eff.84.3% / LDC (Polar)

Luminaire: LEDiL Oy C12767_HB-SQ-A_(MKR) Eff.84.3%
Lamps: 1 x Cree MKR (368.505lm@250mA)

