



22MM METAL ROUND COMPLETE UNIT COMBINATION:
 SELECTOR SWITCH HEAVY DUTY LATCHING 2 SWITCH
 POSITIONS O-I NON-ILLUMINATED SCREW TERMINAL,
 1NO+1NC WITH HOLDER BLACK SOLVENT-RESISTANT

Enclosure:	
material / of the housing	metal
Shape / of the housing front	round
Actuator / signaling device:	
Design of the product	Complete unit, round
Design of the operating mechanism	selector switch heavy-duty version
Type of unlocking device	rotate-to-unlatch mechanism
Color / of the activation element	black
Material / of the activation element	plastic
Number of switching positions	2
Actuating angle	
• clockwise	° 50
Product component / front ring	Yes
Material / of the front ring	metal
Color / of the front ring	silver
Design of front ring	Standard
Contact block / lampholder	
Design of the electrical connection	screw-type terminals

Number of switching elements		1
Number of NC contacts / for auxiliary contacts		1
Number of NO contacts / for auxiliary contacts		1
Number of change-over switches / for auxiliary contacts		0
Product function / positive opening		Yes
Number of lampholders		0
Product component / fluorescent materials		No
Product extension / optional / fluorescent materials		No

Accessories:

Product component / holder for 3 switching elements

No

General technical details:

Type of voltage / of the operating voltage

AC/DC

Operating voltage

- rated value

V

5 ... 400

Operating current

- at AC-12

- at 24 V / rated value

A

10

- at 48 V / rated value

A

10

- at 110 V / rated value

A

10

- at 230 V / rated value

A

10

- at 400 V / rated value

A

10

- at AC-15

- at 24 V / rated value

A

6

- at 48 V / rated value

A

6

- at 110 V / rated value

A

6

- at 230 V / rated value

A

6

- at 400 V / rated value

A

3

- at DC-12

- at 24 V / rated value

A

10

- at 48 V / rated value

A

5

- at 110 V / rated value

A

2.5

- at 230 V / rated value

A

1

- at DC-13

- at 24 V / rated value

A

3

- at 48 V / rated value

A

1.5

- at 110 V / rated value

A

0.7

- at 230 V / rated value

A

0.3

- for devices without incandescent lamp / according to IEC 60068-2-27

<= 50g

Resistance against vibration / according to IEC 60068-2-6		20 ... 200 Hz: 5g
Operating cycles / maximum	1/h	1,000
Mechanical operating cycles as operating time / typical		300,000
Item designation		S
<ul style="list-style-type: none"> • according to DIN EN 61346-2 • according to DIN 40719 extendable after IEC 204-2 / according to IEC 750 		S
Tightening torque / of the screws in the bracket / maximum	N-m	1
<ul style="list-style-type: none"> • during operating • during storage 	°C	-25 ... +70
	°C	-40 ... +80
Protection class IP		IP67
climatic class / during the operating phase / according to EN 60721		3K6
Type of mounting		front mounting
Shape / of the installation hole		round
Installation width	mm	28.5
Mounting diameter	mm	22
Mounting height	mm	24
Mounting depth	mm	63

Certificates/approvals:

General Product Approval



CCC



CSA



GOST



UL

Test Certificates

[Special Test Certificate](#)

Shipping Approval



ABS



BUREAU
VERITAS



DNV



LRS



PRS



RINA

other

[Confirmation](#)

[other](#)



UL

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrial-controls/mall>

Cax online generator:

<http://www.siemens.com/cax>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
<http://support.automation.siemens.com/WW/view/en/3SB3601-2PA11/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)
http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3SB3601-2PA11

last change:

Aug 3, 2012